# elo

## 2794L 27-inch LCD

**Open-Frame Touchscreen** 





**Integrated Touch** 



Commercial Grade



**3-Year Warranty** 

### **Product Overview**

The Elo 2794L 27-inch open-frame LCD touchscreen features a slim design and narrow outside dimensions due to the state-of-the-art, energy-saving LED backlight, using less electricity to operate and generating less heat. This compact display is designed for touch, with proven Elo expertise and reliability built in. The 2794L provides stable, drift-free operation with outstanding image clarity and light transmission for accurate touch responses and vivid images. Featuring a brilliant wide viewing angle panel, the open-frame touchscreen instantly grabs and holds the users' attention for kiosks, casino and amusement, retail self-service, and industrial automation environments.

Choice of touch technology:
Standard bezel: IntelliTouch\* SAW
or IntelliTouch Dual-Touch SAW
Zero-bezel: TouchPro™ PCAP
or IntelliTouch SAW

PCAP 2GS (two glass solution) offers pristine optical clarity and touch durability

10 touch projected capacitive (PCAP) with Thru-glass capabilities that passes UL-60950 & IK-07 impact testing

#### 2794L 27-inch Open-Frame Touchscreen

Specifications					
Model	2794L				
Color	Black				
Active Display Area	23.53" x 13.23" / 597.6mm x 336.15mm				
Diagonal	27"				
Aspect Ratio	16:9				
Dimensions	Bezel: 24.93" x 14.74" x 1.65" / 633.2mm x 374.4mm x 41.8mm Zero-Bezel: 25.36" x 15.29" x 1.56" / 644.2mm x 388.4mm x 39.6mm				
Native Resolution	1920x1080 at 50, 60Hz				
Other Supported Resolutions	640x480 at 60Hz; 720x400 at 70Hz; 800x500 at 60Hz; 800x600 at 56, 60Hz; 1024x768 at 60Hz; 1280 x 800 60 Hz; 1280x1024 at 60Hz; 1366x768 at 60Hz, 60Hz RB; 1440x900 at 60Hz, 60Hz RB; 1680x1050 at 60Hz, 60Hz RB; 1920 x 1080 at 50, 60HzB				
Number of Colors	16.7 million				
Number of Touches	Single-touch, dual-touch and 10-touch				
Brightness (typical)	LCD panel: 300 nits; IntelliTouch ZB: 270 nits; IntelliTouch: 270 nits; IntelliTouch Dual-Touch: 270 nits; PCAP: 270 nits				
Response (typical)	12 msec				
Viewing Angle	Horizontal: 89°/178°; Vertical: 89°/178°				
Contrast Ratio	3000:1				
On-Screen Display	Accessible through switches on the unit's tethered OSD Control box. Controls: Menu, Up, Down, Select, Power  Settings: Brightness, Contrast, Clock, Phase, H-position, V-position, Auto-Adjust, Aspect Ratio, Sharpness, Color, Temperature, OSD Timeout, O Language, OSD H-Position, OSD V-Position, Recall Defaults, Video Priority, Information, Touch On Sleep Mode, Touch Through Languages: English, French, Italian, German, Spanish, Simplified Chinese, Traditional Chinese, Japanese Lockouts: OSD, Power				
Input Video Format	Analog VGA and DisplayPort				
Input Video Signal connector	Analog VGA on Female DB-15 connector; DisplayPort V1.1a - Supports later versions of Display Port video input				
Scanning Frequency	Horizontal: 30 - 82 kHz; Vertical: 50 - 75 Hz				
Power	External DC - Optional power brick (sold separately)  Monitor input power connector: Coaxial power jack (2.0mm (+0.0 -0.1mm) pin outer diameter, 6.4mm (+/- 0.3mm) barrel inner diameter, 8.8mm (+/- 0.3mm) barrel depth)  Monitor input power signal specifications: 12VDC +/- 5%				
Power Consumption	ON (monitor + power brick): 30W  Consumption SLEEP (monitor + power brick): 1.5W  OFF (monitor + power brick): 0.5W				
Temperature	Operating: 0 °C to 40 °C (32 °F to 104 °F); Storage: $-20$ °C to 60 °C ( $-4$ °F to 140 °F)				
Humidity	Operating: 20% to 80%; Storage: 10% to 95%				
Weight	Unpackaged: 16.1 lb (7.3 Kg); Packaged: 22.27 lb (10.1 Kg)				
Shipping Dimensions	30.79" x 20.87" x 7.87" / 782mm x 530mm x 200mm				
Mounting Options	200mm x 100mm VESA mount on rear of unit; 4 Hole mounting interface on all four sides; Front mount with optional bezel kit (IT/AT/ST Models); Flus mount with included brackets (PCAP/iTouch/Non-Touch Models)				
Warranty	3 years standard				
MTBF	50,000 hours demonstrated				
Agency Approvals	UL, FCC; RCM; cUL, IC; CCC; CE, TUV; VCCI; KCC; CoC; BSMI; CB; RoHS, China RoHS, WEEE, IMERC				
What's in the Box	All displays include: VGA Cable, RJ45 OSD Remote, USB Touch Cable, User Manual CD and Quick Install Guide; For Zero-Bezel Models: Flush Mount Brackets w/Screws; For Bezeled Models: "L" (Side Mount) Brackets w/Screws				

#### **Ordering Information**

Model	Part Number	Part Description	Technology	Interface	Surface Treatment	Video Interface	Availability
2794L	E186635	ET2794L-2UWA-0-MT-ZB-NPB-G	Projected Capacitive	USB	Clear	VGA & DP	Worldwide
	E198424	ET2794L-4CWA-0-ST-ZB-NPB-G	IntelliTouch ZB	Dual serial/USB	Clear	VGA & DP	Worldwide
	E187031	ET2794L-8UWA-0-DT-NPB-G	IntelliTouch Dual-Touch	USB	Clear	VGA & DP	Worldwide
	E198623	ET2794L-8CWA-0-ST-NPB-G	IntelliTouch	Dual serial/USB	Clear	VGA & DP	Worldwide

#### **Extended Warranty Options**

Part Number	Description
758588-000	1 Year Extended Warranty, 7-inch to 22-inch LCD Touchmonitor
930057-000	2 Year Extended Warranty, 7-inch to 22-inch LCD Touchmonitor
E67295-000	Elo advance unit replacement for touchmonitors

 $To find out more about our extensive range of Elo touch solutions, go to {\bf elotouch.com}, or call the office nearest you.\\$ 

North America
Tel +1 408 597 8000
Fax +1 408 597 8050
elosales.na@elotouch.com

**Europe**Tel +32 (0)16 70 45 00
Fax +32 (0)16 70 45 49
elosales@elotouch.com

**Asia-Pacific** Tel +86 (21) 3329 1385 Fax +86 (21) 3329 1400 www.elotouch.com.cn **Latin America**Tel +1 786-923-0251
Fax +1 305-931-0124
elosales.latam@elotouch.com

