



1593L 15.6-inch LCD

Open-Frame Touchscreen



Integrated Touch



Commercial Grade



3-Year Warranty

Product Overview

The Elo 1593L 15.6-inch open-frame LCD touchscreen features a slim design and narrow outside dimensions due to the state-of-the-art, energy-saving LED backlight, using less electricity to operate and generating less heat. This compact display is designed for touch with proven Elo expertise and reliability built in. The 1593L provides stable, drift-free operation with outstanding image clarity and light transmission for accurate touch responses and vivid images. Instantly grabbing and holding users' attention, the open-frame touchscreen is perfect for kiosks, casino and amusement, retail self-service, and industrial automation environments.

**Choice of Elo touch technologies:
Standard bezel: IntelliTouch[®] SAW
Zero-bezel: TouchPro™ PCAP**

Elo's TouchPro PCAP offers:

- **2GS (two glass solution) with pristine optical clarity and touch durability.**
- **10 touch with thru-glass capabilities that passes UL-60950 & IK-07 impact testing**

**Video Interfaces: HDMI, VGA & Display Port
UL-60950 & IK-07 impact testing**

1593L 15.6-inch Open-Frame Touchscreen

Specifications	
Model	1593L
Color	Black
Active Display Area	13.55" x 7.62" / 344.232mm x 193.536mm
Diagonal	15.6"
Aspect Ratio	16:9
Dimensions	Bezel: 14.83" x 8.7" x 1.82" / 376.8mm x 221.1mm x 46.3mm Zero-Bezel: 15.54" x 9.53" x 1.71" / 394.7mm x 242.0mm x 43.4mm
Native Resolution	1366 x 768 at 60Hz, 60Hz RB
Other Supported Resolutions	640 x 480 at 60Hz; 720 x 400 at 70Hz; 800 x 500 at 60Hz; 800 x 600 at 56, 60Hz; 1024 x 768 at 60Hz; 1280 x 800 at 60Hz; 1280 x 1024 at 60Hz
Number of Colors	16.7 million
Number of Touches	Single-touch and 10-touch
Brightness (typical)	LCD Panel: 300 nits; IntelliTouch: 270 nits; TouchPro PCAP: 270 nits
Response (typical)	10 msec
Viewing Angle	Horizontal: 80°/160°; Vertical: 80°/160°
Contrast Ratio	500:1
On-Screen Display	Accessible through switches on the unit's tethered OSD Control box. Controls: Menu, Up, Down, Select, Power Settings: Brightness, Contrast, Clock, Phase, H-position, V-position, Auto-Adjust, Aspect Ratio, Sharpness, Color, Temperature, OSD Timeout, OSD Language, OSD H-Position, OSD V-Position, Recall Defaults, Video Priority, Information, Touch On Sleep Mode, Touch Through Languages: English, French, Italian, German, Spanish, Simplified Chinese, Traditional Chinese, Japanese Lockouts: OSD, Power
Video	HDMI V1.3 Type A receptacle for HDMI input Analog VGA on Female DB-15 connector DisplayPort V1.1a - Supports later versions of Display Port video input Input Video Horizontal Sync frequency range: 30 - 82KHz Input Video Vertical Sync (frame rate) frequency range: 50-75Hz
Power	External DC - Optional power brick (sold separately) Monitor input power connector: Coaxial power jack (2.0mm (+0.0 -0.1mm) pin outer diameter, 6.4mm (+/- 0.3mm) barrel inner diameter, 8.8mm (+/- 0.3mm) barrel depth) Monitor input power signal specifications: 12VDC +/- 5%
Power Consumption	ON (monitor + power brick): 13.6W SLEEP (monitor + power brick): 1.5W OFF (monitor + power brick): 0.5W
Temperature	Operating: 0 °C to 40 °C (32 °F to 104 °F); Storage: -20 °C to 60 °C (-4 °F to 140 °F)
Humidity	Operating: 20% to 80%; Storage: 10% to 95%
Weight	Unpackaged: 6.7 lbs / 3.02 kg; Packaged: 10.2 lbs / 4.62 kg
Shipping Dimensions	18.5" x 13.03" x 6.89" / 470mm x 331mm x 175mm
Mounting Options	75mm VESA mount; 2-hole mounting interface on all 4 sides; Rear mount (TouchPro PCAP Models); Front mount with optional bezel kit (IntelliTouch Models); Rack mount with optional bezel kit (IntelliTouch Models); Flush mount with included brackets (TouchPro PCAP Models)
Warranty	3 years standard
MTBF	50,000 hours demonstrated
Agency Approvals	UL, FCC; RCM; cUL, IC; CCC; CE, TUV; VCCI; KCC; CoC; BSMI; CB; RoHS, China RoHS, WEEE, IMERC
What's in the Box	HDMI Cable, VGA Cable, OSD Remote, Touch USB Cable, User Manual CD and Quick Install Guide; For Zero-Bezel Models: Flush Mount Brackets w/Screws; For Bezeled Models: "L" (Side Mount) Brackets w/Screws, EEL Label, Japan Class-B TM info sheet

Ordering Information

Model	Part Number	Part Description	Technology	Interface	Surface Treatment	Video Interface	Availability
1593L	E331799	ET1593L-2UWB-0-MT-ZB-NPB-G	TouchPro PCAP	USB	Clear	HDMI, VGA & Display Port	Worldwide
	E329636	ET1593L-8CWB-0-ST-NPB-G	IntelliTouch	Dual serial/USB	Clear	HDMI, VGA & Display Port	Worldwide

Extended Warranty Options

Part Number	Description
758588-000	1 Year Extended Warranty, 7-inch to 22-inch LCD Touchmonitor
930057-000	2 Year Extended Warranty, 7-inch to 22-inch LCD Touchmonitor
E67295-000	Elo advance unit replacement for touchmonitors

To find out more about our extensive range of Elo touch solutions, go to elotouch.com, or call the office nearest you.

North America

Tel +1 408 597 8000
Fax +1 408 597 8050
elosales.na@elotouch.com

Europe

Tel +32 (0)16 70 45 00
Fax +32 (0)16 70 45 49
elosales@elotouch.com

Asia-Pacific

Tel +86 (21) 3329 1385
Fax +86 (21) 3329 1400
www.elotouch.com.cn

Latin America

Tel +1 786-923-0251
Fax +1 305-931-0124
elosales.latam@elotouch.com

Elo reserves the right to change or update, without notice, any information contained herein; to change, without notice, the design, construction, materials, processing or specifications of any products; and to discontinue or limit production or distribution of any products. Elo, the Elo logo IntelliTouch and TouchPro are either trademarks or registered trademarks of Elo Touch Solutions, Inc. All other trademarks are the property of their respective owners. © 2017 Elo Touch Solutions, Inc. All rights reserved. 17034AES00047

