

Mini DisplayPort to DisplayPort 4K @ 60 Hz Cable Adapter (M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: P583-006-BK



Connects the Mini DisplayPort (mDP) or Thunderbolt™ output on your computer or laptop to the DisplayPort™ input on a monitor, television or projector.

Features

Sends Ultra High Definition Mini DisplayPort Audio/Video to DisplayPort Monitor

- Connects mDP or Thunderbolt computer or laptop to DisplayPort monitor, TV or projector
- Recommended for displaying video on large monitor or digital sign
- No separate power adapter required

Vibrant Video Quality

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 60 Hz
- Meets DisplayPort 1.2 standards
- Supports High Bit Rate 2 (HBR2) bandwidth up to 21.6 Gbps
- Backward compatible with previous DisplayPort versions

Superior Materials for Superior Performance

- Locking DisplayPort connector prevents accidental disconnection
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332203502 |

Highlights

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 60 Hz
- Locking DisplayPort connector prevents accidental disconnection
- Gold-plated connectors and contacts for maximum conductivity
- Meets DisplayPort 1.2 standards
- Supports High Bit Rate 2 (HBR2) bandwidth up to 21.6 Gbps

System Requirements

- Source device with Mini DisplayPort or Thunderbolt output
- Display device with DisplayPort input

Package Includes

- P583-006-BK Mini DisplayPort to DisplayPort 4K @ 60 Hz Adapter Cable (M/M), Black, 6 ft.



| | |
|-------------------------------------|---------------------------|
| Technology | DisplayPort |
| PHYSICAL | |
| Color | Black |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.8 |
| Cable Length (in.) | 72 |
| Shipping Dimensions (hwd / cm) | 15.24 x 10.16 x 1.27 |
| Shipping Dimensions (hwd / in.) | 6.00 x 4.00 x 0.50 |
| Shipping Weight (kg) | 0.09 |
| Shipping Weight (lbs.) | 0.19 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 TO 158 F (0 TO 70 C) |
| Storage Temperature Range | 14 TO 176 F (-10 TO 80 C) |
| Operating Humidity Range | 10% TO 85% RH |
| Storage Humidity Range | 5% TO 90% RH |
| CONNECTIONS | |
| Side A - Connector 1 | DISPLAYPORT (MALE) |
| Side B - Connector 1 | MINI DISPLAYPORT (MALE) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>