

JABRA EVOLVE™ 65



MORE THAN HEADSETS, A WORKPLACE EVOLUTION

- Made for voice calls and music
- Passive noise cancellation
- 30-meter (100 feet) wireless range
- 10-hour battery life

DETAIL	INFORMATION
Packaging dimensions	L 21.0 x W 18.1 x H 5.3 cm
Weight mono / duo	Mono headset 282.1 g, Stereo headset 310.3 g
Whats in the box	Pouch, Evolve 65 Headset, Warning leaflet, Warranty leaflet, Quick Start Guide, Foam inlay (available for DUO only)
Battery included	Yes
Charging time	Max. 120 minutes
AC power supply	USB power supply by PC with USB connection, Battery power with Bluetooth connection
Certifications	Regulatory Approvals: CE, FCC ID, IC ID KCC, RCM, NCC, TELEC, SRRC Industrial Certifications: Lync, Avaya, Cisco, Alcatel Lucent and Astra
Warranty	2 years
Bluetooth device	Yes
DECK Device	No
NFC	No
Operating range	Up to 30m/100ft
Headset bandwidth	Wideband
Connection (mini jack, USB, etc)	USB/Bluetooth
Talk time	Up to 7 hours
Standby time	Up to 15 days
Speaker Size	D28x3.9mm
Speaker sensitivity	93.6dB SPL @1kHz
Speaker impedance	32+/-4.8Ω, @1.0kHz
Speaker Max Input Power	Rated Input 5mW @0.4V, max input 10mW @0.56V
Speaker Frequency Range	150Hz~7kHz, @Output S.PL -10dB
Microphone type	Electret Condenser (ECM) Uni-Directional Microphone
Microphone Sensitivity	f=1 kHz, Pin=1 Pa, 0dB=1V/Pa Min: -32 dB, Max: -28 dB
Microphone Frequency Range	100 Hz – 10 kHz
Supported Bluetooth profiles	A2DP (v1.2), Hands Free Profile (v1.6), Headset Profile (v1.2), AGHFP (v1.6)
Bluetooth wireless technology	Bluetooth 4.0
Speaker bandwidth Music mode	HiFi
Speaker bandwidth Speak mode	Wideband
Microphone bandwidth	Wideband
Operating temperature	-10 °C to + 50 °C
Storage temperature	-30 °C to + 80 °C Storage temperature range: (-20°C to +35°C 6 months), (+35°C to +45°C 3 months), (+45°C to +45°C 1 month), (+60°C to +70°C 1 hour with no degradation), (+70°C to +85°C max. 1 hour (<20% degradation)
Supported modes	SCO, eSCO, Sniff mode
Security	Pairing, Authentication and Encryption (Bluetooth standard)
Paired devices	Up to 8 trusted devices, 2 active stand-by Bluetooth connections
Power consumption speaker	Rated Input 5mW @0.4V, max input 10mW @0.56V

SKU	DESCRIPTION	EAN CODE
6593-823-309	Jabra EVOLVE 65 MS Mono	5706991017168
6599-823-309	Jabra EVOLVE 65 MS Stereo	5706991017144
6593-829-409	Jabra EVOLVE 65 UC Mono	5706991017175
6599-829-409	Jabra EVOLVE 65 UC Stereo	5706991017151

* Phone dependent