


Medical Display Series Solution

MEDDP-524

24" LED LCD Monitor



Features

- 24" LCD Panel with LED Backlight
- Compact and Terse Design
- VGA x 1, HDMI x 1, DP x1
- Wide view angle 178°(H)/178°(V)
- True Flat Screen with PCT Touch
- Invisible OSD Design
- CE/FCC Class B Passed18, EN60601-1:2006
- Low Power Consumption

Specifications

Display

Size	24"
Resolution	Full HD 1920 x 1080
Max. Colors	16.7M
Brightness (Typ.)	250 nits
Viewing Angle (CR=10)(Typ.)	178°(H)/178°(V)
Contrast Ratio (Typ.)	3000:1
Touch Screen	Projective capacitive touch screen (optional)

System

OS Support	Windows® XP, Window® 7
------------	------------------------

I/O

Audio	Audio-in x 1
Serial Port	USB x 1 for touch controller
Signal	VGA x 1, HDMI x 1, DP x 1
Speaker	2W speaker x 2 on back side

Mechanical and Environmental

Power Consumption	Full Loading :34.7Watts
Power Requirement	DC12V / 5A power input
Operating Temperature	5°C ~ 40°C(41°F ~ 104°F)
Storage Temperature	-10°C ~ 60°C(14°F ~ 140°F)
Storage Humidity	10%~90%@35°C, non-condensing
Gross Weight	7.7kg (16.98lb)
Net Weight	5.8kg (12.79lb)
Dimension	576.1 x 344.3 x 62.1 (mm)
EMC	CE/FCC Class B Passed 18, ISO14971, EN 60601-1:2006, UL60601 ver 3.0

Ordering Information

» MEDDP-524DTT-A1-1020

LCD monitor.24" 250nits LED 2.DC 12V.C-TS.Med adapter

» MEDDP-524DT-A1-1020

LCD monitor.24" 250nits LED 2.DC 12V.Med adapter