

New and Improved!

GBC[®] Catena[™] 65

Posters

Signage

Charts

Graphs

Placemats

Certificates

POP Displays

The Catena[™] 65 tackles your most demanding jobs with unmatched ease, versatility and efficiency. This new and improved laminator encapsulates and mount jobs up to 27" wide, making it the perfect choice for small print shops, universities and large offices. Plus, its increased ¼" mounting gap ensures that mounting to foam core is quick and frustration-free. Equipped with new easy-to-use features including an open design, pivoting table, AutoSpeed and programmable presets, the Catena 65 is now simpler than ever to operate--even for first-time users.

Easy to Use

- AutoSpeed takes the guesswork out of laminating and ensures the best output every time
- Pivoting table and heat shield provide easier access when changing film
- AutoGrip aluminum, lightweight shafts make it simple to remove and add film
- Pivoting table offers a place to rest heavy film rolls while inserting film on the shaft, simplifying the film prepping process
- Redesigned, easy-to-use control panel makes key buttons easier to find
- Additional stop button on the back of the machine allows users to easily stop the machine while viewing output
- Programmable preset keys store your most commonly used temperature settings
- Rear trimmer makes trimming after lamination hassle-free

Quality & Versatility

- Designed for thermal encapsulation and mounting applications
- Mount to boards up to ¼" thick
- Optional rewind kit separates the release liner and enables the use of PSA films for cold applications
- Adjustable temperature control up to 302F degrees
- Variable laminating speeds from 1' – 8.5' per minute
- Removable shaft hooks on the back of the machine extend the exit, reducing the likelihood of film wraps
- Open design with improved rollers increase ease-of-use and produce better quality output

www.gbconnect.com



GBC® Catena™ 65



Product Specs


Product Number	1715845
Warm-up Time	<10 Min
Variable Speed	1 – 8.5 ft/min
Film Supplies Supported	
Film Thickness	Up to 10 mil
Film Width	Up to 27"
Core Size	1" (included), 2.25" (with optional core adapter)
Film Type	
Thermal	Nap I; Nap II; PET/LDPE; PET/EVA
Cold	PSA (with optional rewind kit)
AutoSpeed	Yes
Slow Forward/Reverse	Yes
Rear Stop Button	Yes
Rear Trimmer	Yes
Fan	Yes
Ready Light Indicator	Yes
Temperature Display	Yes
Programmable Temperature Preset	Yes
Energy Saver	
Standby	2 Hrs without use
Auto Shut-off	3 Hrs without use
Rewind Kit	Optional
Warranty	90 days
Dimensions	35" (88.9cm) x 14" (35.6cm) x 21" (53.3cm)
Weight	111lbs (50.3kg)
Power Requirements	120V, 60Hz




Rear Stop Button



Easy to Use Control Panel



1/4" Mounting Capability



Pivot Table

