

Single Port KVM over IP Switch with Single Port Power Switch KN1000A

- ATEN's new KN1000A Single Port KVM over IP Switch provides access and control "over-IP" for conventional KVM switches and servers that do not have built-in over-IP functionality. It allows system operators to monitor and access computers from remote locations for "down to the BIOS-level" troubleshooting, using standard Web browsers or Windows and Java based application programs, without the need to be on site for constant IT maintenance. In addition, the KN1000A supports out-of-band access in case the LAN goes down, with external modem support as backup.

To help you manage and control widely distributed servers efficiently from a remote console, a built-in single-port power switch provides remote power management of a server connected locally, allowing you to turn a server On or Off, and reboot it. In addition, you can add an ATEN PDU unit to manage the power status of even more devices. The KN1000A also provides serial console management over the Internet which can remotely control serial console devices such as network switches.

The KN1000A makes it easy to work on many tasks simultaneously, featuring a unique LUC (Laptop USB Console) port for quick KVM access via a laptop, user-friendly OSD, virtual media functionality without additional cables, and video resolutions up to 1920 x 1200.

The KN1000A's Virtual Media function allows you to perform file transfers, system diagnostic testing, software patches and application installations, all from the remote console. There is no need to physically mount an optical drive directly at the server to perform data related tasks. Now you can conveniently troubleshoot and resolve OS and BIOS-level problems from any remote location.


Both Windows GUI Client and Java Client Applet are available from a browser based and Windows application program to provide easy and flexible remote access. Each application provides a unique way to login and access the remote server from anywhere over a network. The inclusion of a Java-based client ensures that the KN1000A platform is independent and able to work with most operating systems.

With these advanced features, the KN1000A is the fastest, most reliable and cost effective solution to remotely access and manage widely distributed multi-server installations, such as for kiosks and automated banking machines.

Front view



Rear view



Features

Hardware

- Provides over-IP capability to servers or KVM switches that do not have built-in over-IP functionality*
- Built in single port Power Switch
- Supports PS/2, USB, Sun Legacy (13W3)** and serial (RS-232) connectivity
- Local console provides PS/2 and USB keyboard and mouse support
- Supports multiplatform server environments: Windows, Mac, Sun, Linux and VT100 based serial devices
- Virtual Media Support
- High video resolution – up to 1920 x 1200 @ 60 Hz with 24 bit color depth for the local console; up to 1920 x 1200 @ 60 Hz with 24 bit color depth for remote sessions

Note:

* Compatible KVM Switches include the following: CS9134, CS9138, CS1308, CS1316, CS1754, CS1758, CS1708A, CS1716A, ACS1208A, ACS1216A, KH2508A, KH2516A, KH1508A and KH1516A (Some of the KN1000A's features may not be supported, depending on the functionality of the connected KVM switch. For example, some switches do not support virtual media). Some features found on the connected KVM switches may not be supported on the KN1000A. (For example, the CS1754's audio.)

** Requires CV130A converter purchase

Management

- Up to 64 user accounts – up to 32 users simultaneously share the control
- End session feature – administrators can terminate running sessions
- Event logging and Windows-based Log Server support
- Critical system event notification via SMTP email; SNMP trap and Syslog support
- Remote firmware upgradable
- Serial console management – serial terminal access. Access the device connected to KN1000A via a built-in serial viewer, or via third party software (such as PuTTY) for Telnet and SSH sessions
- PPP mode (modem) dial-in/dial out support for out-of-band, and low bandwidth operation
- Port Share Mode allows multiple users to gain access to a server simultaneously
- Integration with ATEN CC2000 Centralized Management Software
- Integration with ATEN PDU for remote power control
- Remote power on and off control function with Wake on LAN
- On/Off scheduling for power outlet. Power management tasks can be scheduled on a daily, weekly, monthly or user specified time basis
- Safe shutdown support
- Auto-Ping pings a device to determine its status, if the ping test fails after a set amount of time – it automatically takes an action assigned
- DDNS (Dynamic Domain Name System)
- Export/import user account and configuration settings
- Manage browser access methods (disable browser, http, or https)

Easy-to-Use Interface

- Browser-based and AP GUIs offer a unified multilanguage interface to minimize user training time and increase productivity
- Multiplatform client support (Windows, Mac OS X, Linux, Sun)
- Multi-browser support: Internet Explorer, Chrome, Firefox, Safari, Opera, Mozilla, Netscape
- Browser-based UI in pure Web technology allows administrators to perform administrative tasks without pre-installed Java software package required
- Full-screen or sizable and scalable Virtual Remote Desktop window
- Magic Panel – a special hideaway control panel with configurable function icon

Advanced Security

- Smart Card / CAC Reader Support
- External authentication support: RADIUS, LDAP, LDAPS, and MS Active Directory
- Supports TLS 1.2 data encryption and RSA 2048-bit certificates to secure users log in from browser
- Flexible encryption design allows users to choose any combination of 56-bit DES, 168-bit 3DES, 256-bit AES, 128-bit RC4, or Random for independent KB/Mouse, video and virtual media data encryption
- IP/MAC Filter for enhanced security protection
- Supports password protection
- Private Certificate Authority

Virtual Media

- Virtual media enables file applications, OS patching, software installation and diagnostic testing
- Works with USB enabled servers at the operating system and BIOS levels
- Supports USB 2.0 DVD/CD drives, USB mass storage devices, PC hard drives and ISO images


Virtual Remote Desktop

- BIOS-level access
- Video quality and video tolerance can be adjusted to optimize data transfer speeds; monochrome color depth setting, threshold and noise settings for compression of the data bandwidth in low bandwidth situations
- Full screen video display or scalable video display
- Message Board for communication among remote users
- On-screen keyboard with multilanguage support
- Mouse Dynasync™
- Exit Macros support

Highlights

Over-IP Capability For Legacy KVM Switches	Protects your original KVM switch investment. No need to purchase new KVM switches to achieve the benefits of over-IP connectivity.
Remote Power Control	A built-in single-port Power Switch allows remote power management of a server installation connected locally at the KN1000A. In addition, you can add an ATEN PDU unit and remotely control the power status (On, Off, Reboot) of all devices connected to the installation, and monitor the current power status as well.
Multi-Keyboard Language Support — On-Screen Keyboard	The KN1000A supports multiple keyboard language input – including English, French, German, Italian, Spanish, Japanese, Korean, and Traditional Chinese. There is no need to have a separate keyboard for each language – and you can key data in any of these languages with the KN1000A's convenient on-screen keyboard.

External Authentication Support	In addition to its own security protection, the KN1000A allows you to set up login authentication and authorization management from external sources such as RADIUS, LDAP, LDAPS and MS Active Directory.
Ease-to-use user interface	A user-friendly intuitive GUI provides convenient access, configuration and operation. Local Console, browser-based and AP GUIs offer a unified multilanguage interface to minimize user training time and increase productivity.
Virtual Remote Desktop	The remote desktop can appear full-screen or as a window with a flexible scaling video display. Advanced features such as a Message Board, Mouse DynaSync™, Virtual Media and Keyboard Pass Through, create a Virtual Remote Desktop that allows users to operate servers from remote locations just as if they were actually at the local site.
Superior Video	With enhanced fps throughput for crisp responsive video display, the switches offer resolutions of up to 1920 x 1200 @ 60 Hz; and vibrant 24-bit color depth for rich remote session displays.
Configurable Network Bandwidth settings	A network setting is provided that allows you to streamline data throughput by adjusting the size of the data stream (bandwidth) to match network traffic conditions. Video performance can be adjusted so that data throughput is optimized for the available network bandwidth. With high speed LAN access, the network setting can be adjusted so that a greater amount of video information is sent, resulting in a higher quality video display. In a limited bandwidth situation, the network setting can be adjusted so that net lag is minimized.
Mouse DynaSync™	Automatically synchronizes the local and remote mouse movements for perfect alignment of mouse pointers, regardless of server mouse acceleration settings.
Message Board	To alleviate the problem of access conflicts arising from multiple logins, the Message Board functions like an Internet chat program, allowing users who are logged in to instantly communicate with each other.
Virtual Media	Virtual Media support lets you map DVD/CD-ROMs and other storage media to a remote server. This function allows you to conduct file transfers, application and OS patches, and diagnostics remotely.
Smart Card Reader	The smart card reader function allows a reader plugged into a local client computer's USB port to be redirected, and appear as if it were plugged into the remote server. One purpose of smart cards (Common Access Cards, for example), is to allow authentication to the remote server from the local client.



Specifications

Function	KN1000A
Connectors	
Console Ports	1 x SPHD-18 Male (Yellow)
KVM (Computer) Ports / Virtual Media	1 x SPHD-18 Female (Yellow)
PON	1 x DB-9 Male (Black)
RS-232	1 x DB-9 Male (Black)
LAN Ports	1 x RJ-45 Female
Power Inlets	1 x IEC320 C14
Power Outlets	1 x IEC320 C13
Power	1 x DC Jack
Laptop USB Console (LUC)	1 x USB Mini-B Female (Black)
Switches	
Reset	1 x Semi-recessed Pushbutton
LEDs	
Power	1 (Orange)
Power Outlets	1 (Orange)
Link	1 (Green)
10/100/1000 Mbps	1 (10: Orange / 100: Orange & Green / 1000: Green)
Emulation	
Keyboard / Mouse	USB; PS/2
Video	1920 x 1200 @ 60 Hz; DDC2B
Maximum Input Power Rating	100 – 240 V ~ 50 - 60 Hz; 10A
Output	100 – 240 V ~ 50 - 60 Hz; 9A
Power Consumption	DC 5.3 V; 4.48 W
Environmental	
Operating Temperature	0° to 40° C
Storage Temperature	- 20° to 60° C
Humidity	0 - 80% RH, Non-condensing
Physical Properties	
Housing	Metal
Weight	0.88 kg
Dimensions (L x W x H)	31.00 x 8.39 x 4.20 cm

ATEN International Co., Ltd.

3F, No.125, Sec. 2, Datong Rd., Sijhih District., New Taipei City 221, Taiwan
 Phone: 886-2-8692-6789 Fax: 886-2-8692-6767
 www.aten.com E-mail: marketing@aten.com

Publish Date: 12 / 2016 V1.0



© Copyright 2016 ATEN® International Co., Ltd.
 ATEN and the ATEN logo are trademarks of ATEN International Co., Ltd.
 All rights reserved. All other trademarks are the property of their respective owners.