



HP LaserJet Managed Flow MFP E62575z

This HP LaserJet MFP with JetIntelligence combines exceptional performance and energy efficiency with professional-quality documents right when you need them—all while protecting your network from attacks with the industry's deepest security.¹



Print Speed: Up to 75 ppm black³

Print Resolution: Up to 1200 x 1200 dpi

Standard Connectivity: 1 Hi-Speed Device USB 2.0; 2 Hi-Speed USB 2.0 Host; 1 Gigabit Ethernet; 1 Hardware Integration Pocket

Standard Memory: 1.5 GB (printer); 1 GB (scanner)

Mobile Printing Capability: HP ePrint; Apple AirPrint™; Mopria™-certified; Google Cloud Print 2.0

Paper Handling: 100-sheet multipurpose feeder, 550-sheet input feeder, 150-sheet automatic document feeder, 500-sheet output feeder, 500 sheet output stapler stacker, two-sided printing

Display: 8.0-in (20.3 cm) Color Graphics Display (CGD) with touchscreen; rotating (adjustable angle) display; illuminated Home button (for quick return to the Home menu)

The world's most secure printing¹

- With HP Sure Start, each printer regularly checks its operating code and repairs itself from attempted hacks.
- Run-time intrusion detection continually monitors to detect and stop attacks, then automatically reboots.
- Centralize control of your printing environment with HP Web Jetadmin—and help build business efficiency.²
- Give workgroups what they need to succeed. Easily choose and deploy over 180 HP and third-party solutions.

High-speed performance meets energy efficiency

- Speed through tasks and save paper. Print two-sided documents nearly as fast as single-sided.
- This printer wakes up fast and prints your first page faster—in as quickly as 7.8 seconds.⁴
- This MFP uses exceptionally low amounts of energy thanks to its innovative design and toner technology.⁵
- Paper handling options include a wheeled stand and 550-sheet input feeder for paper sizes A6 to legal.

More. Pages, Performance, and Protection.⁶

- Produce sharp text, bold blacks, and crisp graphics with precision black toner.
- Original HP Toner cartridges with JetIntelligence deliver more pages per cartridge than predecessors.⁶
- Help retain the Original HP quality you paid for with anti-fraud and cartridge authentication technology.
- Spend less time replacing toner, and more on business. Choose high-yield toner cartridges.⁷

Give workgroups the speed they need

- Help workgroups capture every page easily and detect potential errors or missed pages—every time.
- Enter data more quickly and accurately using the pull-out keyboard.
- Help ensure every scanned document is properly oriented, cropped to size, and grayscale-optimized.
- Load up to 150 pages into the automatic document feeder for fast, unattended scanning.



¹ Based on HP review of 2016 published security features of competitive in-class printers. Only HP offers a combination of security features that can monitor to detect and automatically stop an attack then self-validate software integrity in a reboot. For a list of printers, visit <http://www.hp.com/go/PrintersThatProtect>. For more information: <http://www.hp.com/go/printersecurityclaims> ² HP Web Jetadmin is available for download at no additional charge at <http://www.hp.com/go/webjetadmin> ³ Measured using ISO/IEC 24734, excludes first set of test documents. For more information, see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁴ Measured after 15 min in sleep. Exact speed varies depending on the system configuration, software application, driver, document complexity and time in sleep. ⁵ Based on HP testing using the ENERGY STAR® program's Typical Electricity Consumption (TEC) method or as reported in energystar.gov versus the top three leading competitors as of 8/2015. Actual results may vary. For details see <http://www.hp.com/go/ljclaims> ⁶ More pages versus predecessor cartridges claim based on page-yield comparison of HP 37X High Yield Black Original LaserJet Toner Cartridges with HP 87X High Yield Black Original LaserJet Toner Cartridges. For more information, see <http://www.hp.com/go/learnaboutsupplies> ⁷ HP 37X High Yield Black Original LaserJet Toner Cartridges not included; please purchase separately. ⁸ Scan speed measured from ADF at default 300 dpi (black-and-white, grayscale, and color). Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

HP LaserJet Managed Flow MFP E62575z Specifications Table

Functions / Multitasking Supported	Print, Copy, Scan / Yes
Print Speed	Letter: Up to 75 ppm black; ⁵ First Page Out: 5.3 sec ⁷
Print Resolution	Black (fine lines): Up to 1200 x 1200 dpi
Print Technology	Laser
Print Resolution Technologies	FastRes 1200; 1200 x 1200 dpi
Print Cartridges Number	1 (black)
Standard Print languages	HP PCL 6, HP PCL 5 (HP PCL 5 driver available from the Web only), HP postscript level 3 emulation, native PDF printing (v 1.7), Apple AirPrint™
Printer Smart Software Features	Print preview, duplex printing, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, easy-access USB
Printer Management	HP JetAdvantage Security Manager; HP SNMP Proxy Agent; HP Web JetAdmin Software; HP WS Pro Proxy Agent; Printer Administrator Resource Kit for HP Universal Print Driver
Scan Type / Technology	Flatbed, ADF / Charge Coupled Device (CCD)
Scan Resolution	Hardware: 600 x 600 dpi; Optical: Up to 600 dpi
Scan File Format	Digital Send: PDF, Hi-Compression PDF, JPEG, TIFF, MTIFF, XPS, PDF/A, TEXT (OCR), Unicode TEXT (OCR), RTF (OCR), Searchable PDF (OCR), Searchable PDF/A (OCR), HTML (OCR), CSV (OCR); Scan to easy access USB: PDF, JPEG, TIFF, MTIFF, XPS, PDF/A, TEXT (OCR), Unicode TEXT (OCR), RTF (OCR), Searchable PDF (OCR), Searchable PDF/A (OCR), HTML (OCR), CSV (OCR); Print from easy access USB: PDF, PS, Print Ready Files (.prn, .pcl, .cht)
Scan Input Modes	Front panel applications: Copy; E-mail; Save to Network Folder; Save to USB; Save to Device Memory; Save to SharePoint; Open Extensibility Platform (OXp) applications; HP Scan or user application via TWAIN
Scan Size	ADF: 8.5 x 34.0 in Maximum; 2.7 x 5.8 in Minimum; Flatbed: 8.75 x 14.375 in
Scan Speed	Letter: Up to 90 ppm/180 ipm (b&w), up to 90 ppm/180 ipm (color) ¹⁰ ; Duplex Letter: Up to 180 ipm (b&w), up to 180 ipm (color)
Scanner Advanced Features	Optimize text/picture; Image adjustments; Job build; Output quality setting; Selectable scan resolution 75 to 600 dpi; Auto detect color; Edge Erase; Job notification; Blank page suppression; HP Quick Sets; HP EveryPage; Auto orientation; Embedded Optical Character Recognition (OCR), Auto crop to page; Auto-tone
Native Scan File Format	PDF, JPG, TIF, MTIF
Bit depth / Grayscale levels	Internal: 30 bit ; External: 24 bit / 256
Digital Sending Standard Features	Scan to E-mail; Save-to-Network Folder; Save-to-USB drive; Send to Sharepoint; Send to FTP; Send to LAN Fax; Send to Internet Fax; Local Address Book; SMTP over SSL; Blank Page Removal; Edge Erase; Auto Color Sense; Auto Crop To Content; Compact PDF; Auto Tonescale; Auto Orientation; Multi-Pick Detect; Auto Straighten; Auto Crop To Page; OCR
Copy Speed	Black (letter): Up to 75 cpm
Copy Resolution	Black (text and graphics): Up to 600 x 600 dpi (flatbed); Up to 600 x 450 dpi (ADF); Up to 600 x 600 dpi (flatbed); Up to 600 x 450 dpi (ADF)
Maximum Number Of Copies	Up to 9999 copies
Copier Settings	Two-sided copying, scalability, image adjustments (darkness, contrast, background cleanup, sharpness), N-up, N or Z-ordering, content orientation, collation, booklet, job build, edge-to-edge, job storage, ID Copy, Book Copy, A-to-B Copy (different media sizes)
Fax Features	Fax Phone TAM Interface Supported: No; Fax Telephone Mode Supported: No
Standard Connectivity	1 Hi-Speed Device USB 2.0; 2 Hi-Speed USB 2.0 Host; 1 Gigabit Ethernet; 1 Hardware Integration Pocket
Network Capabilities	Yes, via HP Jetdirect Ethernet embedded print server (standard) which supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); 802.11a/b/g/n wireless networking (optional).
Network Ready	Standard (built-in Gigabit Ethernet)
Wireless Capability	Optional, enabled with purchase of HP Jetdirect 2900nw Print Server JB031A or HP Jetdirect 3000w NFC/Wireless Accessory JB030A
Mobile Printing Capability	HP ePrint; Apple AirPrint™; Mopria™-certified; Google Cloud Print 2.0
Memory	Standard: 1.5 GB (printer); 1 GB (scanner); Maximum: 2.5 GB Total
Processor Speed	1.2 GHz / Hard disk: Standard, minimum 320 GB HP High-Performance Secure Hard Disk (AES 256 hardware encryption or greater)
Duty Cycle	Monthly, Letter: Up to 450,000 pages
Recommended Monthly Page Volume	5,000 to 40,000
Media Types Supported	Paper (plain, light, bond, recycled, heavy, extra heavy, cardstock, pre-printed, pre-punched, colored, rough, heavy rough), mono transparency, labels, letterhead, envelope, heavy envelope
Media Weight Supported	Feeder 1: 16 to 53 lb bond (plain), 16 to 24 lb (envelopes); feeder 2: 16 to 32 lb bond (plain)
Media Sizes Supported	feeder 1: Letter, legal, statement, executive, Oficio (8.5 x 13 in), envelopes [No. 9, No. 10, Monarch(7 3/4)], 3 x 5, 4 x 6, 5 x 7, 5 x 8; feeder 2: letter, executive
Media Sizes Custom	feeder 1: 3 x 5 to 8.5 x 14 in; feeder 2: 3.90 x 5.83 to 8.5 x 11 in
Paper Handling	100-sheet multipurpose feeder; 550-sheet input feeder, 150-sheet automatic document feeder; 500-sheet ouput feeder; 500 sheet output stapler stacker, two-sided printing; Duplex Options: Automatic (standard); Auto Document Feeder Capacity: Standard, 150 sheets; Envelope Feeder: Yes, 75 (optional); Standard Paper Trays: ² Input Capacities: up to 650 sheets; Output Capacities: Up to 1000 sheets; Up to 75 envelopes; Up to 200 sheets

What's in the box	JB80A HP LaserJet Multifunction Printer; HP Black Original LaserJet Toner Cartridge (~11K yield); CD with software drivers and documentation; Documentation (Hardware Install Guide); Power cord ¹
Replacement Cartridges	HP Black Managed LaserJet Toner (50,000 yield) W9004MC[3, 12]
Product Dimensions	W x D x H: 20.15 x 22 x 30.7 in; Maximum: 40.5 x 31.5 x 35 in (right side jam access door open, left side cartridge door open, all feeders open and extended, ADF open)
Product Weight	87.7 lb
Warranty Features	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements. Go to hp.com/support to learn about HP award winning service and support options in your region.
Control Panel	8.0-in (20.3 cm) Color Graphics Display (CGD) with touchscreen; rotating (adjustable angle) display; illuminated Home button (for quick return to the Home menu)
Display Description	8.0-in (20.3 cm) Color Graphics Display (CGD) with touchscreen; rotating (adjustable angle) display; illuminated Home button (for quick return to the Home menu)
Software Included	HP Connected, HP Device Experience (DXP), HP PCL 6 Printer Driver, HP Software Installer/Uninstaller, Mac OS Welcome Screen (Directs users to 123.HP.com or OS App Source for printer software), Online user manuals
Fonts and Typefaces	105 internal TrueType fonts scalable in HP PCL, 92 internal scalable fonts in HP postscript level 3 emulation (Euro symbol built-in); 1 internal Unicode fonts (Andale Mono WorldType); 2 Internal Windows Vista 8 Fonts (Calibri, Cambria); Additional font solutions available via third-party flash memory cards; HP LaserJet Fonts and iPOS Emulation available at http://www.hp.com/go/laserjetfonts
Compatible Operating Systems	Android, Linux Boss (5.0), Linux Debian (7.0, 7.1, 7.2, 7.3, 7.4, 7.5, 7.6, 7.7, 7.8, 7.9, 8.0, 8.1, 8.2, 8.3, 8.4, 8.5, 8.6), Linux Fedora (22, 23, 24), Linux Mint (17, 17.1, 17.2, 17.3, 18), Linux Red Hat Enterprise (6.0, 7.0), Linux SUSE (13.2, 42.1), Linux Ubuntu (12.04, 14.04, 15.10, 16.04, 16.10), OS macOS 10.12 Sierra, OS X 10.10 Yosemite, OS X 10.11 El Capitan, Windows 10 all 32- & 64-bit editions (excluding RT OS for Tablets), Windows 7 all 32- & 64-bit editions, Windows 8/8.1 all 32- & 64-bit editions (excluding RT OS for Tablets), Windows Vista all 32bit editions (Home Basic, Premium, Professional, etc.), Windows XP SP3 32-bit editions (XP Home, XP Pro, etc.)
Compatible Network Operating Systems	Citrix MetaFrame Presentation Server 3.0, Citrix MetaFrame XP Presentation Server (Feature Release 1, 2, and 3), Citrix on Windows Server 2003/2003R2, Citrix on Windows Server 2008/2008R2/2008 R2 SP1, Citrix on Windows Server 2012/2012R2, Citrix Presentation Server 4.0/4.5, Citrix XenApp 5.0 (Plus Feature Pack 2 & 3) for Windows Server 2008 Terminal Services 32- and 64-bit, Citrix XenApp 6.0/6.5 (for Windows Server 2008 R2 Terminal Services, 32- and 64-bit), Citrix XenApp 6.0/6.5/7.5 (for Windows Server 2008 R2 SP1 Terminal Services, 32- and 64-bit), Citrix XenApp 7.5 (for Windows Server 2012 and 2012 R2 Terminal Services, 64-bit), Citrix XenDesktop 5.6 (for Windows Server 2008 R2 Terminal Services, 32- and 64-bit), Citrix XenDesktop 5.6/7.0/7.5 (for Windows Server 2008 R2 SP1 Terminal Services, 32- and 64-bit), Citrix XenDesktop 7.0/7.5 (for Windows Server 2012 and 2012 R2 Terminal Services, 64-bit), Novell NetWare 6.5/SP8 Novell Clients www.novell.com/print, Novell Print Appliance v1.0, Novell Open Enterprise Server 11/SP1, Novell Open Enterprise Server 2 for Linux, Novell Servers www.novell.com/print, Windows Server 2003/2003 R2 32-/64-bit (SP1/SP2) Standard/Enterprise/Datacenter (+ Cluster & Terminal Services), Windows Server 2003/2003 R2 32-bit (SP1/SP2), Standard/Enterprise (+ Cluster & Terminal Services), Windows Server 2008 32-/64-bit (SP2) Standard/Enterprise (+ Cluster & Terminal Services), Windows Server 2008 R2 64-bit (SP1) Standard/Enterprise (+ Cluster & Terminal Services), Windows Server 2008/2008 R2 32-/64-bit (SP1/SP2) Standard/Enterprise/Datacenter (+ Cluster & Terminal Services), Windows Server 2012/2012 R2 64-bit Standard/Foundation/Essentials/Datacenter (+ Cluster & Terminal Services), Windows Server 2016/ 64-bit Standard/Essential/Datacenter (+ Cluster & Terminal Services)
Minimum System Requirements	PC: 2GB available hard disk space; OS hardware requirements see microsoft.com; MAC: 1.3 GB available hard drive space; Internet; OS hardware requirements see Apple.com for more info
Power	Power Supply Type: Built in 115 V or 220 V Power Supply; Power Requirements: Input voltage: 100V to 127V nominal (+/-10%), 50 - 60Hz nominal (+/- 3Hz), 12 A; Input voltage: 220V to 240V nominal, (+/-10%) 50 - 60Hz nominal (+/- 3Hz), 6 A; ²
Acoustics	Acoustic Power Emissions: 7.1 B(A); Acoustic Pressure Emissions: 57 dB(A)
Operating Environment	Operating Temperature Range: 59 to 90.5°F; Recommended Operating Temperature: 59 to 80.6°F; Storage Temperature Range: -4 to 104°F; Non-Operating Humidity Range: 10 to 90% RH; Operating Humidity Range: 10 to 80% RH; Recommended Humidity Operating Range: 30 to 70% RH
Security Management	Identity management: Kerberos authentication; LDAP authentication; 1000 user PIN codes; optional HP and 3rd party advanced authentication solutions (e.g.; badge readers); Network: IPsec/firewall with Certificate; Pre-Shared Key; and Kerberos authentication; Supports WJA-10 IPsec configuration Plug-in; 802.1X authentication (EAP-PEAP; EAP-TLS); SNMPv3; HTTPS; Certificates; Access Control List; Data: Storage Encryption; Encrypted PDF & Email (uses FIPS 140 validated cryptographic libraries from Microsoft); Secure Erase; SSL/TLS (HTTPS); Encrypted Credentials; Device: Security lock slot; USB port disablement; hardware integration pocket for security solutions; Intrusion Detection with Red Balloon Security Technology - Constant in-device monitoring for attacks; SureStart Secure Boot - BIOS Integrity Checking with self-healing capability; Whitelisting - loads only known good code (DLLs, EXEs, ...); Security management: Compatible with HP JetAdvantage Security Manager, Device Security Syslog Messages processed and accessible in Arcsight and Splunk SIEMs
Accessories	HP LaserJet 550-sheet paper feeder JB89A, HP Laser Jet 1x550-sheet paper feeder with stand and cabinet JB91A, HP LaserJet 1x550-sheet and 2,000-sheet HCl feeder and stand JB92A, HP LaserJet 3x550-sheet paper feeder with stand JB93A, HP LaserJet Envelope Feeder JB99A, HP Internal USB Ports BS128A, HP Foreign Interface Harness FWH BS131A, HP LaserJet MFP Analog Fax Accessory 500 CC487A, HP Jetdirect 2900nw Print Server JB031A, HP Jetdirect 3000w NFC/Wireless Accessory JB030A, HP Trusted Platform Module Accessory F562A, HP LaserJet Keyboard Overlay Kit for Simplified Chinese & Traditional Chinese A7W12A, HP Laser Jet Keyboard Overlay Kit Sweden A7W14A, HP 1GB DDR3 x32 144-pin 800MHz SODIMM ESX48A
HP Service and Support Options	U9NM8E - HP3yNbd+DMR LJ EntMFP E625xx MNGD HWSupp; U9NM9E - HP4yNbd+DMR LJ EntMFP E625xx MNGD HWSupp; U9NN9E - HP5yNbd+DMR LJ EntMFP E625xx MNGD HWSupp; U9NM1E - HP3yH9x5+DMR LJEntMFP E625xxMNGD HWSupp; U9NN2E - HP4yH9x5+DMR LJEntMFP E625xxMNGD HWSupp; U9NN3E - HP5yH9x5+DMR LJEntMFP E625xxMNGD HWSupp; U9NN4E - HP3yNbdChnlParts LJEntMFP E625xx MNGD SVC; U9NN5E - HP4yNbdChnlParts LJEntMFP E625xx MNGD SVC; U9NN6E - HP5yNbdChnlParts LJEntMFP E625xx MNGD SVC; U9NN7PE - HP1yPW Nbd+DMR LJEntMFP E625xxMNGD HWSupp; U9NN8PE - HP2yPW Nbd+DMR LJEntMFP E625xxMNGD HWSupp; U9NN9PE - HP1yPW4H9x5+DMR LJEntMFP E625xxMNGDHWSupp; U9NPOPE - HP2yPW4H9x5+DMR LJEntMFP E625xxMNGDHWSupp; U9NP1PE - HP1yPWChnlParts LJEntMFP E625xx MNGD SVC; U9NP2PE - HP2yPWChnlParts LJEntMFP E625xx MNGD SVC

Learn more at
hp.com

¹ Cartridges included; yields 11,000 black pages based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/learnaboutsupplies>. ² Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115 V device. ³ Average color composite (C/M/Y) and black declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/learnaboutsupplies>. ⁴ Declared yield value in accordance with ISO/IEC 19752. Actual yields vary considerably based on images printed and other factors. For more information, visit <http://www.hp.com/go/learnaboutsupplies>. ⁵ Measured using ISO/IEC 24734, excludes first set of test documents. For more information see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁶ Measured using ISO 24734 Feature Test, A5 Landscape Feed. Speed may vary based on content, PC, media orientation, and media type. ⁷ Measured using ISO/IEC 17629. For more information see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁸ Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115 V device. ⁹ Based on the BA TEC method with the following possible exceptions: 1 minute or less sleep delay setting, Wi-Fi disabled. ¹⁰ Scan speeds measured from ADF. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software. ¹¹ Scan software not included in box. HP Scan and TWAIN driver available for download. ¹² Original HP LaserJet "A" and "X" toner cartridges are also compatible with this product.

