

## BT-80-TP

BLUETOOTH-COMPATIBLE KEYBOARD WITH TOUCHPAD



iKey introduces the next innovation in Bluetooth®-

compatible, wireless industrial keyboard, the BT-80-TP.

This fully-sealed keyboard is designed to meet NEMA 4X and IP68 specifications, meaning it is resistant to dirt, dust, water, ice and corrosives. Built with an industrial silicone rubber keypad and a rugged ABS polycarbonate case, the BT-80-TP is easy to clean with disinfectants. The compact design and internal Bluetooth® module make the BT-80-TP highly portable. In addition, its red LED backlighting is ideal for nighttime or ambient-light use. It is an ideal fit for mobile, material handling, food and beverage processing, medical, and other environments where rugged flexibility is a necessity. Related: Dual connectivity keyboard with Bluetooth and USB connectivity, BT-870-TP

### Product Code BT-80-TP

CERTIFICATIONS	IP68
SHOCK	3x11 ms pulses of 50g on each of 3 axis
KEY SWITCH	MATERIAL: Industrial Silicone Rubber LIFE: Greater than 10 million cycles TRAVEL: 0.055" ACTUATION FORCE: 7.05 oz +/- 1.06 oz (200g +/- 30g) FEEDBACK: Tactile with Mechanical Snap
VIBRATION	POWER SPECTRAL DENSITY: .04g/HZ FREQUENCY RANGE:20Hz-2Khz DURATION OS TESTS PER AXIS: 3 hours
POWER	BLUETOOTH USB Rechargeable Polymer lithium-ion Battery, 3450mAh
TEMPERATURE RANGE	STORAGE: -40F to +158F (-40C to +70C) OPERATING: -4F to +140F (-20C to +60C)
WEIGHT	1.2 +/- 0.10 lbs (0.54 +/- 0.05kg)
WARRANTY	1 Year Limited Warranty
HUMIDITY	100% Humidity Resistant
DIMENSIONS	10.04" x 7.41" x .71"
MODEL NUMBERS	BT-80-TP