

GCS1934-KM

4-Port DisplayPort 1.2 KVM with Wireless Keyboard and Mouse



- DisplayPort 1.2 computer switch bundle
- Included wireless keyboard and mouse at a fantastic price
- 4K DCI Resolution Support
- Connect up to 3 monitors
- Comfortable typing experience

DisplayPort 1.2 KVM Switch with Wireless Keyboard and Mouse

IOGEAR's 4-Port DisplayPort 1.2 KVM bundle comes complete with a set of IOGEAR's state-of-the-art wireless keyboard and mouse. Streamline your 4K setup with this computer switch, IOGEAR's low-profile keyboard and touch sensor mouse. With a combination of 4K DCI resolution support, the next generation USB3.1 hub, and enhanced user-friendly operation, IOGEAR's DisplayPort 1.2 KVM Bundle provides the latest innovations in DisplayPort KVM technology and convenience in desktop setup. Your most affordable computer switching connectivity solution is ready for setup straight out-of-the-box!

• DisplayPort KVM:

- Switch between 4 computers at the push of a button
- Control 4 computers using a single keyboard, mouse, and up to 3 DisplayPort monitors
- Superior video quality – True 4K (4096x2160@60Hz)
- DisplayPort 1.2 compliant, HDCP compliant
- 2-Port USB3.1 Gen1 Hub with SuperSpeed 5Gbps transfer rate
- MST (Multi-Stream Transport)¹
- DP++ supports HDMI and DVI output²
- Switch between computers via front panel pushbuttons, hotkeys
- Independent switching of the video, USB, and audio
- Supports superior HD quality audio
- Multi-platform support – Windows®7, Windows®8.1, Windows®10, Mac®, and Linux®
- Auto Scan Mode to monitor all computers
- Power On Detection and hot pluggable
- Firmware Upgradable
- Supports keyboard and mouse emulation

- 2.4 GHz wireless- up to 33ft range
- 1000dpi resolution wireless mouse with touch pad
- Low-profile keys for quiet, comfortable typing
- Touch Mouse supports smooth horizontal and vertical animation scrolling*
- 12 multimedia hotkeys for quick access to your music, e-mail, browser and more
- Chiclet style keyboard layout
- Durable keys with a durability of 10 million cycles


¹ MST requires two monitors capable of DisplayPort 1.2 daisy chaining, or use of a powered DisplayPort MST Hub. PC Source must be DisplayPort 1.2 compliant. A DisplayPort 1.1a monitor can be the last monitor in a DP1.2 chain

² Dual-Mode DisplayPort (DP++) does not require an active adapter for most single display setups. Active DisplayPort adapters are recommended if you are unsure of the video source's DP++ compatibility

³ HD audio through DisplayPort cannot be switched independently

• Wireless Keyboard and Mouse:





Requirements

- **Console**
- DisplayPort compatible monitor
- **Computer**
- DisplayPort port
- USB Type A port
- **Wireless Keyboard and Mouse**
- Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
- Mac OS X 10.3+*

Package Contents

- 1 x 4-Port DisplayPort 1.2 KVMP
- 1 x Wireless Keyboard
- 1 x Wireless Laser Mouse
- 1 x USB RF Receiver
- 2 x DisplayPort Cables
- 2 x USB 3.0 Cables
- 4 x Audio Cables
- 1 x Power Adapter
- 1 x Manual

*Some function keys may not work with older Mac OS Systems

**Use with video adapter may change performance

Specifications

Function	GCS1934-KM
Computer Connections	
Direct	4
Port Selection	
	Pushbutton & Hotkeys
Console Connectors	
Monitor	1 x DisplayPort
Keyboard	1 x USB Type A
Mouse	1 x USB Type A
Audio	2 x 3.5mm Mini Stereo Jack (Front and Rear)
Microphone	2 x 3.5mm Mini Stereo Jack (Front and Rear)
CPU Connectors	
Monitor	4 x DisplayPort
Keyboard & Mouse	4 x USB 3.1 Gen1 Type B
Audio	4 x 3.5mm Mini Stereo Jack
Microphone	4 x 3.5mm Mini Stereo Jack
Switches	
F/W Upgrade	1 x USB Type B
Port Selection	4 x Pushbuttons
Connectors	
USB	2 x USB 3.1 Gen1 Type A
LEDs	
Mode	4 x Orange
KVM	4 x Orange

Dimensions	GCS1934-KM
Master Carton	
Width	9" (22.86cm)
Height	10" (25.4cm)
Depth	22" (55.88cm)
Master Carton Qty.	1
Weight	
Master Carton Wt.	7.76lb (17.07kg)

USB Peripherals	4 x Green
Emulation	
Keyboard	USB
Mouse	USB
Video Resolution	4096 x 2160 @ 60Hz (4K DCI)
Scan Interval	1-99 seconds (5 seconds default)
Power	
Voltage	DC 5.3V
Environment	
Operation Temperature	0-50C
Storage Temperature	-20-60C
Humidity	0-80% RH, Non-condensing
Housing	
Case	KVM: Metal; Keyboard & Mouse: Plastic
Operating System Support	Keyboard: Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Mac OS X 10.3+
Interface	Keyboard & Mouse: USB 2.0 and USB 1.1
Resolution	Mouse: 1000dpi
Radio Frequency	Keyboard & Mouse: 2.4GHz
Battery Type	Keyboard: 1 x AAA, Mouse: 1 x AA
Operating Range	Keyboard & Mouse: Up to 33ft (10m)