



6MP H.265 360° Panomorph IP Camera



O6MDP2

1.3mm panomorph lens, black housing

O6MDP2W

1.3mm panomorph lens, white housing



Features

- 360° field of view with built-in panomorph ImmerVision Enables® lens
- Supports up to 6MP resolution @ 30fps
- Adaptive IR LEDs reduce IR saturation
- Built-in standard PoE (IEEE 802.3af)
- Triple codec (H.265/H.264/MJPEG)
- Micro SD card slot (card not included)
- 2-way audio communication
- Supports dewarped output view from camera
- Sensor input and relay output
- IP67 compliant, weather resistant
- IK10 compliant, vandal resistant
- UL listed
- Conformant with ONVIF Profile S
- Included Junction Box
- 5 year warranty



Included Junction Box



Camera Specifications

Image Sensor	Progressive scan 1/1.8" CMOS, 6MP
Maximum Resolution	3072 x 2048
Minimum Illumination	F2.8, 0 lux (IR LED on)
Day/Night	IR cut filter
IR Distance	33 ft. (depending on scene reflection)
White Balance	Auto / Presets / Manual
Compensation	DWDR / BLC / HLC
Electronic Shutter Speed	1/3 - 1/100000 sec
DNR	3D

Video Specifications

Main Resolution	3072x2048 / 2048x2048 / 2048x1536 / 1600x1200 @ 30fps
Compression	H.265, H.264, MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

Network Specifications

Protocols	IPv4/v6, TCP, UDP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, UPnP, DNS
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP address filtering, digest authentication
User Access	Max. 10 simultaneous users, Actual number of users may vary depending on bandwidth

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS
Other Viewing Platforms	Apple TV and Amazon Fire TV

External Terminal Specifications

Ethernet	10/100 Mbps
Alarm	2 sensor inputs, 2 relay outputs
Audio	1 mic in, 1 line out (RCA)
Storage	Micro SD slot
Power	DC jack

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, audio detection
Alarm Triggers	Analytics & sensor input
Alarm Events	FTP upload, email upload, relay out
Image Settings	Privacy mask

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	12W
Operating Temperature	-22°F - 140°F
Operating Humidity	0% - 90% RH
Unit Dimensions	5.9" (Dia.) x 2" (H)
Unit Weight	1.3 lbs.
Certifications	FCC, UL, RoHS

Optional Accessories



ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 7/7/20