

HDMI to DVI Adapter Cable (M/M), 10 ft. (3.1 m)

MODEL NUMBER: P566-010



Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.

Description

This HDMI - DVI cable allows interconnection between digital display devices, such as HDTVs and projectors, to digital source devices, such as Set-Top boxes, DVD/DVD-R players and AV receivers. HDMI DTVs will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. HDMI technology uses a much more compact and user-friendly connector than the existing DVI connector. The HDMI specification handles higher bandwidth, uncompressed video, and multi-channel digital audio, all in one neat cable solution. (HDMI-DVI cable supports digital video only and does not support audio.)

Features

- 10-ft. (3.05 m) HDMI to DVI-D Single Link Adapter Cable
- Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and a DVI-enabled display.
- Gold plated connectors and contacts provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference
- Supports High-Definition (HD) video resolutions up to 1920 x 1080 @60Hz (1080p).

Specifications

| OVERVIEW | |
|--------------|---------------|
| UPC Code | 037332122940 |
| Product Type | Passive Cable |
| Technology | DVI; HDMI |
| VIDEO | |

Highlights

- Premium double shielded digital video cable protects against EMI/RFI noise.
- Gold plated connectors and contacts provide optimal signal transfer.
- Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p).
- Supports a bandwidth up to 5Gbps
- This product is covered by a Lifetime Limited Warranty

Package Includes

- 10-ft. (3.05 m) HDMI to DVI Gold Digital Video Cable - HDMI-M/DVI-M

| | |
|--------------------------------------|-------------------------------|
| Max Supported Video Resolution | 1920 x 1200 (1080p) |
| PHYSICAL | |
| Color | Black |
| Material of Construction | PVC |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 5.5mm |
| Wire Gauge (AWG) | 30 |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Cable Length (in.) | 120 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.33 |
| Shipping Weight (kg) | 0.15 |
| Unit Dimensions (hwd / in.) | 9.000 x 7.000 x 0.500 |
| Unit Packaging Type | Polybag |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 113°F (0° to 45°C) |
| Storage Temperature Range | 14° to 158°F (-10° to 70°C) |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| CONNECTIONS | |
| Side A - Connector 1 | HDMI (MALE) |
| Side B - Connector 1 | DVI-D SINGLE LINK (MALE) |
| Connector Plating | Gold |
| Contact Plating | Gold |
| FEATURES & SPECIFICATIONS | |
| HDCP Specification | 1.3 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty