

## VLD1A

3.6mm fixed lens, white housing



### Features

- Supports HD-TVI, AHD, HD-CVI and analog outputs
- Supports Full HD 1080p @ 30fps
- Adaptive IR LEDs reduce IR saturation
- Full OSD operation through UTC control (up the coax)
- IR Range: 98' (depending on scene reflection)
- IP67 compliant, weather resistant
- IK10 compliant, vandal resistant
- Junction box included
- UL listed
- 5 year warranty



Included Junction Box (O2VLBD)



### Camera Specifications

Image Sensor	1/2.9" CMOS, 2MP
Minimum Illumination	0.02 lux
Supported Resolution	1920 x 1080
Scanning System	Progressive
IR LEDs	12
IR Distance	98 ft. (depending on scene reflection)
White Balance	Auto / Manual
Compensation	WDR (BLC / HLC)
Day / Night	IR cut filter
DNR	3D

### Operating & Unit Specifications

Power	12VDC (power supply not included)
Power Consumption	2.6W max.
Operating Temperature	-22°F - 140°F
Operating Humidity	0% - 95% RH
Unit Dimensions	4.3" (Dia.) x 3.2" (H)
Unit Weight	1 lbs.
Certifications	FCC, UL, RoHS

### Optional Accessories



**HDCONTROLLER**  
HD Format Controller



**O2VLWM**  
Dome Wall Mount



**PSW5**  
12VDC Power Supply

<sup>1</sup> Camera is defaulted to HD-TVI. ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 9/11/17