

Low-Profile TV Wall Mount - Fixed

Product ID: FPWFXBAT



Save space while improving the appearance of your work area, with this low-profile TV wall mount. The mount sits close to the wall to support a VESA Mount compliant TV from 37" to 75", and offers anti-theft protection.

Mount your flat-screen TV or monitor in a location that's convenient for visitors, clients or employees. The wall mount safely and securely supports your TV in a fixed position, less than an inch (22 mm) from the wall, to provide a sleek, low-profile look.

It's ideal for lobbies, hallways, boardrooms, works areas, customer-facing areas or for creating digital signage. The wall mount supports most 37" to 75" (940 to 1905 mm) LED or LCD flat panel TVs weighing up to 88 lb. (40 kg).

Engineered with heavy-duty steel, the robust steel TV wall mount securely supports your flat-screen TV, to protect your investment. Ideal for areas with high traffic and minimal supervision, the TV mount features a steel bar that can be locked into place with a padlock (purchased separately) to deter theft of your equipment.

A built-in level helps to ensure your TV is aligned in a straight position on your wall, to ensure optimum viewing.

The FPWFXBAT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Securely wall-mount a TV
- Keep guests informed and entertained
- Ideal for classrooms, lecture halls or customer-facing areas

- Deter theft of your TV or monitor


Features

- Save space with this flat-screen TV wall mount for 37" to 75" TVs; Heavy-duty steel TV wall mount supports up to 40 kg (88 lb)
- Low profile TV mount sits less than 1" (only 22 mm) from the wall
- Stays in fixed position, with built-in level to ensure ideal position during installation
- Lockable bar securely holds TV and deters theft (padlock required)
- Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400, 800x400

Hardware

Warranty	5 Years
Cable Management	No
# of Displays Supported	1
Articulating	No
Mounting Options	Wall-Mount
Minimum Profile from Wall	0.9 in [22 mm]
VESA Hole Pattern(s)	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600x200 mm
	600x300 mm
	600x400 mm
	800x400 mm

Performance



Weight Capacity (Per Display)	88.4 lb [40 kg]
Minimum Display Size	37"
Maximum Display Size	75"
Video Wall	No
Fits Curved Display	Yes
Anti-theft	Yes

Physical Characteristics

Color	Black
Material	Steel
Product Length	35.4 in [89.8 cm]
Product Width	1.1 in [29.0 mm]
Product Height	17.3 in [44.0 cm]
Weight of Product	6.4 lb [2.9 kg]

Packaging Information

Package Length	38.5 in [97.8 cm]
Package Width	9.3 in [23.5 cm]
Package Height	1.9 in [49.0 mm]
Shipping (Package) Weight	8.5 lb [3.9 kg]

What's in the Box

Included in Package	wall mount
	safety bar
	adapter brackets
	level
	decorative covers



decorative cover screws

M5x14 mm screws

M6x14 mm screws

M8x50 mm screws

M6x30 mm screws

M8x30 mm screws

rectangular washers

small spacers

large spacers

screws

concrete anchors

circular washers

instruction manual

****Product appearance and specifications are subject to change without notice.***

