


## Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M) - White, 6 ft. (1.83 m)

MODEL NUMBER: N001-006-WH



Color-coded Cat5e cable connects high-speed network components like computers, servers, printers, copiers, routers, Blu-ray™ players and switches, in a home or office Cat5/5e application. Ideal for high-density data centers.

### Features

#### An Ideal Solution for High-Speed Cat5/5e Networking

- Connects high-speed network components, such as computers, servers, printers, copiers, routers, Blu-ray players and switches
- Designed for 1000Base-T, 10/100Base-T, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications
- Provides high-speed connections up to 350 MHz/1 Gbps
- Flawless signal delivery with minimal near-end crosstalk levels

#### Snagless RJ45 Male Connectors

- Molded snagless boots prevent locking tabs from damage during installation
- Connectors and cable color-coded white for easy ID in crowded rack or panel

#### Premium Construction Ensures Excellent Performance

- Manufactured from 26 AWG 4-pair stranded UTP
- Gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Durable corrosion-resistant PVC jacket
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (Cat5e draft 11)

### Highlights

- Premium cabling for Cat5/5e applications
- Rated for 350 MHz/1 Gbps communications
- Snagless RJ45 male connectors protect locking tabs from damage
- 26 AWG 4-pair stranded UTP with PVC jacket
- Color-coded white for easy ID in crowded rack or panel

### Package Includes

- N001-006-WH Cat5e 350 MHz Snagless Molded UTP Patch Cable (RJ45 M/M), White, 6 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

| OVERVIEW                           |                      |
|------------------------------------|----------------------|
| UPC Code                           | 037332204196         |
| Technology                         | Cat5/5e              |
| PHYSICAL                           |                      |
| Color                              | White                |
| Cable Shielding                    | UTP                  |
| Cable Jacket Material              | PVC                  |
| Cable Jacket Rating                | CM                   |
| Number of Conductors               | 4 Pair               |
| Conductor Material                 | Stranded Copper      |
| Conductor Gauge                    | 26 AWG               |
| Wire Gauge (OD - mm <sup>2</sup> ) | 26                   |
| Cable Length (ft.)                 | 6                    |
| Cable Length (m)                   | 1.8                  |
| Cable Length (in.)                 | 72                   |
| Cable Length (cm)                  | 182.9                |
| Shipping Dimensions (hwd / cm)     | 22.86 x 17.78 x 1.27 |
| Shipping Dimensions (hwd / in.)    | 9.00 x 7.00 x 0.50   |
| Shipping Weight (kg)               | 0.07                 |
| Shipping Weight (lbs.)             | 0.15                 |
| COMMUNICATIONS                     |                      |
| Bandwidth per TIA Standard         | 100 MHz              |
| Maximum Bandwidth as Tested        | 350 MHz              |
| Maximum Data Rate                  | 1Gbps                |
| Network Speed                      | 1Gbps                |
| CONNECTIONS                        |                      |
| Side A - Connector 1               | RJ45 (MALE)          |
| Side B - Connector 1               | RJ45 (MALE)          |
| Connector Type                     | Molded; Snagless     |
| Wiring Configuration               | EIA/TIA 568B         |
| FEATURES & SPECIFICATIONS          |                      |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                              |
|-------------------------------------|------------------------------|
| Cable Style                         | Unshielded; Molded; Snagless |
| <b>SPECIAL FEATURES</b>             |                              |
| IP68 Rated                          | No                           |
| Snagless Connector                  | Yes                          |
| Antibacterial                       | No                           |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                              |
| Certifications                      | RoHS Compliant               |
| <b>WARRANTY</b>                     |                              |
| Product Warranty Period (Worldwide) | Lifetime limited warranty    |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>