www.spracht.com

650.485.2453

650.215.7500


94303

Palo Alto, CA

974 Commercial Street, Suite 108

ZūM Maestro USB™ Headset

Wireless Headset for Softphone • DECT range up to 350' feet

















Answer your Skype and Skype for Business calls and other VoIP applications remotely...

Go Wireless!

Don't just sit there! You need to move. Just because you're using your computer for a Skype call doesn't mean you have to stay in front of your computer. Get that cup of coffee while still talking.

Eco-DECT lower emissions means the lowest power level needed to stay connected. You will really appreciate the crystal clear sound and voice quality. The noise canceling microphone screens out the noise around you so you will be heard as well as you can hear.

ZūM Maestro USB™ Softphone Headset Features:

- Compatibility: PC and Mac computers and laptops. Not compatible with smartphones.
- Wideband audio for exceptional sound quality
- · Comfortable, lightweight over-the-head wearing style
- · Volume and mute controls on headset
- Noise canceling microphone and echo cancellation
- Wireless DECT range up to 350 feet from Base Unit

- Advanced hearing protection for sudden high volume
- USB Connection from Base Unit to Computer (PC/MAC)
- Eco-DECT: Lower emissions
- Battery talk time: Up to 8 hours.
- Battery lifetime: Minimum 1000 charge cycles.
- Battery standby time: At least 36 hours.
- Battery charge time:

20% charge in less than 20 minutes.

50% charge in less than 45 minutes.

Full charge in less than 3 hours.

· Battery shelf life: headset battery holds charge for 6 months in the off state, before recharge is required.



Part HS-3010 UPC: 800807320406 \$149.00 **MSRP**

www.spracht.com

650.485.2453

<u>Ж</u>

650.215.7500

Ph:

2017 SPRACHT®

ZūM Maestro USB™ Headset

Wireless Headset for Softphone DECT range up to 350' feet



Headset

- Mic Mute
- 2 Headset Volume Up
- Noise Canceling Microphone
- 4 Headset Status LED
- 6 Multiple Function Button
- 6 Headset Volume Down





Base Back and Front

- Charging Contacts
- Page Switch
- Mic Volume UP/DOWN
- **10** USB Port
- Power Adapter Jack
- @ Headset Volume
- Online Indicator
- Audio Link Indicator
- Mute Indicator
- Battery Status



Retail Packaging Includes:

Headset and Base AC adapter for wall power **USB** Cable

Users Guide

Specifications

OPERATIONAL

Operating environment: $32^{\circ}F - 104^{\circ}F (0^{\circ}C - +40^{\circ})C$;

Humidity up to 95% Rh non-condensing.

Wireless Standard: (CAT-IQ) US DECT and European DECT. **DECT range: Range:** For US DECT, up to 350 feet from ZūM Maestro USB™ Headset to Base Unit. For European DECT, up to 120 meters from Headset Base to headset.

DECT Frequencies: US DECT 1.92-1.93 GHz EU DECT 1.88-1.90 GHz

TECHNICAL SPECIFICATIONS

Range: Up to 350' (107 meters)

Battery: 300mAh

Battery Talk Time: Up to 8 hours

Battery Lifetime: Minimum 1000 charge cycles Battery Standby Time: At least 36 hours Operating Temperature Range: -20°C to +60°C

Battery Charge Time: 20% charge in less than 20 minutes. 50% charge in less than 45 minutes. Full charge in less than 3 hours.

Battery Shelf Life: Headset battery holds charge for 6 months in the off state, before recharge is required.

Headphone/Speaker Driver Size: 30mm

Headphone Impedance: 32Ω

Headphone Frequency Response: 300-3,400Hz

Microphone: Noise-canceling Microphone

Microphone Sensitivity: -44±3dB

Microphone Signal to Noise Ratio: 58dB

Microphone Frequency Response: 100-10,000Hz

Certifications: FCC, CE

PHYSICAL SPECIFICATIONS

Height from Base with Headset: 10.5" (266.7)mm Base: 3.5"L x 4.75"H x 2.75"W (89L x 121H x 70W)mm

Weight: 5.6oz (159g)

Packaging: 7.75"L x 6.5"W x 3"H (197L x 165W x 76H)mm

Weight: 15.2oz (431g)

COMPATIBILITY

