

Contour Electrol

The Contour® Electrol® is the latest ceiling or wall-mounted electric screen offering simple installation. A variety of finishes and veneer options make this a seamless addition to any room.

This screen does not include the Tensioning Cable System. See Tensioned Contour Electrol for this feature.

Features

- Standard Silent Drive System to keep your screen whisper quiet (sizes up to 10'x10')
- Standard Low Voltage Control (LVC) to keep your screen operation flexible
- Simple Installation with a new installation kit and user-friendly packaging to keep you on schedule
- Support includes a comprehensive five-year warranty to keep you confident in your purchase
- Available with SCB-100 or SCB-200 (RS-232 serial control board) built into the case (adds 3¾" to overall length of case)
- Available with Video Projector Interface (screen trigger) built into the case (adds 3¾" to overall length of case of 220V motor version)
- Decora-style, three-button wall switch
- Standard black backing retains projected brightness
- Seamless surfaces
- Standard white powder-coated aluminum finish; available in black or veneer upon request

Optional Accessories:

- Radio Frequency Wireless Remote
- Infrared Wireless Remote
- Locking Switch Cover Plate
- Red Laser Pointers
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer



16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
45" x 80"	114 x 203	92"	234	93¾"	238
52" x 92"	132 x 234	106"	269	105¾"	269
54" x 96"	137 x 244	110"	279	109¾"	279
58" x 104"	147 x 264	119"	302	117¾"	299
65" x 116"	165 x 295	133"	338	129¾"	330
78" x 139"	198 x 353	159"	404	153¾"	391
90" x 160"	229 x 406	184"	467	173¾"	441

16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
50" x 80"	127 x 203	94"	239	93¾"	238
57½" x 92"	146 x 234	109"	277	105¾"	269
60" x 96"	152 x 244	113"	287	109¾"	279
65" x 104"	165 x 264	123"	312	117¾"	299
69" x 110"	175 x 279	130"	330	123¾"	314
72½" x 116"	184 x 295	137"	348	129¾"	330
87" x 139"	221 x 353	164"	417	153¾"	391
100" x 160"	254 x 406	189"	480	173¾"	441

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
43" x 57"	109 x 145	72"	183	69¾"	177
50" x 67"	127 x 170	84"	213	79¾"	203
60" x 80"	152 x 203	100"	254	93¾"	238
69" x 92"	175 x 234	120"	305	105¾"	269
87" x 116"	221 x 295	150"	381	129¾"	330
105" x 140"	267 x 356	180"	457	153¾"	391
120" x 160"	305 x 406	200"	508	173¾"	441

Available with the Following Screen Surfaces



Matte White
Half Angle: 60° Gain: 1.0



High Contrast Matte White
Half Angle: 50° Gain: 1.1



Video Spectra 1.5
Half Angle: 35° Gain: 1.5

Product images



White Case (Standard)



Black Case




Veneer Case


Veneer Finishes



Light Oak Veneer




Medium Oak Veneer




Natural Walnut Veneer



Heritage Walnut Veneer



Cherry Veneer



Mahogany Veneer



A BRAND OF MILESTONE AV TECHNOLOGIES | www.milestone.com
P 800.622.3737 / 574.267.8101 **F** 877.325.4832 / 574.267.7804
E info@da-lite.com

In British Columbia, Milestone AV Technologies ULC carries on business as MAVT Milestone AV Technologies ULC.

©2017 Milestone AV Technologies. DL-O441 (Rev. 4) 0717.
Da-Lite is a registered trademarks of Milestone AV Technologies. All other brand names or marks are used for identification purposes and are trademarks of their respective owners. All patents are protected under existing designations. Other patents pending.