

2-Post 12U Heavy-Duty Wall Mount Network Rack, 19" Open Frame Server Rack with Adjustable Depth, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment - Cage Nuts and Screws Included

Product ID: RK12WALLOA



This open-frame wall-mount server rack provides 12U of storage, helping you to save space and stay organized. The equipment rack features an adjustable depth and can hold a total of up to 198 lb. (90 kg).

With adjustable depth to as low as 12 in. (30.5 cm) this network rack is perfect for smaller spaces. It's easy to assemble and features wall-mounting holes that are spaced 12 and 16 in. apart, making it suitable for mounting on almost any wall, based on North American wall-frame stud-spacing standards. The wall-mount rack comes in a flat-pack, which makes it easy to transport and saves you money on shipping.

The open-frame rack adjusts from 12 to 20 in. (30.5 to 50.8 cm) to accommodate larger data, network, and telecommunication devices. The above-average depth also gives you the option to mount shelves and other accessories.

When space is limited you can mount the open-frame rack on a server room wall, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

The rack's open frame design ensures passive cooling for your rack-mounted equipment. Additionally, the open frame provides easy access to your equipment and makes it easier to configure mounted devices, which saves you time.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Mount audio/video broadcast or distribution components
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

Features

- **ADJUSTABLE DEPTH:** This 2-post 12U 19 inch open frame network rack is EIA/ECA-310 compliant and has an adjustable depth (12-20in / 30.5-50.8cm); Data rack is ideal for AV / Audio / IT / computer equipment, servers, switches, patch panels, and PDUs
- **HEAVY DUTY:** Durable rack features a vertical rail made of SPCC cold-rolled steel and a weight capacity of up to 200lbs/90kg; Its design supports unobstructed airflow to help keep your equipment cool and easy to install with access to all sides
- **EFFICIENT FLAT PACK SHIPPING:** The IT rack ships flat packed with ISTA-6 certified packaging (assembly required) to ensure hassle-free installations with complete & undamaged delivery; Comprehensive assembly instructions included
- **HARDWARE INCLUDED:** The open post wall mount server rack includes a complete set of M6 square cage nuts, M6 screws and plastic washers to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 12U wall mounted network rack is backed for 5-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	12U
Special Features	Adjustable Mounting Rails
	Easy Assembly
	U-Markings
	Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)

Industry Standards EIA/ECA-310-E

Performance

Weight Capacity 198.4 lb [90 kg]

Physical Characteristics

Color Black

Construction Material Steel

Material Steel

Product Length 20.0 in [50.8 cm]

Product Width 19.8 in [50.4 cm]

Product Height 25.2 in [64.1 cm]

Weight of Product 32.2 lb [14.6 kg]

Maximum Mounting Depth 20.0 in [50.8 cm]

Packaging Information

Flat Pack (Assembly Required) Yes

Package Quantity 1

Package Length 26.4 in [67.0 cm]

Package Width 20.9 in [53.0 cm]

Package Height 5.1 in [13.0 cm]

Shipping (Package) Weight 37.5 lb [17.0 kg]

What's in the Box

Included in Package

- 2 - Vertical Rails
- 2 - Front Horizontal Brackets
- 2 - Rear Horizontal Brackets
- 48 - M6 Cage Nuts

48 - M6 Screws

48 - Plastic Washers

16 - Assembly Screws

24 - Flat Washers

24 - Bolts

1 - User Manual

****Product appearance and specifications are subject to change without notice.***