

28" 4K Ultra HD LED Monitor

M284K 28" 4K Ultra HD LED monitor


4K



Features

- 4K resolution (3840x2160)
- 16:9 display ratio
- 2 HDMI video inputs
- 2 Displayport inputs
- Displays up to 16.7M colors
- 280 cd/m² brightness
- 3000:1 contrast ratio
- Convenient front controls for on-screen settings
- 100x100mm VESA mount compatible

ITEM		M284K
Display	Screen Size	28" (diagonal)
	Aspect Ratio	16:9
	Brightness (Typical)	280 cd/m ²
	Contrast Ratio (Typical)	3000:1
	Resolution (Max.)	3840 x 2160 @ 60Hz, Downward Compatibility
	Response Time (Typical)	5ms(G2G)
	Viewing Angle	170° / 160° (CR>10)
	Color Support	16.7M
	Filter	3D combo
Connection	HDMI 2.0 Input	x2
	DP 1.2 Input	x2
Cabinet	Front Cover	Plastic Case
	Back Case	Plastic Case
	Stand	Plastic Case
Power	Power Consumption	40W
	Type	12VDC, 5A
Features	Plug & Play	Supported
	Anti Screen Burn-In	Supported
	Remote Control	No
	Audio	5Wx2
	VESA Mount	100x100mm
Dimensions		5.40" (D) x 19.60" (H) x 27.95" (W)
Weight		12 lbs.



Optional Accessory



LCDVLW2
10" Extension Arm

The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 6/7/17