

Epson® DS-410 Document Scanner



Scanners

Documents

The affordable office document scanner with speed and compatibility.

Fast — high-quality scans up to 26 ppm/52 ipm¹; scans both sides in one pass

Unsurpassed compatibility — TWAIN and ISIS® drivers included; connect to virtually any document management software

3-year limited warranty² with world-class service and support — includes Advance Exchange with free Next-Business-Day replacement³ to minimize downtime

Reliable — Double-feed Detection and Paper Protection prevent misfeeds; peak daily duty cycle up to 3,000 sheets⁴

Scan to online storage accounts⁵ — scan to Dropbox®, Evernote®, Google Drive™, SharePoint® and more

Scan to searchable PDFs — save scanned documents as PDF files; scan and edit documents and spreadsheets with OCR software included

Easily scan stacks of documents — 50-page Auto Document Feeder

Versatile paper handling capabilities — scan folded pages up to 11" x 17" (carrier sheet required; sold separately), rigid ID cards, stacks of business cards and single sheets

Up to 30 user-programmable jobs — Epson Document Capture software automates frequent tasks

Paper Protection — efficient paper feeding system that prevents damage to documents when stapled or skewed pages are detected

Specifications

Type Sheet-fed, 1-pass duplex color scanner
Sensor Type Contact Image Sensor (CIS)
Light Source 3-color RGB LED
Optical Resolution 600 dpi
Output Resolution 50 – 1200 dpi
Color Scan Mode (output bit depth) 48-bit internal/
 24-bit external
Grayscale Scan Mode (output bit depth) 16-bit internal/
 8-bit external
Monochrome (output bit depth) 1-bit
Buttons 3 Push Buttons: Power, Start and Stop

Auto Document Feeder

Capacity: 50 sheets
 Document Size: 8.5" x 120" max., 2" x 2" min.
 Paper Weight: 50 – 210 g/m²
Scan Speed (letter size)¹
 26 ppm/52 ipm: 200 dpi Black-and-white, Color, Gray
 26 ppm/52 ipm: 300 dpi Black-and-white, Color, Gray
 21 ppm/42 ipm: 600 dpi Black-and-white
 7 ppm/14 ipm: 600 dpi Color, Gray
Connectivity Hi-Speed USB 2.0
Peak Daily Duty Cycle Up to 3,000 sheets⁴
Consumables Roller Assembly Kit: 100,000 sheets

System Requirements

Windows[®] 7, Windows 8, 8.1, Windows 10
 Mac[®] OS X[®] 10.6.x – macOS[®] 10.12.x
 Software requires Internet connection for download and installation

General

Environmental Conditions
 Temperature (operating): 41 ° to 95 °F (5 ° to 35 °C)
 Humidity: 10 – 80% (no condensation)

Power Requirements

Voltage: 100 – 240 VAC
 Frequency: 50 – 60 Hz
Power Consumption
 Operating: 15 W
 Ready: 4.1 W
 Sleep: 0.6 W
 Off: 0.2 W

Other Features

Double-feed Detection by image, Paper Protection, rigid plastic ID card scanning (including embossed cards), business card scanning, oversized folded document scanning with optional carrier sheet, 30 user-definable scan job settings, security lock (Kensington type)
Warranty 3-year limited warranty² in the U.S. and Canada
Country of Origin China
Weight and Dimensions (W x D x H)
 Product Only: 11.7" x 6.0" x 6.1", 5.5 lb
 Product in Package: 15.4" x 9.6" x 9.5", 7.8 lb

Software Included

Epson Scan 2, Document Capture Pro, ABBYY[®] FineReader[®] OCR, NewSoft[®] Presto![®] BizCard OCR, OpenText[™] Catalina ISIS
Driver Support TWAIN, ISIS

What's In The Box

DS-410, Start Here poster, Hi-Speed USB 2.0 cable, AC adapter, power cable

Eco Features

RoHS compliant
 Recyclable product⁶
 Epson America, Inc. is a SmartWay[®] Transport Partner⁷

Ordering Information

DS-410	B11B249201
Roller Assembly Kit	B12B819381
Carrier Sheets (5)	B12B819051
1-year Extended Service Plan	EPPMSCANEX1
Cleaning Kit	B12B819291

¹ Based on letter-sized scans at 300 dpi in Black-and-White, Grayscale or Color Mode. | ² For more information, go to epson.com/3yearsscannerwarranty | ³ Subject to limited warranty terms and conditions. Expedited shipping not available in all areas. Road Service orders must be in by 3 p.m. Eastern Time for Next-Business-Day delivery. | ⁴ Peak daily duty cycle is the highest recommended number of scanned sheets per day. For best results, do not exceed the peak daily duty cycle. Calculations based on a scanning speed of 26 ppm and an assumed daily use time. | ⁵ With Epson Document Capture software installed on the connected Windows PC or Mac. Internet connection required. | ⁶ For convenient and reasonable recycling options, visit www.epson.com/recycle | ⁷ SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.

See the latest innovations from Epson Business Solutions at www.epson.com/forbusiness

Better Products for a Better Future[™]
eco.epson.com



Epson America, Inc.
 3840 Kilroy Airport Way, Long Beach, CA 90806

Epson Canada Limited
 185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com
www.epson.ca

EPSON is a registered trademark, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future is a trademark of Seiko Epson Corporation. Mac, macOS and OS X are trademarks of Apple Inc., registered in the U.S. and other countries. Google Drive is a trademark of Google Inc. SharePoint and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. SmartWay is a registered trademark of the U.S. Environmental Protection Agency. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks.
 Copyright 2017 Epson America, Inc. CPD-54556 7/17

Contact: