

USB-C & USB-A Dock - Dual Monitor 4K 60Hz Dock DisplayPort + HDMI - Hybrid USB 3.0 Docking Station for USB-C or USB-A Laptops - 6x USB Type-A, GbE - USB 3.1 Gen 1 - Mac/Windows

**Product ID:** DK30A2DH



This dual-4K docking station offers wide flexibility in setting up your workstation, working with both USB-C and USB-A port laptops and supporting multiple combinations of Ultra HD 4K DisplayPort and HDMI monitors.

Ideal for highly detailed graphics applications, this dual-4K 60Hz docking station enhances your productivity by expanding the display capabilities of your laptop across two Ultra HD 4K monitors. The laptop docking station works with DisplayLink to support high-resolution monitors, enabling two full 4K 60Hz displays from a single USB connection.

With the dual-4K dock, connect:


- 2x 4K DisplayPort displays (up to 4096 x 2160p @ 60Hz)
- 2x 4K HDMI displays (up to 4096 x 2160p @ 60Hz)
- 1x 4K DisplayPort + 4K HDMI displays (up to 4096 x 2160p @ 60Hz)

The USB 3.0 docking station supports USB-C and USB-A enabled Mac and Windows laptops. This means you can connect newer USB-C or Thunderbolt 3 laptops or extend the life of legacy USB 3.0 (Type-A) laptops.

This USB-A & USB-C dock lets you transform your Mac or Windows laptop into a full workstation with six USB 3.0 (Type-A) ports, a Gigabit Ethernet port, and separate 3.5 mm audio and microphone ports for multiple audio connections, all using a single cable.

DK30A2DH is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Perfect for laptops in business, government, finance, and sales environments
- Ideal for working with graphics or data-intensive applications on your laptop

## Features

- **DUAL 4K 60Hz HYBRID USB-C & USB-A DOCK:** Universal USB 3.0 docking station (5Gbps) works with USB-C & USB-A laptops/computers; port replicator features 6-Port USB Type-A hub, Gigabit Ethernet, and 3.5mm audio jacks (headset and mic)
- **FLEXIBLE MULTI MONITOR VIDEO:** This dual 4K 60Hz universal laptop docking station can connect up to 2 monitors: Dual DisplayPort or Dual HDMI or DP + HDMI displays; supports two extended displays on MacBooks with both the Intel processor or Apple M1 chip
- **6 DOWNSTREAM USB-A PORTS:** Hybrid USB C dock has a built-in 6-port USB 3.1/3.2 Gen 1 (5Gbps) hub with USB-A ports on the front and back to support devices such as a keyboard, mouse, flash drive, external hard drive, and printer
- **FOR USB-A & USB-C LAPTOPS:** DisplayLink certified DL 6950 chipset supports USB-C/Thunderbolt 3 & USB-A PCs; USB-C & USB-A host cables incl; Supports Windows, macOS, Chrome OS, & Ubuntu; This dock does not provide USB-C Power Delivery to charge your laptop
- **STARTECH.COM ADVANTAGE:** StarTech.com offers a 3-year warranty and free lifetime technical support on all docking stations; with over 3000 products globally, StarTech.com makes hard-to-find easy.

---

### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	2

Bus Type	USB-C
	USB 3.0
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
	USB 3.0 - Backward compatible with USB 2.0/1.1
Chipset ID	DisplayLink - DL-6950
	VIA/VLI - VL813

---

### Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	Single display - DisplayPort - 5120 x 2880 @ 60Hz (using two DP ports) / 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz Single Display - HDMI - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz Dual displays - DisplayPort and HDMI - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

---

### Connector(s)

Connector Type(s)	2 - DisplayPort (20 pin) 2 - HDMI (19 pin) 1 - USB Type-C (24 pin, 5Gbps) 1 - RJ-45 6 - USB 3.2 Gen 1 USB Type-A (9 pin, 5 Gbps) 1 - 3.5 mm Mini-Jack (3 Position) 1 - 3.5 mm Mini-Jack (4 Position)
-------------------	--

---

### Software



OS Compatibility	Windows XP (32-bit), Vista, 7, 8, 8.1, 10, 11, macOS 10.6 - 10.12, 10.14 - 10.15, 11.0, 12.0, Ubuntu 18.04, 20.04, Chrome OS v55+
------------------	---

---

**Special Notes / Requirements**

System and Cable Requirements	A host laptop with an available USB-C port or a USB-A port.
Note	<p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.</p> <p>A USB-C to USB-C cable and a USB-C to USB-A cable are included.</p> <p>4K resolution is supported on both video ports. A 4K-capable DisplayPort or HDMI display is required to achieve 4Kx2K resolution</p> <p>DisplayLink docking stations and video adapters support more than one external display on Apple's M1-based Mac. Requires driver installation. Please contact StarTech.com support for a recommendation based on your specific setup.</p>

---

**Indicators**

LED Indicators	1 - Power
----------------	-----------

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1 A
Output Voltage	20V DC
Output Current	2 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	40W

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10~90% RH



---

**Physical Characteristics**

Color	Black & Silver
Material	Aluminum and Plastic
Cable Length	3.3 ft [1 m]
Product Length	8.9 in [22.6 cm]
Product Width	3.4 in [8.7 cm]
Product Height	1.1 in [2.8 cm]
Weight of Product	10.6 oz [301.0 g]

---

**Packaging Information**

Package Length	12.5 in [31.8 cm]
Package Width	5.1 in [13.0 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package) Weight	1.9 lb [0.9 kg]

---

**What's in the Box**

Included in Package	1 - docking station
	1 - 1 m USB-C to USB-A cable
	1 - 1 m USB-C to USB-C cable
	1 - universal power adapter (NA/JP, UK, EU, ANZ)
	1 - quick-start guide

---

***\*Product appearance and specifications are subject to change without notice.***

