

HP ScanJet Enterprise Flow N9120 fn2 Document Flatbed Scanner



Unbeatable speed. Unparalleled security.

The fastest, most secure A3 departmental scanner helps accelerate your business forward. Utilising high-performance features for a more productive office.^{1,2}



High-performance PC connected digital sender

- PC connected scanner through standard interface or use it as a digital sender through built-in network.
- Easily and quickly transfer scans into editable text, encrypted PDF files, and more files, using built-in OCR.

Accomplish more. Faster than ever.

- Handle large volumes at blazing speeds – up to 120 ppm/240 ipm.¹
- Manage jobs directly, using the 8-inch (20.3 cm) touch control panel with full pull-out keyboard.
- Capture every page easily – even stacks of mixed media – with HP EveryPage and an ultrasonic sensor.³
- Rely on this scanner time after time – recommended up to 12,000 pages per day.

The world's most secure scanning device²

- HP FutureSmart firmware architecture can be scaled across devices and enhanced over time with new features.
- HP OXP offers out-of-the-box or custom-built solutions for processes, such as security, accounting and more.
- Centralise control of your scanning environment with HP Web Jetadmin – and help build business efficiency.⁴
- HP High-Performance Secure Hard Disk helps keep sensitive data safe. Securely erase files.

Easily integrate workflow solutions

- Save time and simplify complex scan jobs with HP Scan.
- Define scan profiles, scan to the cloud and other destinations, and automatically enhance images.
- Embedded OCR creates searchable files that can be scanned to multiple destinations with advanced auto-imaging.
- Capture and organise documents, business cards and other files with a full suite of feature rich software.

Accessories and services

Accessories	A7W13A HP LaserJet Keyboard Overlay Kit-Danish/French-Switzerland/German-Switzerland
	A7W14A HP LaserJet Swedish Overlay Keyboard
	B5L28A HP Internal USB Ports
	B5L29A HP High-Performance Secure Hard Disk
	CZ208A HP Access Control USB Proximity Reader
	E5K48A HP 1 GB x32 144-pin (800 MHz)DDR3 SODIMM
	J8031A HP Jetdirect 2900nw Print Server
	J8J95A HP 300 ADF Roller Replacement Kit
	X3D03A HP Universal USB Proximity Card Reader
Service and support	U9TX1E HP 3 year Next Business Day with Defective Media Retention Services for ScanJet N9120fn2
	U9TX2E HP 4 year Next Business Day with Defective Media Retention Services for ScanJet N9120fn2
	U9TX3E HP 5 year Next Business Day with Defective Media Retention Services for ScanJet N9120fn2
	U9TX7PE HP 1 year Post Warranty Next Business Day with Defective Media Retention Services for ScanJet N9120fn2
	U9TX8PE HP 2 year Post Warranty Next Business Day with Defective Media Retention Services for ScanJet N9120fn2

Technical specifications

Control Panel	XGA 1024 x 768 mm LCD display; Light touch technology that supports gesture based interactions; Screen brightness-adjustment control; Home icon for quick return to the UI Home Screen; Virtual keyboard and a physical keyboard
Scanner specifications	Scanner type: Flatbed, ADF; Scan technology: Charge Coupled Device (CCD) & Contact Image Sensor (CIS); Scan input modes: Front panel applications: E-mail; Save to Network Folder; Save to USB; Save to Device Memory; Open Extensibility Platform (OXp) applications; Software scan using HP Scan Software; User application via TWAIN, ISIS, WIA or Kofax VirtualRescan (VRS) Professional drivers; Twain version: Version 2.1; Colour scanning: Yes; Output resolution dpi settings: 75; 150; 200; 300; 400; 600; Image scaling or enlargement range: 25 to 400% in 1% increments (flatbed)
Scan speed¹	Up to 120 ppm/240 ipm (black and white); Up to 120 ppm/240 ipm (colour)
Scan resolution	Optical: Up to 600 ppi; Hardware: Up to 600 ppi
Scan file format	PDF, JPEG, TIFF, MTIFF, XPS, PDF/A, TEXT (OCR), Unicode TEXT (OCR), RTF (OCR), Searchable PDF (OCR), Searchable PDF/A (OCR), HTML (OCR), CSV (OCR); Scan to easy access USB: PDF, JPEG, TIFF, MTIFF, XPS, PDF/A, TEXT (OCR), Unicode TEXT (OCR), RTF (OCR), Searchable PDF (OCR), Searchable PDF/A (OCR), HTML (OCR), CSV (OCR); For HP Scan: PDF, JPEG, PNG, BMP, TIF, Text (.txt), Rich text (.rtf), Searchable PDF (.pdf), PDF/A (.pdf); For HP Easy Scan: TIFF, PNG, JPEG, JPEG-2000, PDF, PDF-Searchable, RTF, TXT; For Linux: JPEG, PDF, PNG, PNM, PostScript, TEXT, TIFF
Scanner advanced features	Optimise text/picture; Image adjustments; Job build; Output quality setting; Selectable scan resolution 75 to 600 dpi; Auto detect colour; Edge erase; Job notification; Blank page suppression; HP Quick Sets; HP EveryPage; Auto orientation; Embedded Optical Character Recognition (OCR), Auto crop to page; Auto-tone
Grayscale Levels/Bit Depth	256/24-bit
Duty cycle	Recommended daily duty cycle: 12,000 pages
Auto document feeder capacity	Standard, 200 sheets at 75 g/m ²
Connectivity	Standard: 10/100/1000 Ethernet; 1 Hi-Speed USB Host (rear); 1 Hi-Speed USB Host (walk-up); 1 Hardware Integration Pocket (HIP) Hi-Speed USB; 1 USB-Device Port (rear); Optional: HP Jetdirect 2900nw Print Server J8031A
External I/O Ports	10/100/1000 Ethernet; 1 Hi-Speed USB Host (rear); 1 Hi-Speed USB Host (walk-up); 1 Hardware Integration Pocket (HIP) Hi-Speed USB; 1 USB-Device Port (rear)
Media Handling	
Media types	ADF: Paper (Plain, Inkjet, Inkjet Brochure/Glossy), Photo Paper; Flatbed: All ADF Media, Envelopes, Labels, Cards, Books
Media size (ADF)	A3, Ledger, B4-JIS, A4, B5-JIS, A5, B6-JIS, A6
Media weight (ADF)	45 to 199 g/m ²
Compatible operating systems	Linux Debian (7.0, 7.1, 7.2, 7.3, 7.4, 7.5, 7.6, 7.7, 7.8, 7.9, 8.0, 8.1, 8.2, 8.3, 8.4, 8.5, 8.6), Linux Fedora (22, 23, 24), Linux Mint (17, 17.1, 17.2, 17.3, 18), Linux Red Hat Enterprise (6.0, 7.0), Linux SUSE (13.2, 42.1), Linux Ubuntu (12.04, 14.04, 15.10, 16.04, 16.10), OS Mac OS 10.12 Sierra, OS X 10.11 El Capitan, OS X 10.10 Yosemite, UNIX, Windows 10 all 32/64-bit editions (excluding RT OS for Tablets), Windows 7 all 32/64-bit editions, Windows 8/8.1 all 32/64-bit editions (excluding RT OS for Tablets)
Minimum system requirements	PC: 2GB available hard disk space, OS hardware requirements see http://www.microsoft.com or 1.3 GB available hard drive space, Internet; OS hardware requirements see http://www.apple.com for more info; For HP Scan: Microsoft® Windows® 10, 8.1, 8, 7: 32/64-bit, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Microsoft® Internet Explorer, 2 GHz processor, 1024 x 768 SVGA monitor
Software Included²	HP browser, Mac OS Welcome Screen (Directs users to http://www.hp.com or OS App Source for printer software), online user manuals. Download from http://www.hp.com Network TWAIN, and USB TWAIN solution, HP Scan, ISIS, WIA, Kofax VRS Pro, Nuance PaperPort, I.R.I.S. Readiris Pro, I.R.I.S. Cardiris
Dimensions and weight	
Product dimensions (W x D x H)	Minimum: 602 x 635 x 287 mm; Maximum: 602 x 755 x 622 mm
Package dimensions (W x D x H)	794 x 577 x 765 mm
Product weight	21.4 kg
Package weight	26.47 kg
Operating environment	Temperature: 10 to 35°C Humidity: 15 to 80%RH non-condensing 10 to 35°C
Storage	Temperature: -40to 60°C
Power	Requirements: 100 to 240 VAC, 50/60 Hz, 9 A; Consumption: 21 watts (Ready), 1.2 watts (Sleep), 0.3 watt (Off); Energy star: Yes
Certifications	IEC 60950-1:2005+A1:2009+A2:2013 (International); EN60950-1:2006+A11:2009+A1:2010+A12:2011+A2:2013/+AC:2011 (EU); EN 62479:2010/IEC 62479:2010; Low Voltage Directive 2014/35/EU with CE Mark (Europe); GS Certificate (Germany, Europe); Other safety approvals as required by individual countries; Electromagnetic compatibility: CISPR 22:2008 (International) - Class A, CISPR 32:2012 (International) - Class A, EN 55032:2012 (EU) - Class A, EN 61000-3-2:2014, EN 61000-3-3:2013, EN 55024:2010, EMC Directive 2014/30/EU. Other EMC approvals as required by individual countries
What's in the box	L2763A HP ScanJet Enterprise Flow N9120 fn2 Document Scanner; Hardware install guide; HP N9120 fn2 HbrCD for Mac And PC; HP user's guide regulatory Info CD; Power cord; USB cable
Warranty	One-year Next Business Day Onsite repair warranty, phone and Web support included. Warranty may vary by country as required by law. Go to http://www.hp.com/support to learn about HP award winning service and support options in your region.

Footnotes

- ¹ Scan speeds measured from ADF. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.
- ² Based on HP review of 2016 published security features of competitive in-class printers. Only HP offers a combination of security features that can monitor to detect and automatically stop an attack then self-validate software integrity in a reboot. For a list of printers, visit <http://www.hp.com/go/PrintersThatProtect>. For more information: <http://www.hp.com/go/printersecurityclaims>.
- ³ HP EveryPage is referred to as HP Precision Feed on HP ScanJet devices introduced prior to May 2013.
- ⁴ HP Web Jetadmin is available for download at no additional charge at <http://www.hp.com/go/webjetadmin>.

Technical specifications disclaimers

- ¹ Scan speeds measured from ADF. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.
- ² Expected availability for Kofax VRS 5.1 Professional is Spring 2018.



The product could differ from the images shown. © Copyright 2017 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

