

GCS1644DPKIT

4-Port Dual-Link Dual View DVI and DisplayPort KVMP Kit (TAA Compliant)



- Switch between 4 computers on 2 monitors with the push of a button
- Offers the flexibility to mix and match computer connections: DVI and DisplayPort
- Kit includes 8 x DisplayPort to DVI Active adapters ([GDPDV14KA](#))
- Switching via pushbutton, hotkey, or mouse
- Cost effective: Plug-N-Play solution and cables are included

4-Port Dual Monitor Dual-Link DVI / DisplayPort KVM Switch

IOGEAR's DVI and DisplayPort bundle is the perfect accessory for professionals who need the flexibility of DVI and DisplayPort connections. The Dual-Link DVI and DisplayPort KVM Solution enables effortless control over 4 DVI or DisplayPort computers using a single USB keyboard, USB mouse and two monitors. This bundle is perfect for a home office or small / medium size business, as it offers the flexibility of choosing between DVI and/or DisplayPort computers. Take advantage of your existing computers, and use the included DisplayPort adapters¹ to display content from your DisplayPort enabled devices.


- Share 2 monitors, a keyboard and mouse between 4 DVI or DisplayPort computers
- Resolution
 - Dual-Link DVI resolution: (2560 x 1600)
 - 4K UHD Resolution: (3840x2160)¹
- Plug-N-Play - No software installation required
- Built-in USB 2.0 Hub
- IOGEAR's DynaSync™ technology: Remembers monitors configurations when switching²
- Computer switching via front panel pushbuttons, hotkeys, or mouse³
- 2.1 stereo sound - Full bass response and microphone support
- Complete keyboard and mouse emulation for error free booting and real-time switching
- Asynchronous hotkey switching between KVM focus, USB peripheral, and Audio ports
- Quad View (DCC Mode) - when connecting two GCS1642 units together
- Auto Scan Mode to monitor connected computers
- Supports MAC and Sun keyboards
- HDCP Compliant
- Multi OS platform support
- Firmware upgradeable
- All cables included
- Convert your DisplayPort to DVI using the included Active DisplayPort to DVI Adapters
 - Supports up to 3840x2160 @30Hz resolution based on source and monitor capabilities
 - Compatible with AMD® Radeon™ Eyefinity Graphics Processing Units (GPUs)
 - DisplayPort 1.2 and HDMI 1.4 Compliant
 - Plug-N-Play Solution, No Software or Driver installation necessary
 - Powered by DisplayPort Output- No external power adapter needed

¹Both the HDMI monitors and DisplayPort graphics card must support 4K.

²IOGEAR's DynaSync™ provides the EDID support for Windows® 7

³Mouse port switching supported alongside mouse emulation mode using a USB 3-button mouse wheel





Requirements

Package Contents

- **Console:**
 - Standard wired USB keyboard
 - Standard wired USB mouse
 - 4K Resolution: 4K enable HDMI monitor
 - **Computers:**
 - Dual-Link DVI or DisplayPort ports
 - USB Type A port
 - **Operating Systems:**
 - Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
 - Mac OS 9 to 10.x
 - Oracle® Solaris
 - Linux®, Unix and other USB supported systems*
- 1 x 2-Port Dual Monitor Dual-Link DVI KVMP Switch
 - 8 x Active DisplayPort to DVI Adapters ([GDPDVI4KA](#))
 - 2 x Dual-Link DVI-D KVM Cables
 - 2 x Dual-Link DVI-D Cables
 - 1 x Power Adapter
 - 1 x Quick Start Guide
 - 1 x Warranty Card

*Additional drivers and support may be needed

**IOGEAR's DynaSync provides the EDID support for Windows® 7

Specifications

Function	GCS1644DPKIT
Computer Connections	
Direct	4
Port Selection	Hotkeys, Pushbutton, or Mouse
Console Connectors	
Monitor	2 x Dual Link DVI-I Female
Keyboard	1 x USB Type A Female
Mouse	1 x USB Type A Female
Audio	1 x Mini Stereo Jack Female (Green)
Microphone	1 x Mini Stereo Jack Female (Pink)
CPU Connectors	
Monitor	8 x Dual Link DVI-I or DisplayPort Female
Keyboard & Mouse	4 x USB Type B Female
Audio	4 x Mini Stereo Jack Female (Green)
Microphone	4 x Mini Stereo Jack Female (Pink)
Switches	
F/W Upgrade	1 x 4-conductor 3.5mm Jack
Port Selection	5 x Pushbutton
Connectors	
USB	2 x USB Type A Female
LEDs	
Mode	1 x Orange
KVM	4 x Green
Audio	4 x Green
USB Peripherals	4 x Green
Emulation	
Keyboard	USB
Mouse	USB
Video Resolution	Single Link DVI: 1920x1200; Dual Link DVI: 2650x1600; 4K UHD: 3840x2160 (depends on source)
Scan Interval	1~99 seconds (5 seconds by default)
Power	
Voltage	DC 5.3V
Amps	2.4A
Environment	
Operation Temperature	0~50°C
Storage Temperature	-20~60°C
Humidity	0~80% RH, Non-condensing
Housing	
Case	Metal
Power Connections	1 x DC Jack

Dimensions	GCS1644DPKIT
Unit Dimensions	
Height	17" (43.18cm)
Depth	1.75" (4.45cm)
Length	6.125" (15.56cm)
Unit Package Dimensions	
Width	22" (55.88cm)
Height	9.625" (24.45cm)
Depth	8.25" (20.96cm)
Master Carton	
Width	22.625" (57.47cm)
Height	10.125" (25.72cm)
Depth	25.75" (65.41cm)
Master Carton Qty.	3
Weight	
Master Carton Wt.	49.84lb (22.66kg)
Unit Pack Wt.	15.28lb (6.95kg)
Unit Wt.	10.9lb (4.95kg)