

					
	HL-L2375DW	DCP-L2535DW	DCP-L2550DW	MFC-L2715DW	MFC-L2750DW
Key Functions	Automatic 2-sided Printing With Wireless Connectivity	Scan, Copy and Automatic 2-sided Printing with Wireless Connectivity	Scan, Copy and Automatic 2-sided Printing with Wireless Connectivity	Scan, Copy, Fax and Automatic 2-sided Printing with Wireless Connectivity	Automatic 2-sided Print, Scan, Copy and Fax with Wireless and NFC Connectivity
PRINT FUNCTIONS					
Print Speed (A4/Letter)	Up to 34ppm / 36ppm		Up to 34ppm / 36ppm		
2-sided Printing	Yes		Yes		
Print Resolution	600 x 600 dpi; HQ1,200 (2,400 x 600 dpi) quality; 1,200 x 1,200 dpi		600 x 600 dpi; HQ1,200 (2,400 x 600 dpi) quality; 1,200 x 1,200 dpi		
First Printout Time (Ready)	Less than 8.5 secs		Less than 8.5 secs		
COPY FUNCTIONS					
Copy Speed (A4/Letter)	-		Up to 34/36 cpm		
Reduction/Enlargement(%)	-	25% - 400% in 1% increments	25% - 400% in 1% increments		
Copy Resolution (Glass - Optical)	-	600 x 600 dpi	600 x 600 dpi		
Copy Features	-	N in 1	N in 1	N in 1, Auto 2-sided Copy	
SCAN FUNCTIONS					
Scanning Speed (Mono/Colour)*	-		22.5 / 7.5 ipm		
Scan Resolution	-	Optical - 1,200 x 1,200 dpi; Interpolated 19,200 x 19,200 dpi	Optical - 1,200 x 1,200 dpi; Interpolated 19,200 x 19,200 dpi		
Automatic 2-sided Scanning	-		-		Yes (Dual CIS)
Scan to Features	-	SharePoint (PC-CC4 Only), Image, OCR, File, Email	SharePoint (PC-CC4 Only), Image, OCR, File, Email, FTP		SharePoint (PC-CC4 Only), Image, OCR, File, FTP, Email, Email Server (By SST), Network
FAX FUNCTIONS					
Modem Speed	-		-	33,600bps (Fax), Super G3	
PC Fax (Send/ Receive)*	-		-	Yes / Yes (Windows only)	
Internet Fax	-		-	(ITU T.37 simple mode) - By SST	
Speed & Group Dials	-		-	200 locations / 20 Groups	
Out of Paper Reception	-		-	Up to 400 pages (ITU-T Test Chart, Standard Resolution, JBIG)	Up to 500 pages (ITU-T Test Chart, Standard Resolution, JBIG)
PAPER HANDLING					
Input Capacity	250 sheets		250 sheets		
Multi-purpose Tray	1 sheet		1 sheet		
ADF Capacity	-		50 Sheets		
Output Capacity*	150 Sheets Face Down	120 Sheets Face Down	120 Sheets Face Down		
Media Weights	60 to 230g/m² (Manual Feed Slot/ Multi-Purpose Tray)		60 to 230g/m² (Manual Feed Slot/ Multi-Purpose Tray)		
Media Size	A4, Letter, A5, A5(Long Edge), A6, Executive, Legal, Folio, Mexico Legal, India Legal		A4, Letter, A5, A5(Long Edge), A6, Executive, Legal, Folio, Mexico Legal, India Legal		
CONNECTIVITY					
Interface	Hi-Speed 2.0, 10Base-T/100Base-TX, IEEE 802.11b/g/n (Infrastructure Mode), IEEE 802.11g/n (Wi-Fi Direct)	Hi-Speed 2.0, IEEE 802.11b/g/n (Infrastructure Mode), IEEE 802.11g/n (Wi-Fi Direct)	Hi-Speed 2.0, 10Base-T/100Base-TX, IEEE 802.11b/g/n (Infrastructure Mode), IEEE 802.11g/n (Wi-Fi Direct)		
Mobile Solutions	Apple AirPrint, Mopria, Google Cloud Print, Brother iPrint&Scan		Apple AirPrint, Mopria, Google Cloud Print, Brother iPrint&Scan		
Wi-Fi Direct	Yes		Yes		
OTHERS					
Processor Speed	600MHz		600MHz		
Memory	128MB		256MB		
Emulation	PCL6	PCL6, BR-Script3, PDF Version 1.7	PCL6, BR-Script3, PDF Version 1.7		
Security Features	-		-	Secure Function Lock Version 3.0, Secure Print (Windows / Mac)	
Near-Field Connectivity (NFC)	-		-	Yes	
Display	16 characters x 1 lines	16 characters x 2 lines	16 characters x 2 lines	2.7" TFT Colour LCD	
OS Compatibility	Windows 7 SP1, 8, 8.1, 10, Server 2008, Server 2008 R2, Server 2012, Server 2012 R2, Server 2016, macOS v10.10.5, 10.11.x, 10.12.x (Download only), CUPS, LPD/LPRng (x86/x64 environment)	Windows 7 SP1, 8, 8.1, 10, Server 2008 (Network only), Server 2008 R2 (Network only), Server 2012 (Network only), Server 2012 R2 (Network only), Server 2016 (Network only), macOS v10.10.5, 10.11.x, 10.12.x (Download only), CUPS, LPD/LPRng (x86/x64 environment)	Windows 7 SP1, 8, 8.1, 10, Server 2008 (Network only), Server 2008 R2 (Network only), Server 2012 (Network only), Server 2012 R2 (Network only), Server 2016 (Network only), macOS v10.10.5, 10.11.x, 10.12.x (Download only), CUPS, LPD/LPRng (x86/x64 environment)		
Utilities & Solutions	BRAAdmin Light: Windows (by Download); BRAAdmin Pro3: Windows (by Download)		BRAAdmin Light: Windows (by Download); BRAAdmin Pro3: Windows (by Download)		
Energy Saving Mode	Energy Star		Energy Star		
Power Consumption (Printing / Sleep)	Approx. 510W / 6.0W	Approx. 475W / 6.2W	Approx. 475W / 6.2W	Approx. 475W / 6.4W	
Power Source	220-240V, AC 50/60Hz		220-240V, AC 50/60Hz		
Noise Level	LpAm = 49 dB(A)		LpAm = 49 dB(A)		
SUPPLIES					
Standard Yield Toner (TN-2460)*	Approx. 1,200 Pages		Approx. 1,200 Pages		
High Yield Toner (TN-2480)*	Approx. 3,000 Pages		Approx. 3,000 Pages		
Drum (DR-2455)	Approx. 12,000 Pages		Approx. 12,000 Pages		
Toner Save Mode	Yes		Yes		
DIMENSIONS & WEIGHT					
Dimension (W x D X H)	356 x 360 x 183 mm	410 x 398.5 x 272 mm	410 x 398.5 x 318.5 mm		
Weight	7.4kg	11.8kg	11.8kg	12kg	12.2kg

*In accordance with ISO/IEC17991
 *PC Fax Send - Windows, Mac (FaxShare Software by Brother), Linux (LPR / CUPS PC-FAX Send Driver)
 *Actual output tray capacity may vary depending on environmental conditions.
 *In accordance with ISO/IEC 19752

OPTIMISED
PRODUCTIVITY.
THE SMARTER CHOICE
FOR YOUR BUSINESS.


 Productivity


 Workflow


 Connectivity



MFC-L2750DW



DON'T JUST KEEP UP, GET AHEAD.

With top-class print speeds, enhanced mobile connectivity, and cost-saving innovations, Brother's latest range of monochrome laser printers and Multi-Function Centres are setting the pace for business productivity and cost-efficiency. Best of all, you can always count on our award-winning reliability for greater peace of mind year after year.



MFC-L2750DW

up to
34
ppm

250

50 sheets
ADF*

less than
8.5
seconds

34ppm
print speed

250 sheets
paper tray

50 sheets
ADF*

Fast first
page-out time*

Productivity that goes **beyond performance**

Outstanding print speeds

Don't let mediocre print speeds slow you down. With stellar print performance of up to 34ppm, and fast warm-up and first-page-out times, you can take your office productivity to new heights.

Impressive mono print quality

Create impactful, professional-looking documents with crisp text and graphics at high quality resolution.

Lighten your load with advanced paper handling

With a 250 sheets default paper tray, a 50 sheets Auto Document Feeder*, and the ability to handle a variety of papers up to 230g/m²*, you can now do more with less effort.



Enhanced **wireless and mobile connectivity**



Wireless printing made easy

Print or scan effortlessly from your notebook PC, smartphone, or tablet without the need for wires. Brother wireless-enabled machines* allow you to effortlessly connect your wireless devices for fuss-free printing of documents, presentations and emails.



Print directly from your mobile devices

In today's on-the-go business environment, an increasing number of users are printing from their mobile devices. Through Brother's iPrint&Scan, Apple Airprint, Mopria and Google Cloud Print, you can now print directly from your iPhone, iPad, Android™ or Windows® Mobile device.



Scan and print without network access

Brother machines with Wi-Fi Direct* enable you to print or scan directly from your mobile device without access to your network. This allows you to offer temporary printing or scanning access to your visitors.

Designed with **cost-savings in mind**

Lower the total cost of ownership with high-yield cartridges

Enjoy greater print volumes at lower costs-per-page with high-yield 3,000-page replacement toner cartridges*.

Automatically cut your paper waste by 50%

Brother machines with automatic 2-sided printing allow you to set all print jobs to print on both sides of the document unless otherwise stated, cutting down on paper wastage by half.

Cut down on your toner costs

Toner replacements are by far the most costly supplies in any print environment. The Toner Save Mode on selected Brother machines give you the option to print using less toner, while producing clear and legible text at the same time.

Fit more, save more

Brother machines with the N in 1 feature allow you to print multiple pages of your document into one single page, saving up to 93% in paper waste. What's more, Booklet Printing helps you create convenient booklets that use 50% less paper.

A proud legacy of **uncompromising reliability**

Over a hundred years of customer satisfaction

Even with over a century of customer satisfaction under our belt, we aren't taking anything for granted. All Brother machines have undergone rigorous tests and trials to ensure that they will last for years to come. By bringing together traditional Japanese values of quality, service, and integrity with the latest in technological innovation, you can always count on Brother to take your office productivity further.

An award-winning track record

For 4 years in a row, Brother has won PCmag's prestigious Business Choice Award. We have also won PCmag's Readers' Choice Award for an unprecedented 8 years in a row, scoring the highest in overall satisfaction and reliability.

We've got your back

At Brother, our commitment to our customers comes first, which is why we remain dedicated to you far beyond the purchase dates of our products. This is reflected in the outstanding service and warranty that you will enjoy with every Brother product.



NFC Reader

2.7" Touch Screen Display

50 sheets Automatic Document Feeder

Mobile and Cloud Printing Capabilities

Built in Ethernet and wireless networking

Automatic 2-sided features

Up to 34ppm

250 sheets Paper Tray

MFC-L2750DW



One-stop centre for free downloadable templates



Brother strongly recommends the use of genuine Brother consumable products only. Benefits include better quality print, greater yields per consumable, protection of your machine from damages and achievement of optimum performance. As a precaution, please note that your machine warranty may not cover any damages arising from the use of non-genuine consumables.

Microsoft, Windows, the Windows logo and/or other Microsoft products referenced herein are either registered trademarks of Microsoft Corporation in the U.S. and/or other countries. Brother and its logo are trademarks of Brother Industries Ltd., Japan. All specifications are subject to change without notice. All registered trademarks referenced herein are the property of their respective companies. Brother International Corporation, Japan.

www.brother.com.sg

*Applicable to selected models *Print from multi-purpose tray or manual feed slot *Requires additional purchase