



CSP600WSURC2 | PROFESSIONAL SURGE PROTECTOR

Protect home and office computers, electronics, and home theater equipment

The CyberPower Professional Series CSP600WSURC2 Surge Protector is ideal for Home/Office protection with 1,200 joules, 6 swivel outlets, 2 USB charge ports (2.4 Amps shared), and a convenient wall-tap design. The surge protector is ideal for protecting personal computers, phones/fax/modems, printers, stereos, and other electronics. Its two USB are perfect for keeping tablets, smart phones, and other rechargeable electronics ready to use.

The CSP600WSURC2 features six outlets, wall-tap plug, MOV technology to guard the surge protector and connected electronics against line abnormalities and lightning surges, while EMI/RFI filters block unwanted line noise. This surge protector comes with a 1-Year Limited Warranty and a \$75,000 Connected Equipment Guarantee.



TYPICAL APPLICATIONS

- Mobile Devices
- Personal Electronics
- Cell Phones
- Personal Computers

FEATURES

- Surge suppression: 1200 J
- Volts: 125 V
- Plug type: NEMA 5-15P
- Outlet type: 6 NEMA 5-15R
- USB charge ports: 2 (2.4A shared)
- EMI/RFI Filtration: Yes
- LED indicators: Yes
- Warranty: 1-Year Limited
- Connected Equipment Guarantee: \$75,000

SPECIFICATIONS

INPUT	
Circuit Breaker	None
Cord Length	Wall-tap
Input Plug Type	NEMA 5-15P
Maximum Input Current	15 A
Plug Style	Wall-tap
OUTPUT	
Outlet Type	6 - NEMA 5-15R
Outlets - Total	6
USB Charge Port	Yes
USB Charge Port Amperage	2.4 A (Shared)
USB Charge Port Quantity	2
USB Charge Port Type	Type A
USB Charge Port Voltage	5 VDC

SURGE PROTECTION & FILTERING	
Attenuation	32 dB
Clamping Voltage	800V (H-N)
Coax Protection RG6	None
EMI/RFI Filtration	150 KHz 100 MHz Yes
Maximum Surge Current	60,000 A
Maximum Surge Current H-G	15,000 A
Maximum Surge Current H-N	30,000 A
Maximum Surge Current N-G	15,000 A
Maximum Surge Voltage	6,000 V
Response Time	<1 Nanosecond
Surge Suppression (Joules)	1,200 J

CSP600WSURC2

PROFESSIONAL SURGE PROTECTOR

SPECIFICATIONS CONT.

PHYSICAL

Color	White
Form Factors Supported	Direct Plug
Material of Construction	Plastic

PHYSICAL DIMENSIONS

Physical Dimensions - Width/Height/Depth (cm)	10.21 x 14.71 x 5.59 cm
Physical Dimensions - Width/Height/Depth (mm)	102 x 147 x 56 mm
Physical Dimensions - Width/Height/Depth (in.)	4.02 x 5.79 x 2.2 in.
Weight (kg)	0.24 kg
Weight (lb)	0.53 lbs.

SHIPPING DIMENSIONS

Shipping Dimensions - Width/Height/Depth (cm)	22.53 x 6.35 x 11.43 cm
Shipping Dimensions - Width/Height/Depth (mm)	225.3 x 63.5 x 114.3 mm
Shipping Dimensions - Width/Height/Depth (in)	8.87 x 2.5 x 4.5 in.
Weight (kg)	0.38 kg
Weight (lb)	0.83 lbs.

CERTIFICATIONS

Environmental	RoHS Compliant
Safety	UL1449 3rd Edition UL498A

WARRANTY

CEG Amount	\$75,000
Connected Equipment Guarantee	Lifetime
Product Warranty	1-Year Limited Warranty