

1U 19" Rack Mount Light Panel - Dimmable LED - Flexible Gooseneck Arms - Server Cabinet Light - Data Center/IT Network Enclosure Rackmount Lighting Bar w/Power Adapter & 5ft Cable

Product ID: RKPNTLLT



This 1U rack-mount light panel installs into any EIA-310 compliant cabinet and enables you to complete tasks inside your server rack that require lighting. The panel mounts into 1U of rack space in any standard 19 in. rack and features two adjustable gooseneck lights, each 17 in. (432 mm) in length. For easy installation, the light panel also includes a 5 ft. (1.5 m) power cord that can easily reach a PDU that's mounted inside of your rack.

This rack-mount light enables you to direct light exactly where you need it. The lamp features two easy-to-adjust lights that can be positioned independently with flexible gooseneck arms. You can also direct the lights so they'll work together, to intensify the light in a specific location.

The gooseneck design provides virtually limitless movement and easily bends 360 degrees in any direction. The lights tilt, turn and rotate, so you can instantly switch from any position, and back again.

For simple operation, the rack-mount light features a dimming dial, which makes it easy for you to adjust the light to the perfect settings. Unlike some rack-mount lighting systems that require you to physically disconnect the power cable in order to turn them off, this LED rack light features a built-in on/off switch.

The 1U rack light features LED lights which are long lasting and emit very little heat, unlike some systems that use incandescent lighting. With this rack-mount light, you can be confident your equipment won't overheat due to residual heat generated from your lighting.

The RKPNTLLT is backed by a 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Install into your server rack to easily see equipment

- Ideal for multimedia cabinets in dark settings

Features

- Direct light exactly where you need it with two easy-to-adjust lights on independent gooseneck arms
- Get perfect illumination with a dimming dial that adjusts the intensity of both lights
- Save energy and be confident that your equipment won't overheat, with LED lights
- Features an on/off switch making it easy to control
- Installs into only 1U of space

Hardware

Warranty	2 Years
U Height	1U
Industry Standards	EIA-310-D


Performance

General Specifications	Direct Light Intensity: 42 Lumens
	Diffused Light Intensity: 21 Lumens
Maximum Arm Extension	17.0 in [43.2 cm]

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.25 A
Output Voltage	12V DC
Output Current	0.5 A
Center Tip Polarity	Positive
Power Consumption (In Watts)	6

Physical Characteristics



Material	Steel
Product Length	19.0 in [48.3 cm]
Product Width	1.8 in [45 mm]
Product Height	1.7 in [44 mm]
Weight of Product	26.5 oz [750 g]

Packaging Information

Package Length	19.3 in [49 cm]
Package Width	4.3 in [11 cm]
Package Height	3.9 in [100 mm]
Shipping (Package) Weight	25.1 oz [710 g]

What's in the Box

Included in Package	light panel
	M5 cage nuts
	M5 screws
	universal power adapter (NA/JP, UK, EU, ANZ)

****Product appearance and specifications are subject to change without notice.***

