

# HP EliteDisplay E273q 68.58 cm (27") Monitor



## Uninterrupted multi-display multi-tasking in stunning Quad HD

Style meets substance in the strikingly modern HP EliteDisplay E273q 68.58 cm (27") QHD Monitor, a Quad HD display crafted for optimal viewing, productivity, and ergonomics with a 3-sided micro-edge bezel for seamless multi-display tiling, flexible USB-C™<sub>2</sub> connectivity, and 4-way adjustable comfort.



### A whole world view of all your work

- Bring more of your data to the screen at the same time on a massive 68.58 cm (27") diagonal screen with Quad HD 2560 x 1440 resolution<sup>3</sup>, which supports efficient column and row management in your office software and smoother curves in your images.

### Drive your productivity to the edge

- Take visual disruptions out of the picture with the display's 3-sided micro-edge bezel, which essentially removes them from your line of sight so you can multi-task to your heart's content across virtually seamless multi-display arrays.<sup>1</sup>

### Work comfortably

- Find your most comfortable, productive position with adjustable tilt, height, swivel, and up to 150 mm height adjustment settings. Use pivot rotation to customize portrait or landscape views when using multiple displays.<sup>1</sup>

### Expanded, flexible connectivity

- Keep your workspace clean with video and data connections over a single cable with USB-C™<sub>2</sub>. Be ready for multiple generations of products with DisplayPort™, HDMI, VGA, and a 2-port USB hub.

### Featuring

- Mount your compatible HP Desktop Mini PC or select Thin Client or Chromebox directly on the column stand using the optional HP B300 PC Mounting Bracket.<sup>4</sup>
- Reduce power consumption and help lower costs with a low halogen, ENERGY STAR® certified, EPEAT® Gold registered<sup>6</sup> display that meets TCO Certified Edge with 85% Post-Consumer Recycled plastics.<sup>5</sup>
- Design the screen for how you work with HP Display Assistant software, which enables screen partitioning and helps deter theft by dimming a display that's disconnected without approval.
- Build a complete solution with optional HP accessories designed and tested to work with your display.<sup>7</sup>

# HP EliteDisplay E273q 68.58 cm (27") Monitor Specifications Table



<b>Product Number</b>	1FH52AA;1FH52AT;1FH52AS
<b>Product Color</b>	Black
<b>Display size (diagonal)</b>	68.58 cm (27")
<b>Display Type</b>	IPS w/LED backlight
<b>Panel Active Area</b>	59.6 x 33.5 cm;
<b>Viewing Angle</b>	178° horizontal; 178° vertical
<b>Brightness</b>	350 cd/m <sup>2</sup> 1
<b>Contrast Ratio</b>	1000:1 static; 5000000:1 dynamic1
<b>Response Ratio</b>	5 ms on/off1
<b>Aspect Ratio</b>	16:9
<b>Native Resolution</b>	QHD (2560 x 1440 @ 60 Hz)
<b>Resolutions Supported</b>	2560 x 1440; 1920 x 1200; 1920 x 1080; 1680 x 1050; 1600 x 900; 1440 x 900; 1280 x 1024; 1280 x 800; 1280 x 720; 1024 x 768; 800 x 600; 720 x 400; 640 x 480
<b>Display Features</b>	Anti-glare; In plane switching; Language selection; LED Backlights; On-screen controls; Pivot rotation; Plug and Play; User programmable; Anti-static
<b>User Controls</b>	Brightness; Color Control; Contrast; Exit; Image Control; Information; Input Control; Language; Management; Menu; OK; Power
<b>Input signal</b>	1 VGA; 1 HDMI; 1 DisplayPort™ 1.2 with HDCP support
<b>Ports and Connectors</b>	2 USB 3.0; 1 USB Type-C™ (upstream, power delivery up to 15 W)1
<b>Input power</b>	Input voltage: 100 to 240 VAC
<b>Power consumption</b>	Energy Efficiency Class: B; Panel Active Area: 59.6 x 33.5 cm; On-mode power consumption: 39 W; Annual energy consumption: 57 kWh; Power consumption (standby): 0.5 W; Power consumption (off-mode): 0.3 W; Power consumption Description: 75 W (maximum), 45 W (typical), 0.5 W (standby); Screen resolution: QHD (2560 x 1440 @ 60 Hz)
<b>Dimensions with Stand (W x D x H)</b>	61.2 x 21.4 x 52.3 cm
<b>Dimensions without Stand (W x D x H)</b>	61.2 x 4.9 x 36.4 cm
<b>Weight</b>	7.4 kg (With stand)
<b>Ergonomic features</b>	Tilt: -5 to +22° ; Swivel: 45° ± 2° ; Pivot rotation: 90° ; Height: 150 mm
<b>Certification and Compliance</b>	BSMI; CB; CCC; CE; CEL; CECP; FCC; ICE; ISC; ISO 9241-307; PSB; TUV-S; VCCI; WEEE; RCM; TUV-GS; EAC; Vietnam MEPS; Australian-New Zealand MEPS; SmartWay Transport Partnership - NA only; Microsoft WHQL Certification (Windows 10, Windows 8.1 and Windows 7); cTUVus; Mexico CoC; MSIP
<b>Environmental</b>	Arsenic-free display glass; Mercury-free display backlights; Low halogen <sup>2</sup>
<b>Energy Efficiency Compliance</b>	ENERGY STAR® certified; EPEAT® Gold
<b>What's in the box</b>	AC power cord; DisplayPort™ 1.2 cable; Documentation; HDMI cable; USB Type-C™ to A cable
<b>Warranty</b>	5 years Next Business Day Onsite Support. HP support includes HP 3-year limited warranty plus a 5-year HP Onsite Care Pack support, as of date of purchase of the hardware product. Onsite support is offered if the problem cannot be handled over the phone. Delivery of support services outside of the applicable HP coverage areas may be subject to longer response times.

## HP EliteDisplay E273q 68.58 cm (27") Monitor

### Accessories and services (not included)

---

#### HP B300 PC Mounting Bracket



Customize an altogether better solution with the HP B300 PC Mounting Bracket, which lets you attach your HP Workstation, HP Desktop Mini, HP Chromebox or select HP Thin Client directly behind select 2017 and 2018 HP EliteDisplays and HP Z Displays.<sup>1</sup>

**Product number: 2DW53AA**

#### HP Business PC Security Lock v2 Kit



Help prevent chassis tampering and secure your PC and display in workspaces and public areas with the HP Business PC Security Lock v2 Kit.

**Product number: N3R93AA**

---

## HP EliteDisplay E273q 68.58 cm (27") Monitor

### Messaging Footnotes

<sup>1</sup> Each display sold separately.

<sup>2</sup> Only supports USB-C™ DisplayPort Alt mode and no power delivery is enabled.

<sup>3</sup> All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

<sup>4</sup> HP Desktop Mini PC, Thin Client, and Chromebox sold separately and require the HP B300 PC Mounting Bracket, also sold separately. See display QuickSpecs for product compatibility.

<sup>5</sup> External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

<sup>6</sup> EPEAT® registered where applicable. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status in your country. Search keyword generator on HP's 3rd party option store for solar generator accessories at [www.hp.com/go/options](http://www.hp.com/go/options).

<sup>7</sup> Each sold separately.

### Technical specifications disclaimers

<sup>1</sup> All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

<sup>2</sup> External power supplies; power cords; cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

### Sign up for updates

[www.hp.com/go/getupdated](http://www.hp.com/go/getupdated)

---

© Copyright 2018 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. EPEAT® registered where applicable. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status by country. See HP's 3rd party option store for solar energy accessory at [www.hp.com/go/options](http://www.hp.com/go/options) ENERGY STAR® and the ENERGY STAR® mark are registered trademarks of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries.

