



AOC Monitors
IPS LED monitor

IPS Monitor
27", 1920 x 1080

C2789FH8

An Explosion of Beauty and Colors

The C2789FH8 offers great image quality at 1920 x 1080 Full HD resolution, while providing features and connectivity that benefits you. The 27-inch monitor features an IPS panel that gives wide-viewing angles for color uniformity. Slim in design with extra narrow bezel while offering vibrant images with 50M:1 contrast ratio, the C2789FH also has all the connectivity you need for high quality digital video and audio.

Key Features

- 27" viewable image with Full HD 1920 x 1080 resolution
- 1800R curved panel for immersive experience
- IPS panel for wide-viewing angles and color uniformity
- AMD FreeSync Technology
- VGA and HDMI connectivity
- Ultra Slim Design (7.5 mm)
- AOC SuperColor Technology
- ClearVision Technology
- FlickerFree





VA Panel for Wide Viewing Angles

Born to be the perfect supermodel. IPS panels have the best color uniformity at any viewing angle, such as a perfect supermodel without flaws.



True-to-Life Colors

AOC's SuperColor Technology allows for a wider color gamut, meaning the color spectrum has been enhanced to allow true-to-life colors. The larger the color gamut, the more colors that can be displayed, creating unbelievably vivid images.



AOC ClearVision Technology and Flicker Free

ClearVision image performance engine upscales Standard Definition (SD) sources to High Definition (HD) for sharper, more vivid viewing. Flicker free technology uses DC (Direct Current) backlight system rather than PWM (Pulse Width Modulation) to provide more comfort and wellbeing for your eyes.



**Flicker
FREE**

C2789FH8 Specification

Cabinet Color	White/Gold
Panel	TFT Active Matrix LCD, LED Backlight, IPS Panel 27" Class Widescreen, 16:9 Aspect Ratio 27" Viewable Image Size, Diagonal
Pixel Pitch	0.3114(H)mm x 0.3114(V)mm
Display Area	597.88(H)mm x 336.31(V) mm
Brightness	250 cd/m ²
Contrast Ratio	50M:1
Response Time	4ms (OD)
Viewing Angle	Horizontal: 178 Degrees (CR>10) Vertical: 178 Degrees (CR>10)
Scanning Frequency	Horizontal: 30K~83KHz Vertical: 50~76 Hz
Optimal Resolution Recommended	1920x1080@60Hz 1920x1080@60Hz
Supported Resolutions	800x600@56/60/72/75Hz 832x642@75Hz 1024x768@60/70/75Hz 1280x1024@60/75Hz 1280x720@60Hz 1280x960@60Hz 1440x900@60Hz 1680x1050@60Hz 1920x1080@60Hz
Color Depth	16.7M colors
Connectors	1 x VGA, 1 x HDMI
User Control	Source/Auto/Exit, Clear Vision, Menu/Enter, Image Ratio/Volume,Power
Adjustability	Tilt: -3.5°~+21.5°
Power Source	Universal 110~240VAC, 50/60Hz
Power Consumption	30W (typical), Standby: <0.5W,
Regulations	CTUVus, CE, FCC, RoHS, Windows 10 compatible
Other Features	NTSC 90%, Free-Sync. OSD Menu, Kensington Security Slot, AOC's eSaver software, i-Menu software
Dimensions (WxHxD mm)	Monitor: 612.75x452.11x179.94 Carton:715x 527x172
Dimensions (WxHxD inches)	Monitor: 24.12x17.80x7.08Carton: 28.15 x20.75x6.77
Weight (Net)	8.73lbs/3.96Kgs
Weight (Gross)	12.78lbs/5.8Kgs
Loading Qty w/pallet	20'=416pcs; 40' Std=832pcs
UPC Code	685417717088
What's in the Box	27" Curved Monitor, Power Cord, Power Adapter, HDMI Cable, QSG.

1. Wall mount arm & bracket not included. Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. AOC shall not be liable for technical or editorial errors or omissions contained herein. All other trade marks are property of their respective owners. For more information, visit us.aoc.com or call 888-838-6388