Boardroom Electrol

The Boardroom Electrol® is a value-engineered, ceiling recessed screen with a wooden housing. This screen requires the extra step of trim work post installation. Closure doors are not painted, and feature a brushed aluminum finish.

The Boardroom Electrol does not include the ceiling trim flange or painted automatic closure door. See Advantage Electrol for easy installation or Advantage Deluxe Electrol for easy installation and the aesthetic of the white automatic closure door.



Features

- Ceiling closure for concealing screen when not in use
- Available with silent motor option
- Decora-style, three-position wall switch
- Standard black backing retains projected brightness
- Black painted case

Optional Accessories:

- Single Motor Low Voltage Control System
- Radio Frequency Wireless Remote - Single Motor LVC
- Infrared Wireless Remote - Single Motor LVC
- Video Projector Interface
- SCB-100
- Key Operated, 110 Volt Switch
- Locking Switch Cover Plate
- Dual Motor Low Voltage Control System
- Radio Frequency Wireless Remote - Dual Motor LVC
- Infrared Wireless Remote - Dual Motor LVC
- Red Laser Pointers
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer

16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
45" x 80"	114 x 203	92"	234	97½"	248
52" x 92"	132 x 234	106"	269	109½"	278
54" x 96"	137 x 244	110"	279	113½"	288
58" x 104"	147 x 264	119"	302	121½"	309
65" x 116"	165 x 295	133"	338	133½"	339
78" x 139"	198 x 353	159"	404	157½"	400
90" x 160"	229 x 406	184"	467	177½"	451

16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
50" x 80"	127 x 203	94"	239	97½"	248
57½" x 92"	146 x 234	109"	277	109½"	278
60" x 96"	152 x 244	113"	287	113½"	288
65" x 104"	165 x 264	123"	312	121½"	309
69" x 110"	175 x 279	130"	330	127½"	324
72½" x 116"	184 x 295	137"	348	133½"	339
87" x 139"	221 x 353	164"	417	157½"	400
100" x 160"	254 x 406	189"	480	177½"	451

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
43" x 57"	109 x 145	72"	183	73½"	187
50" x 67"	127 x 170	84"	213	83½"	212
60" x 80"	152 x 203	100"	254	97½"	248
69" x 92"	175 x 234	120"	305	109½"	278
87" x 116"	221 x 295	150"	381	133½"	339
105" x 140"	267 x 356	180"	457	157½"	400
120" x 160"	305 x 406	200"	508	177½"	441

Available with the Following Screen Surfaces



Matte White
Half Angle: 60º Gain: 1.0



Video Spectra 1.5
Half Angle: 35º Gain: 1.5

A BRAND OF MILESTONE AV TECHNOLOGIES | www.milestone.com
P 800.622.3737 / 574.267.8101 **F** 877.325.4832 / 574.267.7804
E info@da-lite.com

In British Columbia, Milestone AV Technologies ULC carries on business as MAVT Milestone AV Technologies ULC.

©2017 Milestone AV Technologies. DL-0428 (Rev. 1) 01.17.
Da-Lite is a registered trademarks of Milestone AV Technologies. All other brand names or marks are used for identification purposes and are trademarks of their respective owners. All patents are protected under existing designations. Other patents pending.