

## Compact Black & White Laser All-in-One

MFC-L2750DW **XL**



**The Brother MFC-L2750DW XL delivers full featured performance for busy home or small offices.**

- Up to 2 Years of toner in-box<sup>o</sup>
- Approx. 7,500 pages included<sup>~</sup> with 1 high-yield and 1 super high-yield toner
- Up to 50-sheet automatic document feeder offers multi-page copy, scan & fax
- Engineered for increased efficiency with fast print speeds of up to 36 ppm
- Helps save time with single-pass duplex (2-sided) copying and scanning
- Print-from and scan-to popular cloud services directly from the 2.7" color touchscreen<sup>v</sup>
- No network setup needed for NFC one "touch to connect" printing and scanning<sup>~</sup>
- Print wirelessly from your desktop, laptop, smartphone and tablet<sup>□</sup>

# MFC-L2750DW XL

## Specifications:

<b>Print Technology</b>	Electrophotographic Laser
<b>LCD Display (type/size)</b>	2.7" Color TouchScreen
<b>Paper Size (maximum)</b>	Paper Tray: Up to 8.5" x 14" (legal) Manual Feed Slot: 3" to 8.5" (W), 5" to 14" (L)
<b>Print Speed (maximum)</b>	Up to 36ppm
<b>Print Resolution (maximum)</b>	Up to 2400 x 600 dpi
<b>Emulations</b>	PCL6, BR-Script3±
<b>Memory (std./max.)</b>	256MB / 256MB
<b>Duplex Printing Capability</b>	Yes
<b>Paper Input Capacity (maximum)<sup>∞</sup></b>	250-sheet capacity paper tray, plus a single-sheet manual feed slot
<b>Output Capacity (maximum)<sup>∞</sup></b>	100 sheets (face down), 1 sheet (face up)
<b>Auto Document Feeder<sup>∞</sup></b>	Up to 50 pages
<b>Standard Interfaces</b>	Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0
<b>Copy Speed (maximum)</b>	Up to 36cpm
<b>Automatic Duplex Scan/Copy</b>	Yes
<b>Copy Resolution (maximum)</b>	600 x 600 dpi
<b>Copy Reduction/Enlargement</b>	25% - 400% in 1% increments
<b>Copy Options</b>	Sorting, N-in-1, Multi-copying (up to 99), ID copy
<b>Scanner Type</b>	Color Flatbed with ADF
<b>Document Glass Size</b>	8.5" x 11" (letter)
<b>Scan Resolution (maximum)</b>	Optical: Up to 1200 x 1200 dpi <sup>4</sup> Interpolated: Up to 19200 x 19200 dpi
<b>Scan To Capability</b>	File, Image, E-mail, OCR, FTP, Microsoft® SharePoint®, Cloud (Web Connect™)
<b>Web Connect<sup>∨</sup></b>	DROPBOX, GOOGLE DRIVE™, EVERNOTE®, ONEDRIVE, ONENOTE, BOX
<b>Brother Cloud Apps<sup>♣</sup></b>	Office Print, Easy Scan to E-mail, Scan to mobile
<b>Document Viewer / OCR Software</b>	Nuance™ PaperPort™ 14SE w/ OCR for Windows® (by download)
<b>Fax Modem</b>	33.6K bps
<b>Fax Page Memory (maximum)</b>	Up to 500 pages <sup>2</sup>
<b>Speed Dial Locations</b>	200
<b>PC Fax Capability<sup>3</sup></b>	Yes
<b>Operating Systems Compatibility<sup>o</sup></b>	Windows® 8.1, 8, 7 / Windows® 10 Home / 10 Pro / 10 Education / 10 Enterprise; Windows Server® 2016 / 2012 R2 / 2012 / 2008 R2 / 2008; Mac® OS X® v10.10.5, 10.11.x, 10.12.x, 10.13.x; Linux
<b>Mobile Device Compatibility<sup>□</sup></b>	AirPrint®, Google Cloud Print™, Brother iPrint&Scan, Wi-Fi Direct®
<b>Maximum Monthly Duty Cycle<sup>o</sup></b>	Up to 15,000 pages/month
<b>Recommended Monthly Volume<sup>*</sup></b>	Up to 2,000 pages/month
<b>Warranty</b>	2-year limited warranty

± PostScript®3™ compatible.

\* Additional purchase required.

∞ Maximum capacity based on using 20 lb. paper.

<sup>2</sup> Using ITU-T Test Chart #1 with JBIG coding and std. resolution.

<sup>3</sup> PC Fax Receive not available for Mac users. B&W only.

<sup>4</sup> Max. dpi from glass; max 600x600 dpi from ADF

<sup>o</sup> Server 2003 / 2008 / 2012 network printing only

<sup>□</sup> Requires connection to a wireless network. See [www.brother.com](http://www.brother.com) for details, availability, and mobile device compatibility.

<sup>o</sup> Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

\* The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the

## Supplies & Accessories\*:

### Supplies & Accessories\*:

TN-730	Standard Yield Toner (approx. 1,200 pages) <sup>▼</sup>
TN-760	High-Yield Toner (approx. 3,000 pages) <sup>▼</sup>
TN-770	Super High-Yield Toner (approx. 4,500 pages) <sup>▼</sup>
DR-730	Drum Unit (approx. 12,000 pages) <sup>^</sup>
BP60MPLTR	Letter-size Multi Purpose Paper (500 sheets)



At your side support. Online, call or live chat – Brother provides FREE technical support for the life of your product. At Brother, we want to ensure that your experience with us is exceptional. Visit us at [brother-usa.com](http://brother-usa.com) where you can download the latest product drivers and software, view product manuals, learn how to get the most out of your product with how-to videos and find answers to frequently asked questions.



Working with you for a better environment

### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. [www.brotherearth.com](http://www.brotherearth.com)

COMPATIBLE WITH  
**WINDOWS**



recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

<sup>▼</sup> Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

<sup>^</sup> Drum yield is approx., and may vary by type of use.

<sup>∨</sup> Requires an Internet connection and an account with desired service. See [www.brother.com](http://www.brother.com) for details.

<sup>♣</sup> Requires an Internet connection. See [www.brother.com](http://www.brother.com) for details.

<sup>♣</sup> Feature available using Brother ControlCenter

<sup>~</sup> The mobile device must have NFC capability and run Android OS 4.4 or later.

<sup>o</sup> Approx. 300 pages per month in accordance with ISO/IEC 19752 (Letter/A4) using the 2 toners provided in box.

<sup>\*</sup> Approx. toner cartridge yields in accordance with ISO/IEC 19752 (letter/A4).