

## CHERRY KC 1000



Models may vary from the image shown

### The quiet all-rounder

CHERRY KC 1000 is rock-solid CHERRY technology with an excellent price/performance ratio. Modern, flat design with gentle, quiet and durable wear-resistant keys. Universal, reliable and optimised for professional use. In black or grey.

### Key benefits

- Flat, corded keyboard including cursor and number pad
- Whisper keystroke keys with wear-resistant laser key legends
- Up to 10 million keystrokes
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- Plug & Play via USB connection
- 3 blue status LEDs
- Optimised for professional use in the office (GS approval)

### Technical Data:

#### Layout (country or language):

Product dependant, see table "Models"

#### Housing colour:

Product dependant, see table "Models"

#### Key colour:

Product dependant, see table "Models"

#### Weight (product):

530 g

#### Total weight (with packaging):

725 g

#### Cable Length:

approx. 1.80 m

#### Storage Temperature:

-20°C to 65°C

#### Operating Temperature:

0°C to 50°C

#### Current Consumption:

max. 50 mA

#### Interface:

- USB

#### Product approvals:

Product dependant, see table "Models"

#### System requirements:

- USB connection

#### Delivery Volume:

- CHERRY KC 1000
- Operating instructions in hard copy

#### Dimensions (product):

458 x 170 x 20 mm

#### Packaging dimensions:

480 x 205 x 27 mm

#### Reliability:

- MTBF (90) > 80,000 hours

#### Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 4

#### Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 32

#### Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

## Models:

(possible country/layout versions, others available on request)

|   | Product name   | Order number | EAN code      | Layout (country or language) | Housing colour | Key colour | Product approvals                      | Number of Keys |
|---|----------------|--------------|---------------|------------------------------|----------------|------------|--|----------------|
| 1 | CHERRY KC 1000 | JK-0800BE-0  | 4025112082115 | Belgium                      | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 2 | CHERRY KC 1000 | JK-0800BE-2  | 4025112082122 | Belgium                      | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 3 | CHERRY KC 1000 | JK-0800CH-0- | 4025112082238 | Switzerland                  | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 4 | CHERRY KC 1000 | JK-0800CH-2  | 4025112082689 | Switzerland                  | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 5 | CHERRY KC 1000 | JK-0800DE-0  | 4025112081309 | Germany                      | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 6 | CHERRY KC 1000 | JK-0800DE-2  | 4025112081316 | Germany                      | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 7 | CHERRY KC 1000 | JK-0800ES-0- | 4025112082191 | Spain                        | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 8 | CHERRY KC 1000 | JK-0800ES-2  | 4025112081347 | Spain                        | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 9 | CHERRY KC 1000 | JK-0800EU-0  | 4025112081484 | US English with EURO symbol  | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS, KCC | 104+4          |

|    | Product name   | Order number | EAN code      | Layout (country or language) | Housing colour | Key colour | Product approvals                      | Number of Keys |
|----|----------------|--------------|---------------|------------------------------|----------------|------------|--|----------------|
| 10 | CHERRY KC 1000 | JK-0800EU-2  | 4025112081491 | US English with EURO symbol  | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS, KCC | 104+4          |
| 11 | CHERRY KC 1000 | JK-0800FR-0- | 4025112082207 | France                       | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 12 | CHERRY KC 1000 | JK-0800FR-2  | 4025112081323 | France                       | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 13 | CHERRY KC 1000 | JK-0800GB-0- | 4025112082184 | UK                           | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 14 | CHERRY KC 1000 | JK-0800GB-2  | 4025112081330 | UK                           | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 15 | CHERRY KC 1000 | JK-0800IT-0- | 4025112082221 | Italy                        | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 16 | CHERRY KC 1000 | JK-0800IT-2- | 4025112082702 | Italy                        | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 17 | CHERRY KC 1000 | JK-0800KR-2  | 4025112082054 | English (US) / Korean        | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS, KCC | 104+4          |
| 18 | CHERRY KC 1000 | JK-0800PN-0- | 4025112082214 | Pan-Nordic                   | light grey     | light grey | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |
| 19 | CHERRY KC 1000 | JK-0800PN-2- | 4025112082696 | Pan-Nordic                   | black          | black      | c-tick, UL, CE, FCC, BSMI, TÜV/GS      | 105+4          |