

# EB-W39

## DATASHEET / BROCHURE



With detailed WXGA resolution and the versatility to be positioned just about anywhere, this durable projector will provide years of service.

The compact, stylish design of the EB-W39 makes it the ideal choice for sharp, legible presentations and vivid video content, especially in roles where portability is key. Long lamp life and trusted Epson durability offer peace of mind and minimal maintenance.

### Bright, vivid content on a large scalable screen

Enjoy large scale presentations with crisp, clear text, as well as compelling imagery and video content on screen sizes up to 320 inches. 3,500-lumen performance combines with a high contrast ratio of 15,000:1 to offer outstanding visual performance, even in well-lit rooms.

### Years of uninterrupted meetings

With a lamp life and air filter maintenance cycle of 12,000 hours in eco mode, users won't need to worry about maintenance for more than 5 years<sup>1</sup>.

### Installation and placement flexibility

Automatic vertical and manual horizontal keystone correction provide greater flexibility as to where the projector can be placed in the room for distortion-free images and the wide optical zoom adds to the flexibility.

### Network and Wi-Fi capability

Wi-Fi compatibility and network capability (via RJ45) mean the EB-W39 can be added to a company network or upgraded for wireless device access at a later stage (optional accessory required).

### High-quality sound

This projector has a built-in 5W speaker to allow audio content to be heard clearly, without the need for additional external speakers.

## KEY FEATURES

- **HD-Ready bright images**  
3LCD technology and equally high white and colour light output
- **Contrast ratio of 15,000:1**  
Deep, rich blacks and dense shadow areas
- **Wide connectivity options**  
Network-enabled and Wi-Fi capable
- **Low TCO**  
Lamp and filter life of 12,000 hours
- **Versatile and flexible control**  
Project from different sources with HDMI input and mobile connectivity



**EPSON**  
EXCEED YOUR VISION

## PRODUCT SPECIFICATIONS

### TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0.59 inch with MLA (D9)

### IMAGE

Colour Light Output	3,500 lumen- 2,280 lumen (economy)
White Light Output	3,500 lumen - 2,280 lumen (economy) in accordance with ISO 21118:2012
Resolution	WXGA, 1280 x 800, 16:10
High Definition	HD ready
Aspect Ratio	16:10
Contrast Ratio	15,000 : 1
Light source	Lamp
Lamp	UHE, 210 W, 6,000 h durability, 12,000 h durability (economy mode)
Keystone Correction	Auto vertical: $\pm 30^\circ$ , Manual horizontal $\pm 30^\circ$
Colour Processing	10 Bits
2D Vertical Refresh Rate	50 Hz - 85 Hz
Colour Reproduction	upto 1.07 billion colours

### OPTICAL

Projection Ratio	1.30 - 1.56:1
Zoom	Manual, Factor: 1.2
Lens	Optical
Image Size	33 inches - 320 inches
Projection Distance Wide/Tele	1.68 m - 2.02 m ( 60 inch screen)
Projection Lens F Number	1.58 - 1.72
Focal Distance	16.9 mm - 20.28 mm
Focus	Manual
Offset	10 : 1

### CONNECTIVITY

USB Display Function	3 in 1: Image / Mouse / Sound
Interfaces	USB 2.0 Type A, USB 2.0 Type B, RS-232C, Wireless LAN IEEE 802.11b/g/n (optional), VGA in (2x), VGA out, HDMI in (2x), Composite in, Component in (2x), RGB in (2x), Stereo mini jack audio out, Stereo mini jack audio in (2x), Ethernet interface (100 Base-TX / 10 Base-T)
Epson iProjection App	Ad-Hoc / Infrastructure

### ADVANCED FEATURES

Security	Kensington lock, Security cable hole, Wireless LAN unit lock, Wireless LAN security, Password protection
2D Colour Modes	Dynamic, Cinema, Presentation, sRGB, Blackboard
Features	AV mute slide, Automatic keystone correction, Built-in speaker, Direct Power on/off, Document Camera Compatible, Easy OSD pre-setting, Horizontal and vertical keystone correction, Network projection, OSD copy function, PC Free, Quick Corner, Split-Screen-Function, Wireless LAN capable, iProjection set-up by QR code
Video Colour Modes	Blackboard, Cinema, Dynamic, Presentation, sRGB
Projector control	via: AMX, Crestron, Control4, Extron

## EB-W39

### WHAT'S IN THE BOX

- VGA cable
- Main unit
- Power cable
- Remote control incl. batteries



**EPSON**  
WORLD LEADER  
IN PROJECTORS

Source: Futuresource Consulting Ltd.

**EPSON**<sup>®</sup>  
EXCEED YOUR VISION

---

## PRODUCT SPECIFICATIONS

---

### GENERAL

Energy Use	315 W, 225 W (economy), 0.2 W (standby)
Supply Voltage	AC 100 V - 240 V, 50 Hz - 60 Hz
Product dimensions	302 x 249 x 92 mm (Width x Depth x Height)
Product weight	2.7 kg
Noise Level	Normal: 37 dB (A) - Economy: 28 dB (A)
Temperature	Operation 5° C - 35° C, Storage -10° C - 60° C
Humidity	Operation 20% - 80%, Storage 10% - 90%
Included Software	Epson Projector Management Software, EasyMP Multi PC Projection, EasyMP Network Projection
Options	Document camera, Soft carry case, Wireless LAN unit
Loudspeaker	5 W
Room Type / Application	Boardroom, Portable / Huddle space, Collaboration space / Classroom
Positioning	Ceiling Mounted, Desktop
Colour	White / Grey
TCO Certified	Yes

---

### OTHER

Warranty	36 months Carry in, Lamp: 36 months or 1,000 h Optional warranty extension available
----------	---

---

---

## EB-W39

---

### WHAT'S IN THE BOX

---

- VGA cable
- Main unit
- Power cable
- Remote control incl. batteries

---

## OPTIONAL ACCESSORIES

---

---

EB-W39

---

- Wireless LAN Adapter - ELPAP10  
V12H731P01
- Soft Carry Case - ELPKS70  
V12H001K70
- ELPLP96  
V13H010L96
- Air Filter - ELPAF32  
V13H134A32
- Active Speakers (2 x 15W) - ELPS02  
V12H467040DA
- Ceiling Pipe (700mm) - ELPP14  
V12H003P14
- Ceiling Pipe (450mm) - ELPP13  
V12H003P13
- Ceiling Mount (White) - ELPMB23  
V12H003B23
- Control and Connection Box - ELPCB02  
V12H614040DA

## LOGISTICS INFORMATION

SKU	V11H856041
EAN code	8715946642598
Country of Origin	Philippines



For more information please contact:

Home users: 0343 90 37766  
Business users\*: 0871 42 37766  
Republic of Ireland: 01 436 7742  
Or visit us at <https://www.epson.co.uk/contactus>  
\* 10p per minute plus network extras.

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

1. Based on eight hours of use per day, five days a week.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.  
Last extracted: 2018-09-12

**EPSON**<sup>®</sup>