



HL-L2375DW Compact mono laser printer



PRINT



WIRELESS

Built with reliability in mind, the HL-L2375DW is the printer of choice for busy home and small offices. This affordable device, comes feature packed with wired and wireless connectivity combined with fast print speeds, and up to 1,200 page inbox toner, all in a compact unit.



Key Features:

- **Fast print speeds of up to 34 pages per minute**
- **Automatic 2-sided print**
- **250 sheet paper input**
- **Built in wired and wireless connectivity**
- **Up to 1,200 page* in-box toner**
- **64MB memory**

Performance designed for businesses of tomorrow

Designed to be set-up and ready to use in minutes. The HL-L2375DW, has a fast print speed of 34 pages per minute, together with automatic 2-sided print and large 250 paper tray. Combined with wired and wireless connectivity, you can have more time to focus on your work.

Maximum value for money

With cost being a key factor in many businesses, the HL-L2375DW comes with a large up to 1,200 page* inbox toner. Together with automatic 2-sided printing, significantly saves time, and reduces the cost of each document printed.

Quiet without compromise

Print quietly without comprising on speed or quality, operating at the lowest decibel in class (under 50dB). All the models throughout the range are designed to sit on your desk, printing quietly at full speed while you work without interruption.

Designed to go the distance

Built to perform for longer. The HL-L2375DW, has been designed with you in mind. Made from robust and hardwearing materials and supported by outstanding service as standard, providing the peace of mind that your printer will keep on going.

General

Technology Electrophotographic Laser Printer	Processor 600MHz	Wired Network Interface 10Base-T/100Base-TX
Laser Classification Class 1 Laser Product (IEC60825-1:2014)	Memory 64MB	Local Interface Hi-Speed USB 2.0

Print

Print Speed Standard (A4) Up to 34ppm (pages per minute)	Automatic 2-Sided Printing Print on to both sides of the paper	Embedded Fonts (PCL) 66 scalable fonts, 12 bitmap fonts, 16 barcodes
Print Speed 2-Sided (A4) Up to 16 sides per minute (8 sheets per minute)	FPOT (First Print Out Time) Less than 8.5 seconds from ready mode	Embedded Barcodes (PCL) Code39, Interleaved 2 of 5, FIM (US-PostNet, Post Net (US-PostNet) EAN-8, EAN-13, UPC-A, UPC-E, Codabar, ISBN(EAN), ISBN(UPC-E), Code128 (set A, set B, set C), EAN128 (set A, set B, set C), Code93, GS1Databar, MSI
Resolution Up to 1,200 x 1,200dpi	Warm Up Time Less than 9 seconds from sleep mode	
	Print Languages PCL6	

Printer Functions

N-up Printing³ Reduce up to 2, 4, 9, 16 or 25 A4 pages into just one A4 page (Mac, up to 2, 4, 6, 9, or 16)	Booklet Printing⁴ Print documents in A5 booklet format using automatic or manual 2-sided print
Watermark Printing⁴ Watermark your documents with predefined text or with your own user-defined messages	

Standard Paper Handling

Paper Input² Standard Tray - 250 sheets Manual feed slot - 1 sheet	Paper Output² Face Down - 150 sheets Face Up (Straight Paper Path) - 1 sheets
---	--

Media Specification

Media Types & Weights Standard Plain & recycled paper (between 60 - 163g/m ²)	2-sided Print Plain & recycled paper (between 60 - 105g/m ²)	Media Sizes Standard Tray A4, Letter, A5, A5 (Long Edge), A6, Executive
Manual feed slot Plain, Recycled, Bond, Label, Envelope, (between 60 - 230g/m ²)	Envelope & Label Printing Yes, from the Manual feed slot: support for 1 envelope / sheet	Manual feed slot Width: 76.2mm to 215.9mm x Length: 127mm to 355.6mm 2-sided Print A4

1 Approx declared yield value in accordance with ISO/IEC19752

2 Calculated with 80g/m² paper.

3 Windows[®] & Mac[®] only.

4 Windows[®] only.

5 Optional download.

6 Maximum number of printed pages per month can be used to compare designed durability between like Brother products.

For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

All specifications correct at the time of printing and are subject to change.

Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

Mobile / Web Based Printing

Brother iPrint&Scan (Android/ iPad / iPhone / iPod/ Windows® Phone/ 8,10 & RT)
Print from, scan to, preview copies and check the machine status from a mobile/ tablet/ laptop device

Google Cloud Print 2.0
Print most common file types from any Google Cloud Print enabled application

AirPrint
Print from and scan to most common file types from any AirPrint enabled application

Brother Print Service Plugin
Print from Android devices without a dedicated App

Mopria
Print most common file types from Mopria supported Android devices

Printer Driver

Windows®
Windows®10
(32 & 64 bit editions)
Windows®8
(32 & 64 bit editions)
Windows®7
(32 & 64 bit editions) Windows® Server 2016, 2012 2012R2 & 2008R2 Windows® Server 2008 (32 & 64 bit editions)

Macintosh⁵
macOS 10.8.x or greater

Linux⁵
CUPS, LPD/LPRng (32 & 64 bit editions)

PCL Driver
PCL 6

Network and Security

Wired Network
Built in Ethernet
10Base-T/100Base-TX

Wireless Network
IEEE 802.11b/g/n
(Infrastructure Mode / Adhoc Mode)

Wi-Fi Direct™
Print wirelessly without having to go through a wireless access point (both automatic and manual methods supported)

Wireless Set-Up Support
Wi-Fi Protected Setup (WPS)

Wireless Applications
Vertical Pairing

Network Protocols
TCP/IP (IPv4 and IPv6)

IPv4
ARP, RARP, BOOTP, DHCP, APIPA(Auto IP), WINS/NetBIOS name resolution, DNS Resolver, mDNS, LLMNR responder, LPR/LPD, Custom Raw Port/Port9100, SMTP Client, IPP/IPPS, FTP Server, SNMPv1/v2c/v3, HTTP/HTTPS server, TFTP client and server, ICMP, Web Services (Print)

IPv6
NDP, RA, DNS resolver, mDNS, LLMNR responder, LPR/LPD, Custom Raw Port/Port9100, IPP/IPPS, SMTP Client, FTP Server, SNMPv1/v2c/v3, HTTP/HTTPS server, TFTP client and server, ICMPv6, SNTP Client, Web Services (Print)

Wired Network Security
SMTP-AUTH, SNMP v3,SSL/TLS(SMTP,HTTP,IPP)

Wireless Network Security
WEP 64/128 bit, WPA-PSK (TKIP/AES), WPA2-PSK (TKIP/AES), SMTP-AUTH, SNMP v3,SSL/TLS(SMTP,HTTP,IPP)

E-mail Notifications
Automatically have the device send e-mail alerts when it requires attention, such as when the toner is low or needs replacing

E-mail Reports
Receive usage reports on a regular basis via e-mail

IP Filter
Restrict which network users can or cannot access the device over the network (IPv4 only)

Setting Lock
Secures access to the devices control panel by locking it

1 Approx declared yield value in accordance with ISO/IEC19752.

2 Calculated with 80g/m² paper.

3 Windows® & Mac® only.

4 Windows® only.

5 Optional download.

6 Maximum number of printed pages per month can be used to compare designed durability between like Brother products.

For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

All specifications correct at the time of printing and are subject to change.

Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

Fleet Management Tools

Embedded Web Server
Web based print management software embedded onto the device

BRAdmin Professional^{4&5}
LAN/WAN management software

PrintSmart Solutions (optional)

PrintSmart Cost Control
Monitor and control printing costs for all Brother and 3rd party devices

For more information on PrintSmart Solutions visit: www.brother.eu

Supplies

Inbox Toner
1,200 pages¹

Standard Yield Toner
1,200 pages¹(TN-2410)

High Yield Toner
3,000 pages¹(TN-2420)

Drum (DR-2400)
Approx 12,000 pages

Carton Contents
Toner cartridge, drum, power supply cord, driver software for Windows®, Quick Set-Up Guide (PC interface cable NOT included)

The frequency of replacement consumables will vary depending on the complexity of the prints, the percentage of coverage, paper size, page per job, and the type of media.

Dimensions and Weights

With Carton (WxDxH)
356 x 360 x 183 mm - 7.2kg

Without Carton (WxDxH)
438 x 283 x 519 mm - 8.3kg

Duty Cycles

Recommended Monthly
Up to 2,000 pages monthly print volume

Maximum Monthly⁶
Up to 15,000 pages monthly print volume

Environment

Power Consumption
Printing - 440W (260W in quiet mode), Ready - 42W, Sleep - 6.2W, Deep sleep - 0.6W, Off - 0.03W

TEC Value
1.227kWh / Week

Sound Pressure Level
Printin
g
49dbA,
Quiet mode
printing 44dbA,
Ready
Up to 30dbA

Power Saving
This enables the printer to consume less energy when not in use

Toner Saving
This reduces the toner usage and helps to reduce the total cost of printer ownership

Energy Star
Yes

Eco Mode
Yes

¹ Approx declared yield value in accordance with ISO/IEC19752.

² Calculated with 80g/m² paper.

³ Windows® & Mac® only.

⁴ Windows® only.

⁵ Optional download.

⁶ Maximum number of printed pages per month can be used to compare designed durability between like Brother products.

For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

All specifications correct at the time of printing and are subject to change.

Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.