

SEATING

SWIVEL STOOLS

- Seats made of 19-gauge embossed steel with 1/8" tempered hardboard inlay
- 1" diameter, 16-gauge steel frame all-welded tubing
- Circular 18-gauge footrest guarantees comfort and stability
- Heavy-duty rubber cushioned steel glides protect floors
- 1" x 14 1/2" long steel adjustment stem for easy height selection on all units
- Models **FC661** and **FC665** have 9 1/2" x 15 3/4" 4-way adjustable backrest
- Optional casters available: **FC675**
- Models **FC673** and **FC674** come with a padded seat



FC658



FC661



FC665



FC673



Model No.	Adjustable Height"	Seat Dimensions"	Wt. lbs.	Price /Each
FC658	22-28	14	19	
FC661	22-28	14	28	
FC665	17-23	14 1/2 x 15	27	
FC673	20-26	14	19	
FC674	25-31	14	22	
FC675	Set of 4 casters	-	2	

INDUSTRIAL SEATING

- Features a full 8" of pneumatic lift while seated
- Exclusive extension tube provides an adjustable height range of 17" to 35"
- Seats and backs are microcellular self skinning polyurethane foam which inhibits punctures, tears and moisture absorption
- Large 26" dia. five leg steel base with 2 1/2" diameter glides ensure stability and safety even at the highest levels
- Large wide angle footrests make it easy to step up into seat



FC680

Features 22° back angle and 10° seat tilt adjustment w/double paddle handles.



FC681

Features 3" back rest height and 3" back rest depth adjustment. Assembly required.



Model No.	Seat"	Dimensions Backrest"	No. of Footrests	Price /Each
FC680	18 1/2 x 17	15 3/4 x 9	3	
FC681	16 1/4 x 16 1/4	14 1/2 x 9	1	

DELUXE SWIVEL STOOLS



- These padded stools will provide workers with maximum comfort and support
- 360° swivel motion is ideal for workers who have repetitive side to side movement
- Seat easily adjusts to your selected height, just raise or lower the steel rod and lock securely in place
- 2" foam over a 1/2" plywood base and 1/2" foamed backrest
- All-welded frame constructed of 1" diameter 16-gauge steel
- 3/4" circular tube footrest
- Four leg cluster design has a 22" spread giving them optimum stability
- Black vinyl upholstery with a royal grey frame
- Optional casters available

Model **OJ905** has an ergonomic self-skinned molded polyurethane foam seat and back, features lumbar support, waterfall seat and 4-leg frame for superior comfort and durability.



FC670



OJ905



Model No.	Adjustable Height"	Seat Dimensions"	Wt. lbs.	Price /Each
OJ905	25-31	19 x 17	33	
FC670	25-31	19 x 17	33	
FC675	Set of 4 casters	-	2	

STEEL BASE SWIVEL STOOLS

- 5" pneumatic lift of 25" to 30", for easy height adjustment
- Five legs and an all-welded steel base, gives optimum stability
- 16-gauge, 1" diameter steel legs
- Full 360° rotation
- Colour: Powder coated black Santex
- Optional casters are available



OJ973



OJ974



OJ975

Model No.	Upholstery Seat	Dimensions"	Wt. lbs.	Price /Each
OJ973	Vinyl and foam-padded seat and back	19 x 17	33	
OJ974	Polyurethane seat and back	18 x 17	33	
OJ975	Premium self skinned polyurethane seat and back	19 x 18	35	
OJ976	Optional set of 5 tile casters (includes leg insert socket)			

POLYPROPYLENE SWIVEL STOOLS

- 360° swivel
- Constructed of 1" diameter 16-gauge tubular steel base
- 17" x 16 1/2" sturdy polypropylene seat
- **OA241** comes with a 4-leg base and manual height control from 22" to 28" – simply raise or lower the steel rod and lock securely into place
- **ONS63/ONS64** comes with a 5-leg glass reinforced nylon base and nylon foot ring
- **ONS63/ONS64** features pneumatic height control from 21" to 28"

ONS64



Model No.	Description	Price /Each
OA241	4-leg base with glides	
ONS63	5-leg base with glides	
ONS64	5-leg base with casters	



MUR-VAN MANUFACTURING

