

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

USB-C to DisplayPort Cable, 4K @ 60Hz, Thunderbolt 3, 6 ft.

MODEL NUMBER: U444-006-DP











Features

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-andplay operation—no software required

Applications

- Play 4K video from your laptop, Chromebook or MacBook on a large-screen monitor
- Give a video presentation at a meeting, training session, conference or trade show
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor
- Edit large documents on two different monitors

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DisplayPort
 input

Package Includes



 U444-006-DP USB-C to DisplayPort Cable, 4K @ 60Hz, Thunderbolt 3, 6 ft.

Specifications

MODEL TEXT		
What Does This Product Do?		
OVERVIEW		
Over Current Protection		
INPUT		
Cable Length (ft.)	6	
Cable Length (m)		
Cable Length (in.)		
Built-In Cable Length (ft.)		
Built-In Cable Length (m)		
Built-In Cable Length (in.)		
Built-In Cable Length (cm)		
External Power Supply Input Specs (V / Hz / A)		
External Power Supply Output Specs (V / A)		
External Power Supply Cord Length (ft.)		
External Power Supply Cord Length (m.)		
Bus Powered	Yes	
Cable Length (cm)		
Product Length (in.)		
Product Length (cm.)		
Product Length (ft.)		
Product Length (m.)		
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators		



PHYSICAL		
Shipping Dimensions (hwd / in.)	0.000 × 0.000 × 0.000	
Shipping Weight (lbs.)	0.0000	
Unit Packaging Type	Polybag	
Unit Dimensions (hwd / in.)		
Unit Dimensions (hwd / cm)		
Unit Weight (Ibs.)	0.23	
Unit Weight (kg)	0.10	
Material of Construction	PVC and ABS	
Color	Black	
Transmitter Unit Dimensions (hwd / in.)		
Transmitter Unit Dimensions (hwd / cm.)		
Receiver Unit Dimensions (hwd / in.)		
Receiver Unit Dimensions (hwd / cm.)		
Transmitter Unit Weight (lbs.)		
Transmitter Unit Weight (kg)		
Receiver Unit Weight (lbs.)		
Receiver Unit Weight (kg)		
Cable Jacket Rating	VW-1	
ENVIRONMENTAL		
Operating Temperature Range	32 to 113 F (0 to 45 C)	
Storage Temperature Range	14 to 158 F (-10 to 70 C)	
Relative Humidity		
Operating Elevation (ft.)		
Storage Elevation (ft.)		
BTUs	2.1 BTU/Hr	
Power Consumption (Watts)	0.6	
Operating Humidity Range	10% to 85% RH, non-condensing	
Storage Humidity Range	5% to 90% RH, non-condensing	
Power Provided to Connected Device(s)		
COMMUNICATIONS		



ſ		
Signal Range (ft.)		
CONNECTIONS		
Ports		
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	DISPLAYPORT (MALE)	
Connector Plating	Gold	
PORT EXPANSION		
Max Distance (Between any 2 Units)		
FEATURES & SPECIFICATIONS		
Max Supported Video Resolution	3840 x 2160 @ 60Hz	
Displayport Specification	1.2	
HDCP Specification	1.3	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Audio Specification		
Driver Required	No	
Recommended Category Cable		
CERTIFICATIONS		
Certifications	CE, FCC, ROHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies