



# msi

MONITOR

## Optix MAG27C



### SPECIFICATION

Panel Size	27" (68.6 cm)
Aspect ratio	16:9
Panel Resolution	1920x1080 (FHD)
Pixel Pitch (H x V)	0.3114(H)X0.3114(V)
Refresh Rate	144Hz
Response time	1ms(MPRT)
NTSC / sRGB	85% / 110%
Viewing angle	178° (H) x 178° (V)
Curved	1800R
Brightness	250 cd/m2
Contrast Ratio	3000:1 (HDCR:100000000:1)
Power consumption	48W
I/O	1 x DP 1.2 - 1920 x 1080 (Up to 144Hz) 1 x HDMI 1.4 - 1920 x 1080 (Up to 120Hz) 1 x DVI - 1920 x 1080 (Up to 144Hz)
Control	5 way joystick control button MSI Gaming OSD format Warm, Cool, User Mode PC, Movie, FPS, RTS, Eye saver
Dimension (W x H x D)	612.24 x 434.11 x 205.44mm / 24.10" x 17.09" x 8.09"
Weight	4.89kg / 10.78lbs(NW) 6.53kg / 14.40lbs(GW)

### FEATURE



#### Curved Gaming

View more of your game with the 1800R curve rate that is perfect for gamers to play their games.



#### 144Hz High Refresh Rate

Experience smooth gaming with a blazing fast 144Hz refresh rate, that gives you the upperhand in fast moving games.



#### 1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



#### Gaming OSD

Customize and set the ultimate monitor modes, settings and functions with the monitors Gaming OSD.



#### Adjustable Stand

Maximize your productivity and comfort with the adjustable stand.



#### Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



#### 85% NTSC

Game colors and details will look more realistic and refined, to push game immersion to its limits.



#### 110% sRGB

Get the most vivid and detailed colors with sRGB 110%.

### CONNECTIONS



- 1x HDMI
- 1x HDMI

- 1x Kensington Lock
- 1x Earphone



**msi**®

M O N I T O R

## Optix MAG27C

- 3. 1x Display Port
- 4. 1x USB 3.1 Gen 1 Type B
- 5. 1x Earphone

- 8. 1x Mic
- 9. 2x USB 3.1 Gen 1 Type A