



A height adjustable 32" IPS Panel Technology monitor featuring WQHD resolution
 Looking for the perfect monitor? Choose the best all-around IPS Panel Technology guaranteeing perfect colour reproduction with wide viewing angles. Meeting the demands of both graphic design and the modern work place, the 32" XB3270QS with a high WQHD resolution offers the perfect solution for productivity, design and data analysis. The height-adjustable stand ensures you can adjust the screen position to your preferences, and the flicker-free panel with blue light reducer function reduces eye fatigue. This high-end feature-rich panel is the new hallmark of the discerning user across many sectors.



WQHD

With true WQHD 2560 x 1440p resolution your monitor is ready to display high definition images. This means you can accommodate more information on your screen, i.e. over 76% more in comparison to a 1920 x 1080 monitor.



IPS TECHNOLOGY

IPS technology offers higher contrast, darker blacks and much better viewing angles than standard TN technology. The screen will look good no matter what angle you look at it.

1. DISPLAY CHARACTERISTICS

DIAGONAL 31.5"; 80cm

ASPECT RATIO 16 : 9

PANEL	IPS Panel Technology LED, matte finish
NATIVE RESOLUTION	WQHD 2560 x 1440 (3.7 megapixel)
BRIGHTNESS	300 cd/m ² typical
CONTRAST	1200 : 1 typical
CONTRAST	80 000 000 : 1 ACR
RESPONSE TIME	4ms
VIEWING ZONE	horizontal/vertical: 178° / 178° ; right/left: 89° / 89° ; up/down: 89° / 89°
BLUE LIGHT REDUCER	yes
FLICKER FREE LED	yes
DISPLAY AREA H X W	392.7 x 698.1 mm; 15.5" x 27.5"
PIXEL PITCH H X V	0.273 x 0.273 mm
HORIZONTAL SYNC	30 - 90kHz
VERTICAL SYNC	50 - 75Hz
SYNCHRONIZATION	Separate Sync
DISPLAY COLOURS	1.07 billion

2. INTERFACES & CONNECTORS

DIGITAL INPUT CONNECTOR	DVI, HDMI, DisplayPort
HDCP	yes;
HEADPHONE CONNECTOR	Yes
OUTPUT CONNECTOR	headphone connector

3. FEATURES

APPLE - MAC	All iiyama monitors are compatible with Apple-Macintosh computers.
PLUG & PLAY	VESA DDC2B™
CONTROLS	Via OSD in 11 languages (EN, FR, ES, PT, RU, DE, IT, CZ, NL, PL, JP) and control buttons (Power/ Menu, Scroll up, Scroll down/ ECO Mode, Left/ Input Select, Right/ Audio Adjust)
USER CONTROLS	luminance (contrast, brightness, i-Style Colour, ACR, OverDrive), image setup (aspect ratio), colour temperature, OSD setup (H. position, V. position, timeout, language), PIP (PIP setting, size, position, swap), extra (input select, DDC/CI, reset, information)
SPEAKERS	2 x 3 W (Stereo)
ANTI-THEFT-DEVICE	Kensington-lock™ prepared
CERTIFICATES	CE, TÜV-Bauart, CU, VCCI-B, PSE
HEIGHT ADJUSTABLE STAND	Yes
HEIGHT ADJUSTMENT	100mm
SWIVEL STAND	90°; 45° left; 45° right
TILT ANGLE	22° up; 3° down
VESA MOUNTING	100 x 100 mm

COLOUR	Black
--------	-------

4. ACCESSORIES

INCLUDED ACCESSORIES	power cable, HDMI cable, DisplayPort cable, headphone hook, quick start guide, safety guide
----------------------	---

5. POWER MANAGEMENT

POWER SUPPLY	AC 100 - 240 V, 50 / 60 Hz
POWER SUPPLY UNIT	internal
POWER USAGE	57 W typical; max. 0.5 W in Power management mode
POWER MANAGEMENT	VESA DPMS

6. EU ENERGY EFFICIENCY LABEL

ENERGY EFFICIENCY CLASS	C
ON MODE POWER CONSUMPTION	63.5W
ANNUAL ENERGY CONSUMPTION	93 kWh/annum*
VISIBLE SCREEN DIAGONAL	80 cm; 31.5"; (32" segment)

This is information under Regulation (EU) No 1062/2010.

**Based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.*

7. DIMENSIONS & WEIGHT

DIMENSIONS W X H X D	730 x 445.5 (545.5) x 230 mm
WEIGHT	8.9 kg

All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects.

© IYAMA CORPORATION (). ALL RIGHTS RESERVED.