



## **WWS110i** | 1D Pocket Scanner **Cost-Effective Wireless Scanner for On-the-Go Scanning Applications**



### **Key Features**

- Scans Popular 1D Barcodes
- Pairs with iOS, Android & Windows Mobile Devices
- Built-In Bluetooth
- Transmits Data to Host up to 32 ft
- Laser Aim Assist for Quick Data Capture

# WWS110i | 1D Pocket Scanner

## OPTIC & PERFORMANCE

Light Source: 650nm visible red laser  
Compensation Light: Visible white LED  
Sensor: Linear image sensor  
Scan Rate: 380 Scans/ sec (Smart Detection)  
Resolution: 4mil/ 0.1mm  
Scan Angle: 41°  
Print Contrast Ratio: 30%  
Width of Field: 13Mil Code39: 5.51 in (140 mm)  
Memory: 2MB (20,000 barcodes)

## D.O.F. ENVIRONMENT: 800 LUX

4 Mil Code 39: 1.57 ~ 2.75 in (40 ~ 70 mm)  
5 Mil Code 39: 1.37 ~ 3.54 in (35 ~ 90 mm)  
10 Mil Code 39: 1.57 ~ 6.69 in (40 ~ 170 mm)  
15 Mil Code 39: 1.96 ~ 8.85 in (50 ~ 255 mm)  
13 Mil UPC/EAN: 1.96 ~ 8.26 in (50 ~ 210 mm)

## PHYSICAL CHARACTERISTICS

Dimension: W1.08 x L2.69 x H.63 in (W27.5 x L68.4 x H16.2 mm)  
Weight: .95 oz. (27g) – scanner only  
Color: Black  
Material: PC  
Cable: Micro(M) to USB A(M) cable, 5 ft. (1.5 m)  
Trigger: Scan button, function button  
Indicator: LED, buzzer, vibrator

## ELECTRICAL

Operation Voltage: 3.7 VDC  $\pm$  5%  
Working Current: < 170mA  
Standby Current: < 60mA  
Power Down Current: < 500uA  
Battery: 3.7V, 400mAh, Li-Polymer battery  
Number of Scans (full charge): 5400 scans  
(1 scan/ 5 secs, Bluetooth connected)

## CONNECTIVITY

Radio: Bluetooth 2.1 + EDR (Class2)  
Range: 33 ft./ 10 m (line of sight)  
Interface/Profile: BT HID, BT SPP, USB HID, USB VCP, Memory

## USER ENVIRONMENT

Operating Temperature: 32 ~ 104 °F (0 ~ 40°C)  
Storage Temperature: 14 ~ 140 °F (-10 ~ 60°C)  
Humidity: 0% ~ 95%RH (non-condensing)  
Drop Durability: 5 ft. (1.5 m)  
Sealing:N/A  
Ambient Light: 50,000 Lux (Sunlight)  
Symbologies: UPC-A/UPC-E, EAN-8/EAN-13, Industrial 2 of 5,  
Codabar, Matrix 2 of 5, Code 11, Code 93, Code 32, Code 128,  
Standard Code 39, Full ASCII Code 39, Interleaved 2 of 5, China  
Postal Code, MSI Plessey Code, UK Plessey Code, EAN/UCC 128,  
Telepen Code, IATA Code, GS1 Databar

## REGULATORY

ESD: Functional after 4KV contact, 8KV Air discharge  
EMC/RF: FCC Part15B ClassB, Part15C, CE EN301489-1-17,  
EN300328, EN62479  
Safety Approval: EN/IEC60825-1 (Class 1), FDA, EN/IEC60950-1  
Environmental: WEEE, RoHS 2.0

## ACCESSORY

Cable: Micro(M) to USB A(M) Cable, 1.5M, Black  
(SKU: 633808920708, QTY: 1)  
Hand Strap (Lanyard): Large Hand Strap, 0.53M, Yellow  
(SKU: 633808920715, QTY: 1)

