

Serie | 6 Washer / Dryers

WVG30462GB Automatic washer dryer



A

The washer dryer with the best energy efficiency: washes and dries economically.

- Energy efficiency class A.
- **EcoSilence Drive™**: extremely energy-efficient and quiet in operation with an especially long life.
- **Allergy+/ECARF Quality Seal**: specially developed for the needs of allergy sufferers.
- **HygieneCare**: washing programme with high dry temperature pre-treatment for hygienic fabric care.
- **VarioPerfect™**: takes 65% less time or uses 50% less energy – delivers total flexibility.

Technical Data

Construction type :	Free-standing
Removable work top :	No
Door hinge :	Left
Length of electrical supply cord (cm) :	210
Height of removable worktop (mm) :	850
Dimensions of the product (mm) :	850 x 600 x 590
Net weight (kg) :	79.0
Drum volume (l) :	56
EAN code :	4242005064229
Connection rating (W) :	2200
Current (A) :	10
Voltage (V) :	220-240
Frequency (Hz) :	50
Approval certificates :	CE, VDE
Energy consumption (wash and dry of full wash load) (kWh) :	4.76
Energy consumption (wash only) (kWh) :	0.73
Water consumption (wash and dry full wash load) (l) :	103



4 242005 064229

Optional accessories

WMZ2420 : Built-under cover

Serie | 6 Washer / Dryers

WVG30462GB

Automatic washer dryer

The washer dryer with the best energy efficiency: washes and dries economically.

Performance

- Label: Energy efficiency A at a range of energy efficiency classes from A to G / Washing performance A
- Capacity: 7 kg washing, 4 kg drying
- Non-stop wash and dry programme 4 kg
- Maximum spin speed :1500 rpm
- Energy consumption wash and dry 4.76 kWh Water consumption wash and dry 103 litres
- Drum volume: 56 litres
- Noise level: washing 47 dB (re 1pW) Noise level: spinning 74 dB (re 1pW)
- Noise level: drying 59dB (re 1pW)

Programmes/functions

- Special programmes: Down Wear, Drum clean, Mixed Load , Super Quick 15, Allergy +, Hygiene Care, Wool Programme, Delicate/Silk programme
- Special programme - drying: fluff removal cycle
- Touch control buttons: start/pause with reload function, Start delay, Temperature selection, drying time, SpeedPerfect, EcoPerfect

Key features


- EcoSilence drive with 10 year warranty
- Fully electronic metal control dial for all wash and special programmes
- Autodry function, time selection options
- ECARF Seal of Quality: allergy-friendly product
- Reload function: Be flexible in adding laundry items even after start of the wash cycle.

Additional features


- Large LED display for programme status indication, temperature, spin speed, remaining time and 24 hour time delay
- Extra large drum with SoftSurge system - Gentle washing thanks to a unique drum structure
- ActiveWater: water management system
- Reload facility
- Safeguard monitoring system adjusts load distribution and programme settings to protect clothes
- Buzzer to indicate the end of cycle
- Child lock
- Metal door catch
- Flow-through sensor for optimum water use
- Foam detection system
- Overdosage indication

Technical Information

- Dimensions (H X W X D): 85 x 60 x 59 cm
- Slide-under installation
- Large silver-black grey door with 180° opening and 32cm porthole opening

Serie | 6 Washer / Dryers**WVG30462GB****Automatic washer dryer**

measurements in mm



measurements in mm