



# 4MP H.265 Dome IP Camera with Junction Box

## O4VLD5

2.8mm fixed lens, white housing



### Features

- Supports up to 4MP @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- H.265/H.264/MJPEG compression supported
- True Day/Night operation (IR cut filter)
- Adaptive IR LEDs reduce IR saturation
- IR range: 65' (depending on scene reflection)
- True WDR (wide dynamic range) operation
- IP66 compliant, weather resistant
- IK10 compliant, vandal resistant
- Junction box included
- Conformant with ONVIF Profile S
- 5 year warranty



Included Junction Box

### Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2592 x 1520
Minimum Illumination	F1.2, 0 lux (IR LED on)
3-axis Adjustment	Pan: 0°-240°, Tilt: 0°-68°, Rotate: 0°-220°
Field of View (H)	103°
Day/Night	IR cut filter
White Balance	Auto, Indoor, Outdoor, Manual
Compensation	WDR / BLC / HLC
Electronic Shutter Speed	1/25 - 1/100000 sec.
DNR	2D / 3D

### Video Specifications

Main Resolution	2592x1520 / 2560x1440 / 2304x1296 / 1980x1080 / 1280x720 @ 30fps
Compression	H.265, H.264 (HP/MP/BP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

### Network Specifications

Protocols	IPv4, IPv6, TCP, UDP, RTP, RTSP, HTTP, SMTP, FTP, DHCP
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP/Mac address filtering, digest authentication
User Access	Max. 10 simultaneous users, Actual number of users may vary depending on bandwidth

### Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Mobile (iPhone® and Android™)

### Audio Specifications

Mono Input	G.711A / G.711 U
Mono Output	-

### External Terminal Specifications

Ethernet	10/100 Mbps
Analog Video Output	BNC
Microphone Input	3.5mm
Power	DC jack

### System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, object removal, abnormality, line crossing, intrusion
Alarm Triggers	Analytics
Alarm Events	FTP upload, email upload
Image Settings	Privacy mask, region of interest, OSD

### Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	4W
Operating Temperature	-4°F - 122°F
Operating Humidity	10% - 90% RH
Unit Dimensions	4.6" (Dia.) x 3.6" (H)
Unit Weight	1.4 lbs.
Junction Box Dimensions	4.4" (Dia.) x 1.6" (H)
Junction Box Weight	8 oz.
Certifications	FCC, RoHS

### Optional Accessories



POEINJ  
12.95W  
PoE Injector



PSW5  
12VDC  
Power Supply

ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 8/28/17

