

**msi**®

MONITOR

Optix MAG27CQ

SPECIFICATION

Panel Size	27" (68.6 cm)
Aspect ratio	16:9
Panel Resolution	2560x1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H)X0.2331(V)
Refresh Rate	144Hz
Response time	1ms(MPRT)
NTSC / sRGB	85% / 110%
Viewing angle	178°(H) x 178°(V)
Curved	1800R
Brightness	250 cd/m ²
Contrast Ratio	3000:1 (HDCR:10000000:1)
Power consumption	60W
I/O	1 x DP 1.2 - 2560 x 1440 (Up to 144Hz) 1 x HDMI 2.0 - 2560 x 1440 (Up to 120Hz) 1 x DVI - 2560 x 1440 (up to 60Hz)
Control	5 way joystick control button MSI Gaming OSD format Warm, Cool, User Mode PC, Movie, FPS, RTS, Eye saver
Dimension (W x H x D)	612.24 x 434.11 x 205.44mm / 24.10" x 17.09" x 8.09"
Weight	4.89kg / 10.78lbs(NW) 6.53kg / 14.40lbs(GW)

FEATURE



Curved Gaming

View more of your game with the 1800R curve rate that is perfect for gamers to play their games.



WQHD High Resolution

Game titles will even look better, displaying more details due to the WQHD resolution.



144Hz High Refresh Rate

Experience smooth gaming with a blazing fast 144Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Gaming OSD

Customize and set the ultimate monitor modes, settings and functions with the monitors Gaming OSD.



Adjustable Stand

Maximize your productivity and comfort with the adjustable stand.



85% NTSC

Game colors and details will look more realistic and refined, to push game immersion to its limits.



110% sRGB

Get the most vivid and detailed colors with sRGB 110%.

CONNECTIONS



1. 1x DVI
2. 1x HDMI
3. 1x Display Port

4. 1x Earphone
5. 1x Kensington Lock