

DISPLAY

AVAILABLE COLORS



Silver



Black



*DS-3211MT LANDSCAPE SHOWN IN BLACK
(POLE STAND NOT INCLUDED)*

KEY FEATURES

- 32" Pro Series True Outdoor All-Weather Digital Signage for permanent outdoor installation
- Bright 32"(1000 NIT) full HD, 1080p LED-LCD screen for improved outdoor viewing
- Interactive LG Innotek 10 point PCAP multi touch screen with anti-glare surface.
- Integrated Sharp touch controller. Plug and Play HID with Windows 7, 8 & 10, no calibration needed.
- Media Compartment for digital media player or fan less PC. (Opening: 7" x 12.5" x 3" deep / Interior: 8" x 14" x 2.5" deep)
- Direct Sunlight-Readable
- High temperature Enhanced Solar Tolerance (EST) technology prevents isotropic backout
- Exterior designed to protect internal components from rain, snow, dust, insects, humidity, and salt air.
- Powder-coated rust-proof aluminum exterior for strength and durability.
- Multi-fan airflow system keeps the unit cool and dry in temperatures up to 122 degrees F.
- Ability to operate in cold weather (5 degrees F). *
- Ambient Light Sensor provides automatic dimming of backlight for night time viewing.
- Front tempered anti-reflective glass window provides added protection to LED-LCD screen, and safeguards against vandalism & abuse.
- RS232 serial control with discrete on, off, and input control.
- Rear IR receiver (located in the cable-entry compartment).
- Innovative water-tight Cable Entry System seals out moisture and allows for easy hook-ups.
- Water-tight media player/cable compartment accommodates a variety of media players including Brightsign[®]
- Weatherproof detachable 20W speaker module (not included), remote control, and control buttons.
- Side control button lock-out prevents unauthorized users from changing the programming.
- Includes warranty and manual

SunBriteDS[®]

Outdoor Digital Signage

SCREEN	<p>SCREEN 32" Diagonal Color Active Matrix TFT LED-LCD</p> <p>RESOLUTION 1920 x 1080 Full-HD 1080p</p> <p>ASPECT RATIO 16:9</p> <p>CONTRAST RATIO (32", 47" & 55") 1300:1</p>	<p>FRAME RATE 60hz</p> <p>VIEWING ANGLE 178° x 178°</p> <p>RESPONSE TIME 25ms</p> <p>TV FORMATS (32", 47" & 55") 1080p, 1080i, 720p, 720i, 480p, 480i</p>
CONNECTIONS	<p>RF Antenna/CATV (ATSC/QAM/NTSC) x1</p> <p>HDMI HDMI™ Input x2</p> <p>VIDEO COMPOSITE S-Video x1 and Composite Video x1, L/R Audio Inputs x1</p> <p>VIDEO COMPONENT YPbPr plus Stereo Audio x2</p> <p>PC 15-pin D-sub VGA plus Stereo Audio</p> <p>CONTROL SET RS232 Serial, Discrete IR Control, Concealed IR Window</p>	<p>TOUCH INTERFACE USB 2.0 type B female jack. USB type A to B cable required (not included)</p> <p>AUDIO OUT Digital SPDIF Audio(fixed) Analog 1/8" headphone jack (variable)</p> <p>SPEAKERS 20 WATT detachable speaker module (not included)</p> <p>INPUT POWER 100-240 VAC, 50-60 Hz,</p>
TEMPERATURE TOLERANCES	<p>OPERATING TEMP 5° to 122° F. (-15° to 50°C.)*</p> <p>NON-OP. TEMP -24° to 122° F. (-31° to 50°C.)*</p> <p>(OFF MODE WITH POWER APPLIED) The non-operating temperature feature requires power to be applied.</p>	
PHYSICAL SPECS	<p>ACCESSORIES INCLUDED Weatherproof remote control</p> <p>EXTERIOR Powder-coated aluminum.</p> <p>EXTERIOR COLORS Black, Silver</p> <p>TV DIMENSIONS (3211MTSL) 31.08"(789mm) W x 18.87"(479mm) H x 5.49"(139mm) D (3211MTSP) 18.87"(479mm) W x 31.08"(789mm) H x 5.49"(139mm) D</p> <p>RESIDENTIAL WARRANTY Two-year parts and labor.</p> <p>COMMERCIAL WARRANTY Two-year parts and labor.</p>	