

LG MONITORS

24MP58VQ-P

24" Full HD IPS Monitor

24"

* Class size: See below for details.

Full HD IPS Display
On-Screen Control
My Display Presets
Smart Energy Saving

PANEL

Screen Size	23.8"
Panel Type	IPS
Color Gamut (CIE 1931)	72%
Color Depth (Number of Colors)	16.7M colors
Pixel Pitch (mm)	0.2745 x 0.2745
Response Time	5ms
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness	250cd/m ²
Contrast Ratio	Mega
Viewing Angle	178/178
Surface Treatment	Anti-glare, 3H

INPUT/OUTPUT

HDMI (ver 1.4)	Yes
DVI-D	Yes
D-Sub	Yes

POWER

Type	Adapter
Input	100-240Vac, 50/60Hz
Normal On (EPA 6.0)	22W

SPECIAL FEATURES

Picture Mode	Yes
Reader Mode	Yes
Original Ratio	Yes
PIP/PBP	Yes
Color weakness	Yes
Flicker safe	Yes
Automatic Standby	Yes
Six Axis Control	Yes
Smart Energy Saving	Yes
Super Resolution+	Yes
4 screen split	Yes
On-Screen Control	Yes
Others	Black Stabilizer

DIMENSIONS/WEIGHT

Without Stand (WxHxD)	21.7" x 3.4" x 13.1"
With Stand (WxHxD)	21.7" x 7.4" x 16.5"
Shipping Dimensions (WxHxD)	24.4" x 15.6" x 5.1"
With Stand Weight	7.1 lbs
Shipping Weight	10.2 lbs

CABINET / ACCESSORIES

Power Cord	Yes
HDMI	Yes
CD	Yes
ESG	Yes
Manual	Yes
Cable holder	Yes

STANDARD

UL(cUL)	Yes
TUV-TYPE	Yes
FCC-B, CE	Yes
EPA 6.0	Yes
ErP	Yes
EPEAT	Yes (Gold)
Windows	Yes (win10)

LIMITED WARRANTY / UPC

Limited Warranty	1 Year Parts and Labor
UPC	719192199699

Country of Origin: China