

USB-C Docking Station, 4K @ 30 Hz, HDMI, Thunderbolt 3, USB Hub, Gb Ethernet – Silver

MODEL NUMBER: U442-DOCK13-S



Features

Highlights

- Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- USB-A/USB-C ports transfer data from thumb drives or printers at speeds up to 5 Gbps
- Connects you to a wired Ethernet network when no Wi-Fi is available
- Easy installation with plug-and-play operation—no software required

Applications

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your notebook or download data from the Ethernet at true 10/100/1000 Mbps Ethernet speeds
- Transfer data to and from a USB flash drive
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode



- Display device with DVI* or HDMI input
- Not for use with Thunderbolt monitors

Package Includes

- U442-DOCK13-S USB-C Docking Station, 4K, HDMI, Thunderbolt 3, Gb Ethernet – 30 Hz, Silver
- Owner's manual

Specifications

MODEL TEXT	
What Does This Product Do?	
OVERVIEW	
Over Current Protection	
INPUT	
Cable Length (ft.)	
Cable Length (m)	
Cable Length (in.)	
Built-In Cable Length (ft.)	
Built-In Cable Length (m)	
Built-In Cable Length (in.)	6
Built-In Cable Length (cm)	15
External Power Supply Input Specs (V / Hz / A)	
External Power Supply Output Specs (V / A)	
External Power Supply Cord Length (ft.)	
External Power Supply Cord Length (m.)	
Bus Powered	Yes
Cable Length (cm)	



Product Length (in.)	9.80
Product Length (cm.)	
Product Length (ft.)	
Product Length (m.)	
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Yellow = ACT Green = LINK White = POWER
PHYSICAL	
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	9.8 x 1.5 x .6
Unit Dimensions (hwd / cm)	
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
Material of Construction	Aluminum
Color	Silver
Transmitter Unit Dimensions (hwd / in.)	
Transmitter Unit Dimensions (hwd / cm.)	
Receiver Unit Dimensions (hwd / in.)	
Receiver Unit Dimensions (hwd / cm.)	
Transmitter Unit Weight (lbs.)	
Transmitter Unit Weight (kg)	
Receiver Unit Weight (lbs.)	
Receiver Unit Weight (kg)	
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 131F (0C ~ 55C)
Storage Temperature Range	14 ~ 158F (-10 ~ 70C)
Relative Humidity	40 ~ 50% RH
Operating Elevation (ft.)	
Storage Elevation (ft.)	
BTUs	
Power Consumption (Watts)	
Operating Humidity Range	



Storage Humidity Range	
Power Provided to Connected Device(s)	
COMMUNICATIONS	
Signal Range (ft.)	
CONNECTIONS	
Ports	
Side A - Connector 1	(1) USB C (MALE)
Side B - Connector 1	(1) HDMI (FEMALE); (1) RJ45 (FEMALE); (1) USB A (FEMALE); (1) USB C (FEMALE)
Connector Plating	Nickel
PORT EXPANSION	
Max Distance (Between any 2 Units)	
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	4096 x 2160
HDMI Specification	1.4
HDCP Specification	2.2
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	
Driver Required	No
Recommended Category Cable	
CERTIFICATIONS	
Certifications	
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>