

## USB-C Memory Card Reader, 2-in-1 USB-A/USB-C, USB 3.1 Gen 1

MODEL NUMBER: U452-000-SD-A



### Features

### Highlights

- Built-in USB-A and USB-C male connectors are compatible with most devices
- USB 3.1 Gen 1 data transfer speeds up to 5 Gbps for fast file sharing
- Supports latest SD and Micro SD formats, including SDXC and SDHC
- Easy plug-and-play operation—no new software or drivers required
- Fits easily into camera bag or laptop sleeve for use anywhere

### Applications

- Transferring videos, images and other data between an SD or Micro SD memory card and your MacBook, Chromebook, PC, tablet, smartphone or laptop
- Loading a PowerPoint file onto a memory card at the office for presenting on a different computer on the road
- Storing digital photographs for later upload to your work computer

### System Requirements

- MacBook, Chromebook, PC, tablet, smartphone or laptop with USB port (USB 3.0 port required for maximum speeds)
- Compatible with the following memory cards:
- SD Cards: Secure Digital (SD), Elite Pro SD, Extreme III SD,



Gaming Edition SD, Platinum II SD, SD Pro, SDHC, SDXC, SD-Max, SD-Pleomax, SD-Pro C, Super SD, Turbo SD, Ultima I SD, Ultima II SD, Ultimate SD, Ultra High Speed SD, Ultra II SD, Ultra II SD Plus, Ultra SD, Ultra-X SD, DV-RS MMC, High Speed MMC/RS-MMC, MCCmobile, MMC Pro, MMCplus, MMCplus Turbo, RS-MMC

- Micro SD Cards: MicroSD (TransFlash), microSDHC

**Package Includes**

- U452-000-SD-A USB-C Memory Card Reader, 2-in-1 USB-A/USB-C, USB 3.1 Gen 1

## Specifications

MODEL TEXT	
What Does This Product Do?	Transfers memory card data to your MacBook, PC, phone or laptop via your device's USB-A, USB-C or Thunderbolt 3 port.
OVERVIEW	
Over Current Protection	
INPUT	
Cable Length (ft.)	0
Cable Length (m)	0
Cable Length (in.)	
Bus Powered	Yes
Cable Length (cm)	
Product Length (in.)	3.00
Product Length (cm.)	7
Product Length (ft.)	0



Product Length (m.)	0
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power/Data)
<b>PHYSICAL</b>	
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.43 x 2.9 x 0.79
Unit Weight (lbs.)	0.03
Unit Weight (kg)	0.01
Material of Construction	ABS
Color	Black
Cable Outer Diameter (OD)	
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80% RH, Non-Condensing
Operating Elevation (ft.)	
Storage Elevation (ft.)	
Operating Humidity Range	
Storage Humidity Range	
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB 3.0 A (MALE)
Side A - Connector 2	USB C (MALE)
Side B - Connector 1	SD (FEMALE)
Side B - Connector 2	MICRO SD (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>CERTIFICATIONS</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Certifications	Tested to CE, FCC, RoHS, REACH, ICES
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>