

N 30
B1HCCOANOB
SINGLE OVEN



COOKING PASSION SINCE 1877



A



Included accessories

1 x combination grid, 1 x universal pan

Built-in oven with CircoTherm® - The award-winning hot air system from Neff

- ✓ CircoTherm® - the unique hot air-system for simultaneous baking and roasting on up to 3 levels
- ✓ Hinged door

Features

Technical Data

Color / Material Front : Stainless steel
Built-in / Free-standing : Built-in
Integrated Cleaning system : No
Required niche size for installation (HxWxD) : 585-595 x 560-568 x 550
Dimensions of the product (mm) : 595 x 594 x 548
Dimensions of the packed product (HxWxD) (mm) : 675 x 690 x 660
Control Panel Material : Stainless steel
Door Material : Glass
Net weight (kg) : 41.8
Usable volume (of cavity) - cavity 1 (l) : 71
Cooking method : Conventional heat, Full width grill, Heißluft sanft, Hot Air, Hot air grilling
First cavity material : Other
Temperature control : No control of the temperature
Number of interior lights : 1
Approval certificates : CE, VDE
Length electrical supply cord (cm) : 120
EAN code : 4242004234456
Number of cavities (2010/30/EC) : 1
Energy efficiency class (2010/30/EC) : A
Energy consumption per cycle conventional (2010/30/EC) : 0.97
Energy consumption per cycle forced air convection (2010/30/EC) : 0.81
Energy efficiency index (2010/30/EC) : 95.3
Electrical connection rating (W) : 2990
Current (A) : 13
Voltage (V) : 220-240
Frequency (Hz) : 50; 60
Plug type : no plug



N 30
B1HCCOAN0B
SINGLE OVEN

Features

Design

- LED Display (Red)
- Fixed control dials, Bevelled oval controls
- Cavity inner surface: Enamel grey
- Drop down door
- Bar handle

Features

- Control panel lock
- Interior halogen light
- Double glazed door

Cleaning

- Full glass inner door

Programmes/functions

- 5 heating methods: CircoTherm®, Top/bottom heat, Hot air grilling, Full surface grill, CircoTherm® gentle
- Cooling fan

Accessories

- 1 x combination grid, 1 x universal pan

Performance/technical information

- Energy efficiency rating (acc. EU Nr. 65/2014): A
Energy consumption per cycle in conventional mode: 0.97 kWh
Energy consumption per cycle in fan-forced convection mode:
0.81 kWh
Number of cavities: Main cavity
Heat source: electrical
Cavity volume: 71 litre
- Total connected load electric: 2.99 kW
- Temperature range 50 °C - 275 °C
- Length of mains cable: 120 cm
- Nominal voltage: 220 - 240 V
- Appliance dimension (hxwxd): 595 mm x 594 mm x 548 mm
- Niche dimension (hxwxd): 585 mm - 595 mm x 560 mm - 568 mm
x 550 mm
- Please refer to the dimensions provided in the installation manual

N 30
B1HCCOANO B
SINGLE OVEN

Dimensioned drawings

