



T58UB10X0 INDUCTION HOB
FRAMELESS WITH FACETTED EDGES
802 MM



FlexInduction hob with TouchControl.

- ✓ TouchControl is a highly convenient way to control the hob. One touch is enough. A timer is also included.
- ✓ FlexInduction - The FlexZone lets you place your pots and pans anywhere you want and heats them exactly where they stand.
- ✓ Induction - With induction cooking, the heat is generated directly in the cookware for precise cooking that stops when power is off.
- ✓ PanBoost - Optimised power level function for more flexible and even faster heating.

Features

Technical Data

Product name/family : Cooking zone ceramic
 Construction type : Built-in
 Energy input : Electric
 Total number of positions that can be used at the same time : 4
 Required niche size for installation (HxWxD) : 51 x 750-750 x 490-500
 Appliance Width (mm) : 802
 Dimensions of the product (mm) : 51 x 802 x 522
 Dimensions of the packed product (HxWxD) (mm) : 126 x 953 x 603
 Net weight (kg) : 16.0
 Gross weight (kg) : 18.0
 Residual heat indicator : Separate
 Location of control panel : Hob front
 Basic surface material : Ceramic
 Color of surface : Black
 Approval certificates : AENOR, CE
 Length electrical supply cord (cm) : 110
 EAN code : 4242004234524
 Electrical connection rating (W) : 7400
 Current (A) : 2*16; 32
 Voltage (V) : 220-240
 Frequency (Hz) : 50; 60



4 242004 234524

Optional accessories

Z9410X1	Stainless Steel roaster with glass lid
Z9415X1	Steaming Rack for Stainless Steel roaster
Z9416X2	Griddle Plate
Z9417X2	Teppan Yaki (large)

T58UB10X0 INDUCTION HOB

FRAMELESS WITH FACETTED EDGES

802 MM

Features

Control

- Touch control

Flexibility

- Flex Induction
- 4 zone induction hob
-

Special features


- Boost setting for all zones
- Variable 17-stage power settings for each zone
- Digital display of cooking levels
- 2 stage residual heat indicators
- Timer with automatic shut off for all zones
LED timer for each zone with switch off function and acoustic signal
- ReStart function
- Automatic pan recognition
4.6kW power output (20A); current management options for 16A, 13A or 10A connection
- Safety cut out facility
- Control panel lock
- Control panel suspension
-

Technical information

- Cooking zones: 1 x Ø 400 mm x 240 mm, 3.3 kW (max. Power levels 3.7 kW) Induction or 2 x Ø 200 mm, 2.2 kW (max. Power levels 3.7 kW) Induction; 1 x Ø 280 mm, 2.6 kW (max. Power levels 3.7 kW) Induction; 1 x Ø 145 mm, 1.4 kW (max. Power levels 2.2 kW) Induction
- Measurement: (H/B/T) 51 x 802 x 522 mm
- Installation dimensions: (ID/W/D) 51 mm x 750 mm x 490 mm
- 80 cm width
- Length wire connection: 110 cm
- Main switch
- Min. worktop thickness: 30 mm
- Output 7400 W
- Cable included in packaging

T58UB10X0 INDUCTION HOB
FRAMELESS WITH FACETTED EDGES
802 MM

Dimensioned drawings



①
Ventilation gap must
be present

All measurements in mm