

FIELDBOOK KS80



Fieldbook KS80 is powered by a 64-bit Octa-core processor running at 1.5 GHz, to run the most demanding enterprise applications.

Designed to operate in harsh environments, this tablet is IP68 certified and fully protected against dust and water.




8' Gorilla Glass 3



Android 7.0



IP68 - Etanche



Octa-core



8 500 mAh



32 GB Storage

Technical Specifications

Software	Android® 7.0 Nougat	Interface	x1 Micro SD (SDHC/SDXC) max 128GB x1 SIM card (3G/4G) x1 USB 2.0 type A x1 3.5mm standard earphone jack x1 power on/off x1 volume +/-
Processor	Mediatek® MT6753, max 1.5GHz ARM Mali™ -T720 graphics	Sensors	G-sensor Proximity sensor Light sensor
RAM & Storage	3 GB RAM DDR3L 32 GB storage	Power Supply	Battery Lithium-ion polymer x1 Batterie 8 500mAh removable Adapter AC 100V-240VAC, 50/60Hz Output 5V 2A
Display	8" IPS (1280x800) HD 350 nits Capacitive 10-points multi-touch Corning Gorilla Glass 3	Environment	Drop Resistant 1m Certified IP68 Internal Stainless steel frame Temperature - Operate : -20°C à 55°C - Storage : -30°C à 70°C Humidity 95% non condensing
Network & Communication	Wifi a/b/g/n Bluetooth 4.0 GSM : 850/900/1800/1900 3G : 900/2100 LTE : B1/3/7/20 NFC GPS		
Camera	Front : 2 MP Rear : 13 MP + Flash Led		
Dimensions	226 x 141 x 14 mm 644g		