

22BK430H-B

22" Full HD IPS Monitor

KEY FEATURES

- 22" (21.5" DIAGONAL) IPS DISPLAY
- FHD RESOLUTION (1920X1080)
- EYE COMFORT : READER MODE
- SMART ENERGY SAVING
- ON SCREEN CONTROL
- COMPACT BEZEL



Images on screen are simulated



FULL HD IPS DISPLAY

IPS (In-Plane Switching) technology highlights the performance of liquid crystal displays. Response times are shortened, color reproduction is improved, and users can view the screen at virtually any angle.

ON-SCREEN CONTROL

On-Screen Control puts a host of essential monitor settings into a handy window for quick, easy access. Volume, brightness, picture mode presets, Screen Split 2.0 and Dual Controller and more can now be adjusted with just a few clicks of the mouse, instead of hard buttons on the monitor.








22BK430H-B

22" Full HD IPS Monitor

PICTURE QUALITY	
Screen Size	22" Class (21.5" diagonal)
Panel Type	IPS
Color Gamut (CIE1931)	72%
Color Depth(Number of Colors)	16.7M colors
Pixel Pitch(mm)	0.24795x0.24795
Response Time (GTG)	5ms (Faster)
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness	250cd/m ² (Typ.) 200cd/m ² (Min.)
Contrast Ratio	1000:1 (Typ.)
Viewing Angle	178/178
Surface Treatment	Anti glare, 3H
INPUT/OUTPUT	
HDMI	Yes (ver1.4, 1ea)
D-Sub	Yes (1ea)
DisplayPort	No
Headphone Out	Yes
POWER	
Type	Adapter
Input	100 ~240 , 50/60Hz
Output	19V/1.3A
Normal On (EPA Typ.)	25W
Normal On (factory out condition Typ.)	29W
Power Save/Sleep Mode (Max)	Under 0.3W
DC Off (Max)	Under 0.3W
SPECIAL FEATURES	
Picture Mode	Custom, Reader, Color Weakness, Photo, Cinema, Game
Ratio	Wide/Original
DDC/CI	Yes
HDCP	Yes (Ver 1.4)
Plug & Play	Yes
Response Time Control	Yes
Adaptive Sync	AMD FreeSync™
DAS Mode	Yes
Black Stabilizer	Yes
Crosshair	Yes
Flicker Safe	Yes
Automatic Standby	Yes

SPECIAL FEATURES	
Smart Energy Saving	Yes
On Screen Control (OSC)	Yes
Super Resolution+	Yes
Black Level	Yes
DFC	Yes
Gamma Control	Yes
Color Temperature	Yes
R/G/B Color Control	Yes
OSD Lock	Yes
Auto Adjustment(D-sub Only)	Yes (Ver 1.4)
DIMENSIONS/WEIGHT	
With Stand (WxHxD)	20.1" x 15.6" x 7.2"
Without Stand (WxHxD)	20.1" x 12.03" x 1.5"
Shipping Dimensions (WxHxD)	25.2" x 14.4" x 4.9"
With Stand Weight	6.2 lbs
Without Stand Weight	5.5 lbs
Shipping Weight	8.4 lbs
DESKTOP STAND	
Base Detachable	Yes
Tilt(Angle)	-5~20 Degree
CABINET / ACCESSORIES	
Wall Mountable	Yes
Power Cord	Yes
HDMI	Yes (1.8m cable)
S/W Install CD	Yes
Easy Setup Guide	Yes
Manual	Yes
STANDARD	
UL(cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
VCCI	Yes
ErP	Yes
Windows 10	Yes
LIMITED WARRANTY / UPC	
Limited Warranty	3 Year Parts and Labor
UPC	7 19192 61983 8
Country of Origin	China

-  <http://www.lg.com/us/business/commercial-display>
-  <http://www.twitter.com/LGCommDisplays>
-  <http://www.facebook.com/LGcommercialdisplays>
-  <http://www.linkedin.com/company/lg-commercial-displays-usa>
-  <http://www.youtube.com/lgcommercialdisplayusa>