CT INFO

LG MONITORS



24BK430

24" IPS FHD Monitor

24" FHD(1920x1080) IPS Display

AMD FreeSync™ Technology

Eye Comfort: Reader Mode

Smart Energy Saving

On Screen Control

Compact Bezel



Screen Size	23.8"
Panel Type	IPS
Color Gamut (CIE1931)	72%
Color Depth(Number of Colors)	16.7M colors
Pixel Pitch(mm)	0.2745 x 0.2745
Response Time (GTG)	5ms (Faster)
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness	250cd/m2(Typ.) 200cd/m2(Min.)
Contrast Ratio	1000:1(Typ.)
Viewing Angle	178/178
Surface Treatment	Anti glare ,3H
INPUT/OUTPUT	
HDMI	Yes (ver1.4, 1ea)
D-Sub	Yes (1ea)
Headphone Out	Yes
POWER	
Туре	Adapter
Input	100 ~240, 50/60Hz
Output	19V/1.3A
Normal On (EPA Typ.)	26W
Normal On (factory out	30W
condition Typ.)	
	Under 0.3W

SPECIAL FEATURES	
Picture Mode	Custom, Reader, Color Weakness, Photo, Cinema, Game
sRGB	No
Ratio	Wide/Original
DDC/CI	Yes
HDCP	Yes (Ver 1.4)
Plug & Play	Yes
Response Time Control	Yes
Adaptive Sync	AMD FreeSync™
DAS Mode	Yes
Black Stabilizer	Yes
Crosshair	Yes
Flicker Safe	Yes
Automatic Standby	Yes
Smart Energy Saving	Yes
On Screen Control (OSC)	Yes
Super Resolution+	Yes
Black Level	Yes
DFC	Yes
Gamma Control	Yes
Color Temperature	Yes
R/G/B Color Control	Yes
OSD Lock	Yes
Auto Adjustment(D-sub Only)	Yes

DIMENSIONS/WEIGHT	
With Stand (WxHxD)	21.9" x 16.6" x 7.2"
Without Stand (WxHxD)	21.9"x 13.02" x 1.5"
Shipping Dimensions (WxHxD)	27.1" x 15.4" x 4.9"
With Stand Weight	6.8 lbs
Without Stand Weight	6.2 lbs
Shipping Weight	9.3 lbs
DESKTOP STAND	
Base Detchable	Yes
Tilt(Angle)	-5~20 Degree
CABINET / ACCESSORIES	
VESA size (mm)	75 x 75
Power Cord	Yes
HDMI	Yes (1.8m cable)
S/W Install CD	Yes
Easy Setup Guide	Yes
Manual	Yes
STANDARD	
UL(cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
VCCI	Yes
ErP	Yes
Windows 10	Yes
LIMITED WARRANTY / UPC	
Limited Warranty	3 Year Parts and Labor
Limited Warranty UPC	3 Year Parts and Labor 7 19192 61984 5